



APC Smart-UPS On-Line, 3kVA, Rackmount 2U, 230V, 6x C13+2x C19 IEC outlets, SmartSlot, Extended runtime, W/rail kit, W/O Lithium-ion external battery

Brand : APC

Product code: SRT3000UXI-LI



Product name : APC Smart-UPS On-Line, 3kVA, Rackmount 2U, 230V, 6x C13+2x C19 IEC outlets, SmartSlot, Extended runtime, W/rail kit, W/O Lithium-ion external battery

APC Smart-UPS On-Line, 3kVA, Rackmount 2U, 230V, 6x C13+2x C19 IEC outlets, SmartSlot, Extended runtime, W/rail kit, W/O Lithium-ion external battery

[APC Smart-UPS On-Line, 3kVA, Rackmount 2U, 230V, 6x C13+2x C19 IEC outlets, SmartSlot, Extended runtime, W/rail kit, W/O Lithium-ion external battery:](#)

This APC Smart-UPS SRT3000UXI-LI is designed for IT professionals or network administrators to maintain business uptime and continuity. This 3kVA on-line 2U rackmount UPS provides pure sine wave power and extended runtime to support critical electronics during power disruptions. It comes with BS1363A British, IEC 320 C20, and Schuko CEE 7/EU1-16P inputs, 6x IEC 320 C13 and 2x IEC 320 C19 outlets. It has a SmartSlot for optional Network Management Card that enables graceful shutdown of physical servers, virtual machines & HCI Clusters via PowerChute Network Shutdown. The UPS can connect to EcoStruxure IT or third-party centralized management platforms. The UPS has a 5-year warranty, and has to be used with an external Lithium-ion battery sold separately.

Features		Ports & interfaces	
UPS topology *	Double-conversion (Online)	SmartSlot	✓
Output power capacity *	3 kVA	Design	
Output power *	2700 W	Form factor *	Compact
Waveform *	Sine	Rack capacity	2U
Input operation voltage (min) *	50 V	Product colour *	Black
Input operation voltage (max) *	240 V	Operational conditions	
Input frequency *	40/70 Hz	Operating temperature (T-T)	0 - 40 °C
Output operation voltage (min)	220 V	Storage temperature (T-T)	-20 - 50 °C
Output operation voltage (max)	240 V	Operating relative humidity (H-H)	0 - 95%
Output frequency	50/60 Hz	Storage relative humidity (H-H)	0 - 95%
Surge energy rating	432 J	Operating altitude	0 - 3048 m
Crest factor	3:1	Non-operating altitude	0 - 15240 m
Audible alarm(s)	✓	Weight & dimensions	
Ports & interfaces		Width	85 mm
AC outlet types	C13 coupler, C19 coupler	Depth	508 mm
AC outlets quantity	10 AC outlet(s)	Height	432 mm
Number of output IEC jumpers	8	Weight	22 kg
USB port	✓	Logistics data	
Serial interface	✓	Harmonized System (HS) code	85078000
		Total carbon footprint (kg of CO2e)	4848.09



5415247285069



0731304345039



731304345039



7313043450392

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.