



Lenovo Xeon Intel Gold 6354 processor 3 GHz 39 MB

Brand : Lenovo

Product family: Xeon

Product code: 4XG7A63450

Product name : Intel Xeon
Gold 6354



Intel® Xeon® Gold 6354

Lenovo Xeon Intel Gold 6354. Processor family: Intel® Xeon® Gold, Processor socket: LGA 4189, Processor lithography: 10 nm. Memory channels: Octa-channel, Maximum internal memory supported by processor: 6 TB, Memory types supported by processor: DDR4-SDRAM. Market segment: Server, Supported instruction sets: SSE4.2, AVX, AVX 2.0, AVX-512, Scalability: 2S. Maximum Enclave Size Support for Intel® SGX: 64 GB. Processor package size: 77.5 x 56.5 mm

Processor		Processor special features	
Processor manufacturer *	Intel	Intel® AES New Instructions (Intel® AES-NI)	✓
Processor generation	3rd Generation Intel® Xeon® Scalable	Intel Trusted Execution Technology	✓
Processor model *	6354	Intel® Speed Shift Technology	✓
Processor base frequency *	3 GHz	Intel® Transactional Synchronization Extensions	✓
Processor family *	Intel® Xeon® Gold	Intel® Total Memory Encryption	✓
Processor cores *	18	Intel® Crypto Acceleration	✓
Processor socket *	LGA 4189	Intel® Platform Firmware Resilience Support	✓
Component for	Server/workstation	Maximum Enclave Size Support for Intel® SGX	64 GB
Processor lithography *	10 nm	Intel VT-x with Extended Page Tables (EPT)	✓
Processor threads	36	Intel Software Guard Extensions (Intel SGX)	✓
System bus rate	11.2 GT/s	Intel 64	✓
Processor operating modes *	64-bit	Intel Virtualization Technology (VT-x)	✓
Processor boost frequency	3.6 GHz	Intel Virtualization Technology for Directed I/O (VT-d)	✓
High priority cores	8	AVX-512 Fused Multiply-Add (FMA) units	2
High priority core frequency	3.1 GHz	Intel® Deep Learning Boost (Intel® DL Boost) on CPU	✓
Low priority cores	10	Intel® Resource Director Technology (Intel® RDT)	✓
Low priority core frequency	2.8 GHz	Intel® Volume Management Device (VMD)	✓
Processor cache	39 MB	Intel® Run Sure Technology	✓
Thermal Design Power (TDP)	205 W	Mode-based Execute Control (MBE)	✓
Processor codename	Ice Lake	Intel® Optane™ DC Persistent Memory Supported	✓
Processor ARK ID	212460		
Memory		Operational conditions	
Maximum internal memory supported by processor	6 TB	Tcase	77 °C
Memory types supported by processor	DDR4-SDRAM	Technical details	
Memory channels *	Octa-channel	Target market	Cloud Computing
ECC	✓	Launch date	Q2'21
Graphics		Status	Launched
On-board graphics card *	✗	Supported memory types	DDR4-SDRAM
Discrete graphics card *	✗	Memory speed (max)	3200 MHz
On-board graphics card model *	Not available		
Discrete graphics card model *	Not available		
Features			
Execute Disable Bit	✓		
Market segment	Server		
Maximum number of PCI Express lanes	64		

Features		Technical details	
PCI Express slots version	4.0	Number of UPI links	3
Supported instruction sets	SSE4.2, AVX, AVX 2.0, AVX-512	Servicing status	Baseline Servicing
Scalability	2S	Logistics data	
Export Control Classification Number (ECCN)	5A992CN3	Harmonized System (HS) code	85423119
Commodity Classification Automated Tracking System (CCATS)	G178966	Weight & dimensions	
Processor special features		Processor package size	77.5 x 56.5 mm
Intel® Hyper Threading Technology (Intel® HT Technology)	✓	Other features	
Intel® Turbo Boost Technology	2.0	Maximum internal memory	6 TB



0889488531271



889488531271

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.