
Lenovo 00WE027 interface cards/adapter Internal



Brand : Lenovo

Product code: 00WE027

Product name : 00WE027

Intel OPA 100 Series Single-port PCIe 3.0 x16 HFA

Lenovo 00WE027 interface cards/adapter Internal:

Intel Omni-Path Architecture (OPA) is a family of PCIe adapters, switches, cables, and management software that provides high-performance connectivity between servers. This product guide describes the PCIe adapters, known as Omni-Path Host Fabric Adapters (HFAs).
Lenovo 00WE027. Host interface: PCIe, Host interface gender: Male, Expansion card standard: PCIe 3.0. Purpose: Server, Cooling type: Passive, Certification: FCC Part 15, Subpart B, Class A CAN ICES-3 (A) CISPR22 CISPR32/EN55032 EN55024 EN61000-3-2.... Weight: 240 g


Ports & interfaces	
Host interface *	PCIe
Host interface gender	Male
Expansion card standard	PCIe 3.0

Design	
Internal *	✔
Purpose	Server
Cooling type	Passive

Design	
Certification	FCC Part 15, Subpart B, Class A CAN ICES-3 (A) CISPR22 CISPR32/EN55032 EN55024 EN61000-3-2 EN61000-3-3 VCCI, Class A AS/NZS CISPR 22, Class A RRA/KC (KN22, KN24), Class A BSMI (CNS 13438), Class A GOST R IEC 60950-1 GOST R 51318.22 GOST 30804.24 GOST R 51317.3.2 (Section 6, 7) GOST R 51317.33 TUV NRTL: 60950-1, CSA 22.1.No. 60950-1 TUV SUD EN60950-1 CB Scheme: IEC 60950-1 RoHS II Directive 2011/65/EU REACH 1907/2006

Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-40 - 70 °C
Operating relative humidity (H-H)	5 - 85%
Storage relative humidity (H-H)	5 - 95%

Weight & dimensions	
Weight	240 g



0889488118472



889488118472



8894881184728

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date