HP Color LaserJet Enterprise Flow MFP 5800zf Printer



Brand : HP

Product family: Color LaserJet Enterprise Flow

Product code: 58R10A#B19

Product name : Color LaserJet Enterprise Flow MFP 5800zf Printer

Color LaserJet Enterprise Flow MFP 5800zf Printer

HP Color LaserJet Enterprise Flow MFP 5800zf Printer:

The most customisable HP A4 LaserJet, with advanced workflow solutions optimised for distributed office collaboration. Transform your workflows with advanced capabilities in a compact footprint. From print speeds to colour panels[11], get flexible configurations to meet your needs today and tomorrow. All while protecting your business against evolving cyber threats.

Dynamic security enabled printer Certain HP printers are intended to work only with cartridges that have a new or reused HP chip or electronic circuitry. These printers use dynamic security measures to block cartridges using a non-HP chip or electronic circuitry. Periodic firmware updates will maintain the effectiveness of these measures and block cartridges that previously worked. Reused HP chips and electronic circuitry enable the use of reused, remanufactured, and refilled cartridges.

Printing	
Duplex printing mode	Auto
Print resolution colour	1200 x 1200 DPI
Print resolution black	1200 x 1200 DPI
Print technology *	Laser
Printing *	Colour printing
Duplex printing *	✔
Maximum resolution *	1200 x 1200 DPI
Print speed (black, normal quality, A4/US Letter) *	43 ppm
Print speed (colour, normal quality, A4/US Letter)	43 ppm
Time to first page (black, normal)	6.8 s
Time to first page (colour, normal)	7.4 s
Watermark printing	✔
Secure printing	✔
Booklet printing function	✔

Copying	
Duplex copying *	✔
Duplex copying mode	Auto
Copying *	Colour copying
Maximum copy resolution *	600 x 600 DPI
Maximum copy size	A4
Copy speed (black, normal quality, A4)	43 cpm

Network	
Mobile printing technologies	Mopria Print Service, Apple AirPrint

Performance	
Maximum internal memory	6144 MB
Internal storage capacity	500 GB
Internal memory *	6144 MB
Built-in processor	✔
Processor frequency	1200 MHz
Sound pressure level (printing)	52 dB
Sound pressure level (duplex printing)	52 dB
Sound pressure level (scanning)	57 dB
Sound pressure level (standby)	22 dB
Sound power level (printing)	6.3 dB

Design	
Product colour *	White
Market positioning *	Business
Built-in display *	✔
Display	CGD
Display diagonal	25.6 cm (10.1")
Control type	Touch
Colour display	✔

Power	
Power consumption (printing)	655 W
Power consumption (copying)	655 W

Copying	
Copy speed (colour, normal quality, A4)	43 cpm
Time to first copy (black, normal)	6.1 s
Time to first copy (colour, normal)	8.6 s
Maximum number of copies	9999 copies
Copier resize	25 - 400%
N-in-1 copy function	✔
Book copy function	✔
ID-card copy function	✔
Auto fit function	✔
Edge erase function	✔
Stamp function	✔
Watermark copying	✔

Scanning	
Duplex scanning *	✔
Duplex scanning mode	Auto
Scanning *	Colour scanning
Optical scanning resolution *	600 x 600 DPI
Maximum scan resolution	600 x 600 DPI
Maximum scan area	216 x 356 mm
Scanner type *	Flatbed scanner
Scan technology	CIS
Scan to	E-mail, Network folder, USB
Scan speed (colour)	56 ppm
Scan speed (black)	56 ppm
Image formats supported	JPEG, MTIFF, TIFF
Document formats supported	CSV, DOCX, HTML, PDF, RTF, UNICODE, XLSX, XML, XPS
Input colour depth	24 bit
Greyscale levels	256
Scan drivers	TWAIN

Fax	
Faxing *	Colour faxing
Fax resolution (black)	300 x 300 DPI
Fax transmission speed	3 sec/page
Modem speed	33.6 Kbit/s
Fax memory	1000 pages
Auto-redialing	✔
Speed dialling	✔
Fax forwarding	✔
Fax delayed sending	✘
Auto reduction	✔

Features	
Recommended duty cycle	2000 - 10000 pages per month
Maximum duty cycle *	80000 pages per month
Duplex functions *	Print
Digital sender	✔
Number of print cartridges *	4
Printing colours *	Black, Cyan, Magenta, Yellow
Page description languages	PostScript 3, PDF 1.7, PCL 5c, XPS
Printer fonts	Scalable, TrueType, Windows, PCL, PostScript
All-In-One-multitasking	✔
Country of origin	Czech Republic

Power	
Power consumption (ready)	50.1 W
Power consumption (sleep)	0.9 W
Power consumption (off)	0.09 W
Energy Star Typical Electricity Consumption (TEC)	0.552 kWh/week
AC input voltage	100 - 240 V
AC input frequency	50/60 Hz

Brand-specific features	
HP Auto-On/Auto-Off	✔
HP Dynamic security	✔
HP Security tools	Identity management: Kerberos authentication; LDAP authentication; 1000 user PIN codes; optional HP and 3rd party advanced authentication solutions (e.g.; badge readers); Network: IPsec/firewall with Certificate; Pre-Shared Key; and Kerberos authentication; Supports WJA-10 IPsec configuration Plug-in; 802.1X authentication (EAP-PEAP; EAP-TLS); SNMPv3; HTTPS; Certificates; Access Control List; Data: Storage Encryption; Encrypted PDF & Email (uses FIPS 140 validated cryptographic libraries from Microsoft); Secure Erase; SSL/TLS (HTTPS); Encrypted Credentials; Device: Security lock slot; USB port disablement; hardware integration pocket for security solutions; Hardware-based Memory ShieldTM with Control Flow Integrity (CFI) in-device monitoring for attacks; SureStart Secure Boot - BIOS Integrity Checking with self-healing capability; Whitelisting - loads only known good code (DLLs, EXEs, ...); Security management: Compatible with Device Security Syslog Messages processed and accessable in Arcsight and Splunk SIEMs
HP GTIN (EAN/UPC) with options	(201) 196337404649; (AAZ) 196337404656; (AB0) 196786225222; (AB2) 196786225239; (ABJ) 196786225246; (ABT) 196337404663; (ABY) 196337404670; (AC4) 196337404694; (AC8) 196337404717; (ACJ) 196786225253; (ACQ) 196337404731; (AKV) 196337713390; (B13) 196337404755; (B19) 196337404779; (BAZ) 196337404786; (BBU) 196786225260; (BGJ) 196337404793; (BGM) 196786225277
HP GTIN (EAN/UPC)	196337404649, 196337404656, 196786225222, 196786225239, 196786225246, 196337404663, 196337404670, 196337404694, 196337404717, 196786225253, 196337404731, 196337713390, 196337404755, 196337404779, 196337404786, 196786225260, 196337404793, 196786225277

System requirements	
Windows operating systems supported	Windows 10, Windows 11

Features	
Replacement cartridges	HP 213A Black Original LaserJet Toner Cartridge (~3,500 pages) W2130A; HP 213A Cyan Original LaserJet Toner Cartridge (~3,000 pages) W2131A; HP 213A Yellow Original LaserJet Toner Cartridge (~3,000 pages) W2132A; HP 213A Magenta Original LaserJet Toner Cartridge (~3,000 pages) W2133A; HP 213X High Yield Black Original LaserJet Toner Cartridge (~9,000 pages) W2130X; HP 213X High Yield Cyan Original LaserJet Toner Cartridge (~6,000 pages) W2131X; HP 213X High Yield Yellow Original LaserJet Toner Cartridge (~6,000 pages) W2132X; HP 213X High Yield Magenta Original LaserJet Toner Cartridge (~6,000 pages) W2133X; HP 213Y Extra High Yield Black Original LaserJet Toner Cartridge, (~18,000 pages) W2130Y; HP 213Y Extra High Yield Cyan Original LaserJet Toner Cartridge (~12,000 pages) W2131Y; HP 213Y Extra High Yield Yellow Original LaserJet Toner Cartridge (~12,000 pages) W2132Y; HP 213Y Extra High Yield Magenta Original LaserJet Toner Cartridge (~12,000 pages) W2133Y
HP segment	Business

Input & output capacity	
Total number of input trays *	2
Total input capacity *	650 sheets
Total output capacity *	250 sheets
Paper tray 1 input capacity	100 sheets
Paper tray 2 input capacity	550 sheets
Multi-Purpose tray	✔
Multi-Purpose tray input capacity	100 sheets
Auto document feeder (ADF)	✔
Auto document feeder (ADF) input capacity	100 sheets
Maximum number of input trays	5
Maximum input capacity	2300 sheets
Maximum output capacity	250 sheets

Paper handling	
Maximum ISO A-series paper size *	A4
Maximum print size	207.4 x 1191.4 mm
Paper tray media types *	Plain paper, Glossy paper, Bond paper, Recycled paper, Envelopes, Card stock, Labels, Transparencies, Heavy paper, Lightweight paper, Rough paper, Letterhead
ISO A-series sizes (A0...A9) *	A4, A5, A6
ISO B-series sizes (B0...B9)	B5, B6
ISO C-series sizes (C0...C9)	C5, C6
Non-ISO print media sizes	Oficio, 16K
Envelopes sizes	B5, B6, C5, C6
Photo paper sizes	10x15 cm
Custom media width	64 - 216 mm
Custom media length	127 - 1200 mm
Paper tray media weight	60 - 220 g/m²
Multi-Purpose Tray media weight	45 - 199 g/m²

Ports & interfaces	
Direct printing *	✔
USB port	✔

System requirements	
Mac operating systems supported	Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina, Mac OS X 11.0 Big Sur, Mac OS X 12.0 Monterey, MacOS
Linux operating systems supported	✔
Other operating systems supported	ChromeOS, Android, iOS

Operational conditions	
Operating relative humidity (H-H)	10 - 80%
Recommended humidity operating range	30 - 70%
Recommended operating temperature range (T-T)	15 - 27 °C
Storage temperature (T-T)	-20 - 40 °C
Operating temperature (T-T)	10 - 32.5 °C

Certificates	
Certification	CISPR 22:2008 (International) Class A, CISPR 32:2015 (International) Class A / EN 55032:2015 Class A + A11:2020, CISPR 35:2016 (International) / EN 55035:2017 + A11:2020, EN IEC 61000-3-2:2019, EN 61000-3-3:2013+A1:2019 + A2:2021, FCC 47 CFR Part 15 Class A, ICES-003, Issue 7 Class A. Other EMC approvals as required by individual countries.

Sustainability	
Sustainability compliance	✔
Sustainability certificates	Blue Angel, ENERGY STAR, EPEAT Gold
Sustainable technologies and materials	15% post-consumer recycled plastic; ENERGY STAR® certified; EPEAT® registered

Carbon footprint	
Total carbon footprint (kg of CO2e)	410
Carbon emissions, manufacturing (kg of CO2e)	327
Carbon emissions, logistics (kg of CO2e)	13
Carbon emissions, end-of-life (kg of CO2e)	46
Total carbon emissions, w/o use phase (kg of CO2e)	19

Weight & dimensions	
Width	547 mm
Depth	460 mm
Height	583 mm
Weight	39.1 kg

Packaging data	
Package width	598 mm
Package depth	758 mm
Package height	652 mm
Package weight	44 kg

Packaging content	
Cartridge(s) included	✔
Included cartridge capacity (black)	7000 pages
Included cartridge capacity (CMY)	3000 pages
Cables included	AC

Logistics data	
Pallet gross weight	278.9 kg
Layers per pallet	3 pc(s)
Products per pallet	6 pc(s)

Ports & interfaces

USB 2.0 ports quantity	1
USB 3.2 Gen 1 (3.1 Gen 1) ports quantity	2

Network


Wi-Fi *	✕
Ethernet LAN *	✔
Cabling technology	10/100/1000Base-T(X)
Ethernet LAN data rates	10,100,1000 Mbit/s
Security algorithms	SNMPv3, SSL/TLS, EAP-PEAP, EAP-TLS, FIPS 140, HTTPS, IPSec

Technical details

Box contents	HP Color LaserJet Enterprise Flow MFP 5800zf Printer; HP Black Original LaserJet Toner Cartridge (~7,000 yield), HP Cyan, Magenta and Yellow Original LaserJet Toner Cartridges (~3,000 yield each) (toner cartridges installed); Documentation (Hardware Install Guide); Power cord
Master (outer) cases per pallet layer	2 pc(s)
Compliance certificates	CECP, GS mark, CCC, BIS, cUL, UL, CE, BSMI
General Product Safety Regulation (GPSR) URL	https://support.hp.com/gb-en/product/setup-user-guides/hp-color-laserjet-enterprise-flow-mfp-5800zf-printer-series/model/2101542943?sku=58R10A&serialnumber=58R10A ; https://kaas.hpcloud.hp.com/pdf-public/pdf_4666361_en-US-1.pdf

Other features

Number of users	15 user(s)
Custom media sizes	Tray 1: 64 x 127 to 216 x 1200 mm; Tray 2, optional 1x550-sheet feeders: 101 x 148 to 216 x 356 mm
Pallet dimensions (W x D x H)	800 x 1200 x 2083 mm
Recommended system requirements	2 GB available hard disk space; Internet connection; or USB port; Internet browser. 2 GB available hard drive space; Internet connection; or USB port; Internet browser.
Compatible operating systems	Windows 11; Windows 10; Windows Client OS; Android; iOS; Mobile OS; macOS 12 Monterey; macOS 11 Big Sur; macOS 10.15 Catalina; SAP; Chrome OS; Linux
Pallet dimensions (W x D x H) (imperial)	800.1 x 1199.9 x 2083.1 mm (31.5 x 47.2 x 82")
Pallet weight (imperial)	278.4 kg (613.7 lbs)
Acoustic power emissions (ready)	35 dB
Acoustic pressure emissions bystander (ready)	22 dB
Typical electricity consumption (TEC) number	0.552 kWh/week (Energy Star 3.0); 0.551 kWh/week (Blue Angel)
UNSPSC-code	43212110
Processor frequency	1.2 GHz
Manufacturer warranty	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements.
Electromagnetic compatibility	CISPR 22:2008 (International) Class A, CISPR 32:2015 (International) Class A / EN 55032:2015 Class A + A11:2020, CISPR 35:2016 (International) / EN 55035:2017 + A11:2020, EN IEC 61000-3-2:2019, EN 61000-3-3:2013+A1:2019 + A2:2021, FCC 47 CFR Part 15 Class A, ICES-003, Issue 7 Class A. Other EMC approvals as required by individual countries.



0196337404779



196337404779

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date