



Lenovo ThinkSystem ST50 server 4 TB Tower (4U) Intel Xeon E E-2224G 3.5 GHz 8 GB DDR4-SDRAM 250 W



Brand : Lenovo

Product family: ThinkSystem

Product code: 7Y48A03CEA

Product name : ST50

- Intel Xeon E-2224G (8MB Cache, 3.5GHz)
- 8GB (2666MHz) DDR4-SDRAM (1 x 8) & 4000GB HDD
ThinkSystem ST50 Tower Server

Lenovo ThinkSystem ST50 server 4 TB Tower (4U) Intel Xeon E E-2224G 3.5 GHz 8 GB DDR4-SDRAM 250 W:

The optimal first server

A powerful, yet whisper quiet, entry tower server featuring Intel® Xeon® processor. Ideal for retail, remote/ branch or home office, and perfect for desktide/ under-desk placement. Featuring enterprise-class storage, reliability, and serviceability support, the ThinkSystem ST50 is the ideal first server for the growing SMB or distributed work environment.

Lenovo ThinkSystem ST50. Processor family: Intel Xeon E, Processor frequency: 3.5 GHz, Processor model: E-2224G. Internal memory: 8 GB, Internal memory type: DDR4-SDRAM, Memory layout (slots x size): 1 x 8 GB. Total storage capacity: 4 TB. Ethernet LAN, Cabling technology: 10/100/1000Base-T(X). Power supply: 250 W. Chassis type: Tower (4U)

Processor		Design	
Processor manufacturer *	Intel	Chassis type *	Tower (4U)
Processor family *	Intel Xeon E	Product colour	Black
Processor model *	E-2224G	Performance	
Processor frequency *	3.5 GHz	Performance management	XClarity Provisioning Manager Lite
Processor boost frequency	4.7 GHz	Trusted Platform Module (TPM)	✓
Processor cache	8 MB	Software	
Motherboard chipset	Intel C246	Compatible operating systems *	Microsoft Windows Server, Red Hat Enterprise Linux, VMware ESXi
Number of processors installed	1	Processor special features	
Execute Disable Bit	✓	CPU configuration (max)	1
Idle States	✓	Enhanced Intel SpeedStep Technology	✓
Embedded options available	✗	Intel Virtualization Technology for Directed I/O (VT-d)	✓
Memory		Intel Trusted Execution Technology	✓
Internal memory *	8 GB	Intel VT-x with Extended Page Tables (EPT)	✓
Internal memory type *	DDR4-SDRAM	Intel TSX-NI	✓
ECC	✓	Intel Clear Video Technology	✓
Memory clock speed	2666 MHz	Intel Software Guard Extensions (Intel SGX)	✓
Memory layout (slots x size)	1 x 8 GB	Intel 64	✓
Storage		Intel Virtualization Technology (VT-x)	✓
Total storage capacity *	4 TB	Power	
Number of HDDs installed	2	Power supply *	250 W
HDD capacity	2 TB	Number of redundant power supplies installed	1
Graphics		Logistics data	
On-board graphics card	✓	Harmonized System (HS) code	84714100
On-board graphics card model	Intel UHD Graphics P630	Weight & dimensions	
Network		Width	175 mm
Ethernet LAN	✓	Depth	424 mm
Cabling technology	10/100/1000Base-T(X)		
Ports & interfaces			
Ethernet LAN (RJ-45) ports *	1		
USB 2.0 ports quantity	2		
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	4		

Ports & interfaces		Weight & dimensions	
Serial ports quantity	1	Height	376 mm
DisplayPorts quantity	2		



8032976146590

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.