



APC Smart-UPS On-Line, 1500VA, Rackmount 2U, 230V, 8x C13 IEC outlets, Network Card, W/ rail kit, Used W/O Lithium-ion external battery

Brand : APC

Product code: SRT1500UXI-NCLI



Product name : APC Smart-UPS On-Line, 1500VA, Rackmount 2U, 230V, 8x C13 IEC outlets, Network Card, W/ rail kit, Used W/O Lithium-ion external battery

APC Smart-UPS On-Line, 1500VA, Rackmount 2U, 230V, 8x C13 IEC outlets, Network Card, W/ rail kit, Used W/O Lithium-ion external battery


[APC Smart-UPS On-Line, 1500VA, Rackmount 2U, 230V, 8x C13 IEC outlets, Network Card, W/ rail kit, Used W/O Lithium-ion external battery:](#)

This APC Smart-UPS SRT1500UXI-NCLI is designed for IT professionals or network administrators to maintain business uptime and continuity. This 1500VA on-line 2U rackmount UPS provides pure sine wave power and extended runtime to support critical electronics during power disruptions. It comes with 1x IEC 320 C14 input and 8x IEC 320 C13 outlets. The UPS has a preinstalled Network Management Card for UPS network-based monitoring and management. The UPS comes with PowerChute Network Shutdown that provides graceful shutdown of physical servers, virtual machines, and HCI clusters. The UPS can connect to EcoStruxure IT or third-party centralized management platforms. The UPS has a 5-year warranty, and has to be used with an external Lithium-ion battery sold separately.

Features		Design	
UPS topology *	Double-conversion (Online)	Form factor *	Rackmount
Output power capacity *	1.5 kVA	Rack capacity	2U
Output power *	1350 W	Product colour *	Black
Waveform *	Sine	International Protection (IP) code	IP20
Input operation voltage (min) *	80 V	Operational conditions	
Input operation voltage (max) *	240 V	Operating temperature (T-T)	0 - 40 °C
Input frequency *	40 - 70 Hz	Storage temperature (T-T)	-15 - 45 °C
Output operation voltage (min)	220 V	Operating relative humidity (H-H)	0 - 95%
Output operation voltage (max)	240 V	Storage relative humidity (H-H)	0 - 95%
Output frequency	50/60 Hz	Operating altitude	0 - 3048 m
Surge energy rating	340 J	Non-operating altitude	0 - 15240 m
Heat dissipation	450 BTU/h	Certificates	
Crest factor	3:1	Certification	CE, CE Mark, EAC, RCM, UK PSTI, VDE
Output voltage Total Harmonic Distortion (THD)	2%	Weight & dimensions	
Noise level	50 dB	Width	432 mm
Ports & interfaces		Depth	590 mm
AC outlet types	C13 coupler, C14 coupler	Height	85 mm
AC outlets quantity	8 AC outlet(s)	Weight	17.5 kg
USB port	✓	Packaging data	
Serial ports quantity	1	Package width	810 mm
Ethernet LAN (RJ-45) ports	1	Package depth	600 mm
Emergency Power Off (EPO) connector	✓	Package height	245 mm
SmartSlot	✓	Package weight	28.2 kg
		Logistics data	
		Total carbon footprint (kg of CO2e)	2523.22



0731304338727



731304338727

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.