



REVISIONS	
NO.	DESCRIPTION/DATE



Impedance	75Ω
Frequency range	0 to 4GHz
Voltage rating	500 volts peak
Dielectric withstanding voltage	1500 volts rms
VSWR	M39012 straight connectors: 1, 3 max. 0-4GHz M39012 right angle: 1.95 max 0-4GHz
Other (MIL-C-39012 Cable Connectors)	Contact resistance: center contact 1.5 milliohm outer contact 0.2 milliohm Insertion loss: 0.2db max at 3.0GHz Insulation resistance: 5000 mΩ(min)

Recommended
Cable Stripping



1: Crimped Contact
Hex Crimp Size: .068"
2: Crimped Ferrule
Hex Crimp Size: .213"

5	Ferrule	Brass	Nickel
4	Shell	Brass	Nickel
3	Insulator	Telfon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

CUSTOMER OUTLINE DRAWING

Unless Otherwise Specified Tolerances
Dimensions Are In Millimeters
And For Customer Reference Only

0.5-6±/-0.2
6-30±/-0.4
30-120±/-0.6
120-315±/-1.0




RF/Microwave Connectors Professional Manufacture Copy Right Reserved

Best No. 730439

Part: B-010-58-75-TGN

Title: BNC PLUG R/A CRIMP FOR RG/58U CABLE 75Ω T.G.N.

Date: Jun/10/2009



Scale: 2.5:1

Unit: M/M

Rev: A