


Electrical	
Impedance	50 Ω
Frequency range	DC-4GHz
VSWR	≤ 1.2 typ
Test voltage	1500 volts rms
Working voltage	400 V rms
Voltage rating	500 volts peak
Power handling	≤ 80 W (2GHz)
Other (MIL-C-39012 Cable Connectors)	Contact resistance: center contact ≤ 1.5 m Ω outer contact ≤ 1 m Ω Insertion loss: $\leq 0.1x \sqrt{f(\text{GHz})}$ dB Insulation resistance: ≥ 5000 m Ω
Material	
Mating cycles	≥ 500
Center contact captivation	Axial: ≥ 27 N
Environmental	
Temperature range	-55 $^{\circ}$ C + 85 $^{\circ}$ C
Thermal shock	US MIL-STD 202, Meth, 107, Cond, B
Vibration	US MIL-STD 202, Meth, 204, Cond, B
Climatic class	IEC 60068 65/165/21
Shock	US MIL-STD 202, Meth, 213, Cond, B
Corrosion resistance	US MIL-STD 202, Meth, 101, Cond, B
Degree of protection (mated pair)	IEC 60529

NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER JIS-C3604
2. PH/BRONZE PER ASTM B196 UNS C17300
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 μ " THICK OVER COPPER STRIKE
6. GOLD PL 1-3 μ " OVER NICKEL PL 70 μ " THICK OVER COPPER STRIKE



3	Insulator	Delrin	White
2	Contact	PH/Bronze (P)	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

Artikelnummer

Artikeltext

730464

Adapter, TNC-Kupplung auf TNC-Kupplung, 50 Ohm