







Impedance	50 Ω
Frequency range	0-6 GHz
Voltage rating	1500 volts peak
Dielectric withstanding voltage	2500 volts rms
VSWR	M39012 straight connectors: 1.3 max. 0-11GHz M39012 right angle: 1.35 max. 0-11GHz
othr (MIL-C-39012 cable connectors)	Contact resistance: center contact 1.0 milliohm outer contact 0.2 milliohm Insertion loss: 0.15db max at 10.0GHz Insulation resistance: 5000 megohms(min)

NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER JIS-C3604
2. TEFLON PER ASTM D1457 AND ASTM D1710
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 μ " THICK OVER COPPER STRIKE
6. GOLD PL 1-3 μ " OVER NICKEL PL 70 μ " THICK OVER COPPER STRIKE



- Recommended Cable Stripping
- 1: CRIMPED PIN
HEX CRIMP SIZE: 2.54mm(.100")
 - 2: CRIMPED FERRULE
HEX CRIMP SIZE: 6.50mm(.256")
HEX CRIMP SIZE: 5.41mm(.213")

4	Ferrule	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

Artikelnummer Artikeltext

730476

N-Reverse, Kupplung 50 Ohm, Crimpausf., Teflon-Isolation, Belden H 155

BKL - ELECTRONIC Kreimendahl GmbH ~ Märkenstück 14 ~ 58509 Lüdenscheld

Telefon +49(0)2351/3621-0 ~ Telefax +49(0)02351/3621-29 ~ E-Mail: info@bkl-electronic.de ~ www.bkl-electronic.de