



APC GVSUPS15KB4HS uninterruptible power supply (UPS) Double-conversion (Online) 15 kVA 15000 W

Brand : APC

Product code: GVSUPS15KB4HS

Product name : GVSUPS15KB4HS

15 kVA, 15 kW, 40/70Hz, 55 dB, 521x847x1485mm, 330kg

APC GVSUPS15KB4HS uninterruptible power supply (UPS) Double-conversion (Online) 15 kVA 15000 W:


GVSUPS15KB4HS Features

- Galaxy VS UPS 15kW 400V, 1 internal 9Ah smart modular battery string, expandable to 4, Start-up 5x8
- Highly efficient, easy-to-deploy 15kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and 1 smart high-capacity modular battery string, expandable to 4 strings for extended runtime. Runtime charts available in the Documents tab.
- Includes: Battery modules ship installed, Dust filter, EcoStruxure Ready ((UPS)), Installation guide, Integrated network management, Power modules ship installed, Start-Up Service



Features		Design	
UPS topology *	Double-conversion (Online)	Form factor *	Tower
Output power capacity *	15 kVA	Product colour *	White
Output power *	15000 W	Display type	LCD
Waveform *	Sine	International Protection (IP) code	IP20
Input operation voltage (min) *	340 V	Operational conditions	
Input operation voltage (max) *	460 V	Operating temperature (T-T)	0 - 40 °C
Input frequency *	40/70 Hz	Storage temperature (T-T)	-15 - 40 °C
Output operation voltage (min)	380 V	Operating relative humidity (H-H)	0 - 95%
Output operation voltage (max)	415 V	Storage relative humidity (H-H)	0 - 95%
Output frequency	50/60 Hz	Operating altitude	0 - 1000 m
Maximum current	27 A	Non-operating altitude	0 - 3000 m
Number of input phases	3	Certificates	
Number of output phases	3	Certification	CSA C22.2 NO. 107.3, EN/IEC 62040-1, EN/IEC 62040-2, EN/IEC 62040-3, IEC 60721-4-2 Level 2M2, UL 1778 5th edition
Input power factor	0.99		
Crest factor	2.5:1	Packaging content	
ECO mode	✓	Management card included	✓
Output voltage Total Harmonic Distortion (THD)	3%	Quick installation guide	✓
Input current Total Harmonic Distortion (THD)	3%	Weight & dimensions	
Noise level	55 dB	Width	521 mm
Power protection features	Overload, Short circuit	Depth	847 mm
Audible alarm(s)	✓	Height	1485 mm

Ports & interfaces		Weight & dimensions	
AC outlet types	Hard Wire 3-wire (1PH + N + G), Hard Wire 4-wire (3PH + G)	Weight	330 kg
SmartSlot	✓	Packaging data	
SmartConnect port	✗	Package width	640 mm
Battery		Package depth	990 mm
Battery technology	Sealed Lead Acid (VRLA)	Package height	1680 mm
Battery voltage	480 V	Package weight	360 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0731304406747



731304406747



5054444446103



5705154232783

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.