



APC NetShelter Rack PDU Advanced, Metered, 3Phase, 43.5kW 400V 63A or 34.6kW 415V 60A, 42 Outlets, IEC309

Brand : APC


Product code: APDU10450ME

Product name : NetShelter Rack PDU Advanced, Metered, 3Phase, 43.5kW 400V 63A or 34.6kW 415V 60A, 42 Outlets, IEC309

- Maximum Outlet Density All models include 40, 42, or 48 outlets
 - Space Saving
 - High Power Capacity Models now available to provide up to 34.6kW
 - APC Locking Power Cord Compatible Optional AP8700 power cords will fit into any standard IEC receptacle or power inlet
 - Circuit Breaker Monitoring
 - Alternating Phase
 - 60°C (140°F) Operating Temperature
 - Rack PDUs cascaded together via the two ethernet ports on each PDU allow Network Management Cards (NMC) to continue functioning in the event of an AC power loss to a given PDU
 - Hydraulic Magnetic Circuit Breakers
 - Live Swap Network Management Card
 - Environmental Sensor Support
 - Color LCD Display
 - Dual Network Ports
- NetShelter Rack PDU Advanced, Metered, 3Phase, 43.5kW 400V 63A or 34.6kW 415V 60A, 42 Outlets, IEC309



Design		Certificates	
PDU types *	Switched	Certification	CSA C22.2 No 62368-1, FCC part 15 subpart B, UL 62368-1
Type	Single-phase	Operational conditions	
Rack capacity *	0U		
Mounting	Vertical	Operating temperature (T-T)	-5 - 60 °C
Product colour	Black	Storage temperature (T-T)	-25 - 65 °C
Display	LCD	Operating relative humidity (H-H)	5 - 95%
On/off switch	✗	Storage relative humidity (H-H)	5 - 95%
Ports & interfaces		Operating altitude	0 - 3048 m
AC outlets quantity *	48 AC outlet(s)	Non-operating altitude	0 - 15240 m
Power plug	IEC 60309	Weight & dimensions	
AC outlet types *	C13 coupler, C15 coupler, C19 coupler, C21 coupler	Width	56 mm
Features		Depth	75 mm
Daisy chain	✓	Height	1826 mm
Power		Weight	11.7 kg
Nominal input voltage *	415 V	Packaging data	
AC input frequency	50 - 60 Hz	Package weight	14.7 kg
Maximum current *	60 A	Package width	262 mm
Nominal output voltage	240 V	Package depth	132 mm
Output voltage	240 V	Package height	1980 mm
Load capacity	34600 VA	Logistics data	
Maximum input current per phase	60 A	Total carbon footprint (kg of CO2e)	21687.02
Maximum total current draw per phase	48 A		



0731304439103



731304439103

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.