



HP Scanjet Pro 3600 f1 Flatbed & ADF scanner 1200 x 1200 DPI A4 White

Brand : HP

Product family: Scanjet

Product code: 20G06A#B19

Product name : Scanjet Pro 3600 f1



Scanjet Pro 3600 f1 Flatbed Scanner with HP EveryPage technology.

[HP Scanjet Pro 3600 f1 Flatbed & ADF scanner 1200 x 1200 DPI A4 White:](#)

Enhance productivity with reliable and fast, two-sided scanning, a 60-page ADF, and one-button shortcuts.

Boost productivity for professional scanning tasks with the fast, compact, and reliable HP Scanjet Pro, designed for scanning up-to 3,000-pages daily. Automate workflows with one-click shortcuts and fast, two-sided scanning from the auto document feeder.


HP Scanjet Pro 3600 f1. Maximum scan size: 216 x 297 mm, Optical scanning resolution: 1200 x 1200 DPI, ADF scan speed (b/w, A4): 30 ppm. Scanner type: Flatbed & ADF scanner, Product colour: White. Sensor type: CIS, Daily duty cycle (max): 3000 pages, Scan file formats: BMP, CSV, DOC, DOCX, JPEG, PDF, PNG, RTF, TIFF, TXT, XLS, XLSX. Maximum ISO A-series paper size: A4, Scanning media types supported: Card stock, Envelopes, Labels, Photo paper, Plain paper, ISO A-series sizes (A0...A9): A4, A5, A6. USB version: 3.2 Gen 1 (3.1 Gen 1)

Scanning		Power	
Maximum scan size *	216 x 297 mm	Power supply type *	AC
Optical scanning resolution *	1200 x 1200 DPI	Power consumption (typical)	13.31 W
Colour scanning	✓	Power consumption (standby)	5.31 W
Duplex scanning *	✓	Power consumption (off)	0.07 W
Greyscale levels	256	Sleep mode	✓
ADF scan speed (b/w, A4)	30 ppm	Input voltage	100 - 240 V
ADF scan speed (greyscale, A4)	30 ppm		
ADF scan speed (colour, A4)	30 ppm		
Design		Weight & dimensions	
Scanner type *	Flatbed & ADF scanner	Width	491.5 mm
Product colour *	White	Depth	422.3 mm
Built-in display *	✗	Height	387.4 mm
		Weight	5.4 kg
Performance		Packaging data	
Sensor type *	CIS	Package width	600 mm
Scan file formats	BMP, CSV, DOC, DOCX, JPEG, PDF, PNG, RTF, TIFF, TXT, XLS, XLSX	Package depth	245 mm
Daily duty cycle (max) *	3000 pages	Package height	499 mm
Scan to	E-mail, PC	Package weight	7.3 kg
Scan drivers	TWAIN		
Internal memory	256 MB		
Built-in processor	✓		
Processor frequency	666 MHz		
HP segment	Business, Home, Home office		
Paper handling		Packaging content	
Scanning media types supported	Card stock, Envelopes, Labels, Photo paper, Plain paper	Cables included	USB
Maximum ISO A-series paper size *	A4		
ISO A-series sizes (A0...A9)	A4, A5, A6		
ISO B-series sizes (B0...B9)	B5		
Auto Document Feeder (ADF) media weight	49 - 120 g/m ²		
Maximum scan area (ADF)	216 x 3100 mm		
Minimum scan area (ADF)	89 x 148 mm		
		System requirements	
		Windows operating systems supported	Windows 10, Windows 11, Windows 7, Windows 8.1
		Mac operating systems supported	Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 11.0 Big Sur
		Server operating systems supported	Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Server 2019
		Operational conditions	
		Operating temperature (T-T)	10 - 35 °C
		Storage temperature (T-T)	-40 - 60 °C
		Operating relative humidity (H-H)	15 - 80%
		Storage relative humidity (H-H)	0 - 90%

Ports & interfaces		Other features	
USB port *	✓	Scan speed (ADF, A4)	30 ppm
USB version	3.2 Gen 1 (3.1 Gen 1)	Logistics data	
		Country of origin	China, Taiwan
		Harmonized System (HS) code	84716070



0195697674020



195697674020

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date