



SPECIFICATIONS

Current Rating: 3.0 Amp

Dielectric Withstand: 1000V AC

Insulator Resistance: 1000 MΩ min.

Contact Resistance: 20mΩ Max.

Operating Temperature: -55°c to + 105°c

MATERIALS

Insulator: P.B.T30%GF, UL94V-0
Nylon-6T

Contacts: Copper Alloy

All materials must be RoHS compliant.

Datenblatt passend zu folgenden Artikelnummern

10120406