



BenQ LU9800 Standard throw projector 10000 ANSI lumens DLP WUXGA (1920x1200) 3D Black

Brand : BenQ

Product code: 9H.JPM77.25E

Product name : LU9800

- Compatible with 9 electrical optional lenses to maximize throw ratio coverage
- Support BenQ factory white balance calibration
- Up to 70,000 hrs laser light source life under Dimming Mode
- 3000000:1 high contrast ratio

DLP, 10000 ANSI Lumen, WUXGA (1920x1200), 3000000:1, 16:10, 500 x 211 x 587.3 mm

BenQ LU9800. Projector brightness: 10000 ANSI lumens, Projection technology: DLP, Projector native resolution: WUXGA (1920x1200). Light source type: Laser, Service life of light source: 20000 h, Service life of light source (economic mode): 38000 h. Horizontal lens shift range: -5 - 5%, Vertical lens shift range: -15 - 55%. Serial interface type: RS-232, HDMI connector type: Full-size. Noise level: 42 dB, Noise level (economic mode): 38 dB



Projector		Network	
Screen size compatibility *	1270 - 12700 mm (50 - 500")	Smart TV *	✗
Projector brightness *	10000 ANSI lumens	Ethernet LAN *	✓
Projection technology *	DLP	Ethernet LAN (RJ-45) ports	1
Projector native resolution *	WUXGA (1920x1200)	Wi-Fi *	✗
Contrast ratio (typical) *	3000000:1	Storage	
Native aspect ratio *	16:10	Card reader integrated *	✗
Number of colours	1.07 billion colours	Features	
Horizontal scan range	15 - 135 kHz	Interactive *	✗
Vertical scan range	23 - 120 Hz	Noise level (economic mode)	38 dB
Keystone correction, horizontal	-30 - 30°	On Screen Display (OSD)	✓
Keystone correction, vertical	-30 - 30°	Number of OSD languages	12
Matrix size	1.7 cm (0.67")	Noise level *	42 dB
Matrix type	DMD	Design	
Light source		Market positioning *	Business
Light source type *	Laser	Product type *	Standard throw projector
Service life of light source *	20000 h	Product colour *	Black
Service life of light source (economic mode)	38000 h	Display	
Lens system		Built-in display *	✗
Horizontal lens shift range	-5 - 5%	Power	
Vertical lens shift range	-15 - 55%	Power source *	AC
Number of optional lenses supported	9	Power consumption (typical) *	792 W
Video		Power consumption (standby) *	0.5 W
Full HD *	✓	Power consumption (max)	885 W
3D *	✓	AC input voltage	100 - 240 V
		AC input frequency	50 - 60 Hz

Ports & interfaces		Operational conditions	
HDMI connector type	Full-size	Operating temperature (T-T)	0 - 45 °C
HDMI version	2.0	Weight & dimensions	
HDBaseT port	✓	Width	500 mm
USB 2.0 ports quantity	2	Depth	587.3 mm
Audio (L/R) in *	1	Height	211 mm
Serial interface type *	RS-232	Weight *	26.8 kg
PC Audio out	✓	Packaging content	
PC in (D-Sub)	✓	Remote control included *	✓
VGA (D-Sub) ports quantity *	1	Remote control type	Wireless/Wired
HDMI ports quantity *	2	Batteries included	✗
BNC input ports	1	Cables included	AC
DVI port *	✓	Manual	✓
		Logistics data	
		Quantity per pack	1 pc(s)
		Other features	
		Security updates end date	31/12/2024



4718755087318



0840046046293



840046046293

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.