

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Kunststoff-Tiefenpflege 500ML
Art.: 1536

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture:

Care product for plastic surfaces

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH, Jerg-Wieland-Straße 4, D-89081 Ulm-Lehr
Telephone (+49) 0731-1420-0, Fax (+49) 0731-1420-88

E-mail address of the competent person: info@chemical-check.de, k.schnurbusch@chemical-check.de

1.4 Emergency telephone

Advisory office in case of poisoning:

Telephone number of the company in case of emergencies:

Tel.: (+49) 0731-1420-0

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) 1272/2008 (CLP)

Not determined

2.1.2 Classification according to Directives 67/548/EEC and 1999/45/EC (including amendments)

The mixture is not classified as dangerous in the terms of the directive 1999/45/EC.

2.2 Label elements

2.2.1 Labeling according to Regulation (EC) 1272/2008 (CLP)

Not determined

2.2.2 Labeling according to Directives 67/548/EEC and 1999/45/EC (including amendments)

Symbols: Not applicable

Indications of danger: ---

R-phrases:

S-phrases:

Additions:

Safety data sheet available for professional user on request.

2.3 Other hazards

Page 2 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 06.07.2012 / 0006
 Replaces revision of / Version: 19.01.2011 / 0005
 Valid from: 06.07.2012
 PDF print date: 06.07.2012
 Kunststoff-Tiefenpflege 500ML Art.: 1536

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

REGULATION (EC) No 648/2004

less than 5 %
 anionic surfactants

perfumes
 BENZISOTHIAZOLINONE
 METHYLISOTHIAZOLINONE

SECTION 3: Composition/information on ingredients

3.1 Substance

n.a.

3.2 Mixture

Poly[3-((2-aminoethyl)amino)propyl]methyl(dimethyl)siloxane, methoxy-terminated	
Registration number (REACH)	--
Index	---
EINECS, ELINCS, NLP	-
CAS	CAS 102782-92-3
content %	1-5
Classification according to Directive 67/548/EEC	Irritant, Xi, R36/38
Classification according to Regulation (EC) 1272/2008 (CLP)	Skin Irrit. 2, H315 Eye Irrit. 2, H319

For the text of the R-phrases / H-phrases and classification codes (GHS/CLP), see Section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

Inhalation

Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Wash thoroughly using copious water - remove contaminated clothing immediately. If skin irritation occurs (redness etc.), consult doctor.

Unsuitable cleaning product:

Solvent

Thinners

Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.

Give copious water to drink. Consult doctor if necessary.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

4.3 Indication of any immediate medical attention and special treatment needed

n.c.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Page 3 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revised on / Version: 06.07.2012 / 0006
Replaces revision of / Version: 19.01.2011 / 0005
Valid from: 06.07.2012
PDF print date: 06.07.2012
Kunststoff-Tiefenpflege 500ML Art.: 1536

Water jet spray / alcohol resistant foam / CO₂ / dry extinguisher

Unsuitable extinguishing media

None known

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Oxides of carbon
Oxides of sulphur
Oxides of nitrogen
Toxic gases

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.
Protective respirator with independent air supply.
According to size of fire
Full protection, if necessary
Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Ensure sufficient supply of air.
Avoid contact with eyes or skin.
If applicable, caution - risk of slipping

6.2 Environmental precautions

If leakage occurs, dam up.
Prevent surface and ground-water infiltration, as well as ground penetration.
Prevent from entering drainage system.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.
Flush residue using copious water.

Unsuitable cleaning product:

Solvent
Thinners

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Avoid contact with eyes.
Avoid long lasting or intensive contact with skin.
Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.
Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.
Wash hands before breaks and at end of work.
Keep away from food, drink and animal feedingstuffs.
Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Store product closed and only in original packing.
Not to be stored in gangways or stair wells.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 06.07.2012 / 0006
 Replaces revision of / Version: 19.01.2011 / 0005
 Valid from: 06.07.2012
 PDF print date: 06.07.2012
 Kunststoff-Tiefenpflege 500ML Art.: 1536

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.
 If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.
 Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.
 Wash hands before breaks and at end of work.
 Keep away from food, drink and animal feedingstuffs.
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:
 Tight fitting protective goggles (EN 166) with side protection, with danger of projections.

Skin protection - Hand protection:
 Rubber gloves (EN 374).
 Protective PVC gloves (EN 374)
 Protective hand cream recommended.

Skin protection - Other:
 Usual protective working garments

Respiratory protection:
 Normally not necessary.

Thermal hazards:
 Not applicable

Additional information on hand protection - No tests have been performed.
 In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.
 Selection of materials derived from glove manufacturer's indications.
 Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.
 Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.
 In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.
 The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	White
Odour:	Characteristic
Odour threshold:	Not determined
pH-value:	5-7 (20°C)
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	100 °C
Flash point:	n.a.
Evaporation rate:	Not determined
Flammability (solid, gas):	Not determined
Lower explosive limit:	Not determined
Upper explosive limit:	Not determined
Vapour pressure:	23 hPa (20°C)
Vapour density (air = 1):	Not determined

Page 5 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 06.07.2012 / 0006
 Replaces revision of / Version: 19.01.2011 / 0005
 Valid from: 06.07.2012
 PDF print date: 06.07.2012
 Kunststoff-Tiefenpflege 500ML Art.: 1536

Density:	1 g/cm ³ (20°C)
Bulk density:	n.a.
Solubility(ies):	Not determined
Water solubility:	Mixable
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	Ignition temperature n.a.
Decomposition temperature:	Not determined
Viscosity:	Not determined
Explosive properties:	Product is not explosive.
Oxidising properties:	Not determined

9.2 Other information

Miscibility:	Not determined
Fat solubility / solvent:	Not determined
Conductivity:	Not determined
Surface tension:	Not determined
Solvents content:	0 %

SECTION 10: Stability and reactivity

10.1 Reactivity

Not to be expected

10.2 Chemical stability

Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

See also section 7.

None known

10.5 Incompatible materials

See also section 7.

None known

10.6 Hazardous decomposition products

See also section 5.2

No decomposition when used as directed.

SECTION 11: Toxicological information

Possibly more information on health effects, see Section 2.1 (classification).

Kunststoff-Tiefenpflege 500ML

Art.: 1536

Toxicity/effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:						n.d.a.
Acute toxicity, by dermal route:						n.d.a.
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin sensitisation:						n.d.a.
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity - single exposure (STOT-SE):						n.d.a.
Specific target organ toxicity - repeated exposure (STOT-RE):						n.d.a.
Aspiration hazard:						n.d.a.
Respiratory tract irritation:						n.d.a.
Repeated dose toxicity:						n.d.a.
Symptoms:						n.d.a.

Page 6 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 06.07.2012 / 0006
 Replaces revision of / Version: 19.01.2011 / 0005
 Valid from: 06.07.2012
 PDF print date: 06.07.2012
 Kunststoff-Tiefenpflege 500ML Art.: 1536

Other information:						Classification according to calculation procedure.
--------------------	--	--	--	--	--	--

SECTION 12: Ecological information

Possibly more information on environmental effects, see Section 2.1 (classification).

Kunststoff-Tiefenpflege 500ML Art.: 1536

Toxicity/effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
Toxicity to fish:							n.d.a.
Toxicity to daphnia:							n.d.a.
Toxicity to algae:							n.d.a.
Persistence and degradability:							The surfactant(s) contained in this mixture complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents., Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
Bioaccumulative potential:							n.d.a.
Mobility in soil:							n.d.a.
Results of PBT and vPvB assessment							n.d.a.
Other adverse effects:							n.d.a.
Other information:							According to the recipe, contains no AOX.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2001/118/EC, 2001/119/EC, 2001/573/EC)

20 01 30 detergents other than those mentioned in 20 01 29

Recommendation:

Pay attention to local and national official regulations

E.g. suitable incineration plant.

E.g. dispose at suitable refuse site.

For contaminated packing material

Pay attention to local and national official regulations

Empty container completely.

Untamminated packaging can be recycled.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

Recommended cleaner:

Water

15 01 02 plastic packaging

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 06.07.2012 / 0006
 Replaces revision of / Version: 19.01.2011 / 0005
 Valid from: 06.07.2012
 PDF print date: 06.07.2012
 Kunststoff-Tiefenpflege 500ML Art.: 1536

SECTION 14: Transport information

General statements

UN number: n.a.

Transport by road/by rail (ADR/RID)

UN proper shipping name: n.a.
 Transport hazard class(es): n.a.
 Packing group: n.a.
 Classification code: n.a.
 LQ (ADR 2011): n.a.
 LQ (ADR 2009): n.a.
 Environmental hazards: Not applicable
 Tunnel restriction code:

Transport by sea (IMDG-code)

UN proper shipping name:
 Transport hazard class(es): n.a.
 Packing group: n.a.
 Marine Pollutant: n.a.
 Environmental hazards: Not applicable

Transport by air (IATA)

UN proper shipping name:
 Transport hazard class(es): n.a.
 Packing group: n.a.
 Environmental hazards: Not applicable

Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

For classification and labelling see Section 2.

Observe restrictions: n.a.

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

These details refer to the product as it is delivered.

Revised sections: 1-16

The following statements are the indicated R-phrases / H-phrases and classification codes (GHS/CLP) for the ingredients (listed in Section 3).

36/38 Irritating to eyes and skin.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

Skin Irrit.-Skin irritation

Eye Irrit.-Eye irritation

Any abbreviations and acronyms used in this document:

AC Article Categories

acc., acc. to according, according to

ACGIH American Conference of Governmental Industrial Hygienists

ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)

AOEL Acceptable Operator Exposure Level

AOX Adsorbable organic halogen compounds
 approx. approximately
 Art., Art. no. Article number
 ATE Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)
 BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)
 BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
 BCF Bioconcentration factor
 BGV Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)
 BHT Butylhydroxytoluol (= 2,6-Di-t-butyl-4-methyl-phenol)
 BMGV Biological monitoring guidance value (EH40, UK)
 BOD Biochemical oxygen demand
 BSEF Bromine Science and Environmental Forum
 bw body weight
 CAS Chemical Abstracts Service
 CESIO Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques
 CIPAC Collaborative International Pesticides Analytical Council
 CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
 CMR carcinogenic, mutagenic, reproductive toxic
 COD Chemical oxygen demand
 CTFA Cosmetic, Toiletry, and Fragrance Association
 DMEL Derived Minimum Effect Level
 DNEL Derived No Effect Level
 DOC Dissolved organic carbon
 DT50 Dwell Time - 50% reduction of start concentration
 DVS Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)
 dw dry weight
 e.g. for example (abbreviation of Latin 'exempli gratia'), for instance
 EC European Community
 ECHA European Chemicals Agency
 EEA European Economic Area
 EEC European Economic Community
 EINECS European Inventory of Existing Commercial Chemical Substances
 ELINCS European List of Notified Chemical Substances
 EN European Norms
 EPA United States Environmental Protection Agency (United States of America)
 ERC Environmental Release Categories
 ES Exposure scenario
 etc. et cetera
 EU European Union
 EWC European Waste Catalogue
 Fax. Fax number
 gen. general
 GHS Globally Harmonized System of Classification and Labelling of Chemicals
 GWP Global warming potential
 HET-CAM Hen's Egg Test - Chorionallantoic Membrane
 HGWP Halocarbon Global Warming Potential
 IARC International Agency for Research on Cancer
 IATA International Air Transport Association
 IBC Intermediate Bulk Container
 IBC (Code) International Bulk Chemical (Code)
 IC Inhibitory concentration
 IMDG-code International Maritime Code for Dangerous Goods
 incl. including, inclusive
 IUCLID International Uniform Chemical Information Database
 LC lethal concentration
 LC50 lethal concentration 50 percent kill
 LCLo lowest published lethal concentration
 LD Lethal Dose of a chemical
 LD50 Lethal Dose, 50% kill
 LDLo Lethal Dose Low
 LOAEL Lowest Observed Adverse Effect Level
 LOEC Lowest Observed Effect Concentration
 LOEL Lowest Observed Effect Level

Page 9 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revised on / Version: 06.07.2012 / 0006
Replaces revision of / Version: 19.01.2011 / 0005
Valid from: 06.07.2012
PDF print date: 06.07.2012
Kunststoff-Tiefenpflege 500ML Art.: 1536

LQ Limited Quantities
MARPOL International Convention for the Prevention of Marine Pollution from Ships
n.a. not applicable
n.av. not available
n.c. not checked
n.d.a. no data available
NIOSH National Institute of Occupational Safety and Health (United States of America)
NOAEC No Observed Adverse Effective Concentration
NOAEL No Observed Adverse Effect Level
NOEC No Observed Effect Concentration
NOEL No Observed Effect Level
ODP Ozone Depletion Potential
OECD Organisation for Economic Co-operation and Development
org. organic
PAH polycyclic aromatic hydrocarbon
PBT persistent, bioaccumulative and toxic
PC Chemical product category
PE Polyethylene
PNEC Predicted No Effect Concentration
POCP Photochemical ozone creation potential
ppm parts per million
PROC Process category
PTFE Polytetrafluorethylene
REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)
REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)
SADT Self-Accelerating Decomposition Temperature
SAR Structure Activity Relationship
SU Sector of use
SVHC Substances of Very High Concern
Tel. Telephone
ThOD Theoretical oxygen demand
TOC Total organic carbon
TRGS Technische Regeln für Gefahrstoffe (= Technical Regulations for Hazardous Substances)
VbF Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))
VOC Volatile organic compounds
vPvB very persistent and very bioaccumulative
WEL-TWA, WEL-STEL WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).
WHO World Health Organization
wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.
No responsibility.

These statements were made by:

Chemical Check GmbH, Wöbbeler Straße 2-4, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.