

Page 1 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005

Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012

PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

# Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

## Kunststoff "Wie Neu" (schwarz) 250ML

Art.: 1552

## 1.2 Relevant identified uses of the substance or mixture and uses advised against Relevant identified uses of the substance or mixture:

Care product for plastic surfaces

Sector of use [SU]:

SU 3 - Industrial uses: Uses of substances as such or in preparations at industrial sites

SU21 - Consumer uses: Private households (=general public = consumers)

SU22 - Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

Chemical product category [PC]:

PC31 - Polishes and wax blends

PC35 - Washing and cleaning products (including solvent based products)

Process category [PROC]:

PROC 8a - Transfer of substance or preparation (charging/discharging) from/to vessels/large containers at non-dedicated facilities

PROC 8b - Transfer of substance or preparation (charging/discharging) from/to vessels/large containers at dedicated facilities

PROC 9 - Transfer of substance or preparation into small containers (dedicated filling line, including weighing)

PROC10 - Roller application or brushing

PROC19 - Hand-mixing with intimate contact and only PPE available

Article Categories [AC]:

AC99 - Not required.

Environmental Release Category [ERC]:

ERC 4 - Industrial use of processing aids in processes and products, not becoming part of articles

ERC 7 - Industrial use of substances in closed systems

ERC 8a - Wide dispersive indoor use of processing aids in open systems

ERC 8d - Wide dispersive outdoor use of processing aids in open systems

#### Uses advised against:

No information available at present.

## 1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH, Jerg-Wieland-Straße 4, D-89081 Ulm-Lehr Telephone (+49) 0731-1420-0, Fax (+49) 0731-1420-88

E-mail address of the competent person: info@chemical-check.de, k.schnurbusch@chemical-check.de

## 1.4 Emergency telephone

## Emergency information services / official advisory body:

#### Telephone number of the company in case of emergencies:

Tel.: (+49) 0731-1420-0

#### **SECTION 2: Hazards identification**

#### 2.1 Classification of the substance or mixture

#### 2.1.1 Classification according to Regulation (EC) 1272/2008 (CLP)

Not determined

#### 2.1.2 Classification according to Directives 67/548/EEC and 1999/45/EC (including amendments)

The mixture is not classified as dangerous in the terms of the directive 1999/45/EC.



Page 2 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005 Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012 PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

#### 2.2 Label elements

#### 2.2.1 Labeling according to Regulation (EC) 1272/2008 (CLP)

Not determined

#### 2.2.2 Labeling according to Directives 67/548/EEC and 1999/45/EC (including amendments)

Symbols: Not applicable Indications of danger:

R-phrases:

S-phrases:

Additions:

Safety data sheet available for professional user on request.

#### 2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

## **SECTION 3: Composition/information on ingredients**

#### 3.1 Substance

## n.a. 3.2 Mixture

Poly[3-((2-aminoethyl)amino)propyl]methyl(dimethyl)siloxane, methoxy- terminated	
Registration number (REACH)	
Index	
EINECS, ELINCS, NLP	-
CAS	CAS 102782-92-3
content %	1-5
Classification according to Directive 67/548/EEC	Irritant, Xi, R36/38
Classification according to Regulation (EC) 1272/2008 (CLP)	Skin Irrit. 2, H315
	Eye Irrit. 2, H319

For the text of the R-phrases / H-phrases and classification codes (GHS/CLP), see Section 16.

#### **SECTION 4: First aid measures**

#### 4.1 Description of first aid measures

#### Inhalation

Supply person with fresh air and consult doctor according to symptoms.

#### Skin contact

Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

#### Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

#### Ingestion

Rinse the mouth thoroughly with water.

Give copious water to drink - consult doctor immediately.

#### 4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.



Œ

Page 3 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005 Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012 PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

## 4.3 Indication of any immediate medical attention and special treatment needed

n c

#### **SECTION 5: Firefighting measures**

## 5.1 Extinguishing media Suitable extinguishing media

Cool container at risk with water. Adapt to the nature and extent of fire. Water jet spray/foam/CO2/dry extinguisher

### Unsuitable extinguishing media

High volume water jet

#### 5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop: Oxides of carbon

Silicon dioxide Toxic gases

#### 5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.

Protective respirator with independent air supply.

Dispose of contaminated extinction water according to official regulations.

#### **SECTION 6: Accidental release measures**

#### 6.1 Personal precautions, protective equipment and emergency procedures

Ensure sufficient supply of air.

Avoid contact with eyes or skin.

If applicable, caution - risk of slipping

#### 6.2 Environmental precautions

If leakage occurs, dam up.

Prevent from entering drainage system.

Prevent surface and ground-water infiltration, as well as ground penetration.

#### 6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.

#### 6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

#### **SECTION 7: Handling and storage**

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

#### 7.1 Precautions for safe handling

#### 7.1.1 General recommendations

Ensure good ventilation.

Avoid contact with eyes.

Avoid long lasting or intensive contact with skin.

Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.

Observe directions on label and instructions for use.

#### 7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

#### 7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.

Store product closed and only in original packing.

Protect from direct sunlight and warming.

Protect from frost.



Œ

Page 4 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005 Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012 PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

#### 7.3 Specific end use(s)

No information available at present.

#### **SECTION 8: Exposure controls/personal protection**

#### 8.1 Control parameters

---

#### 8.2 Exposure controls

#### 8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.

If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn. Applies only if maximum permissible exposure values are listed here.

## 8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:

Tight fitting protective goggles (EN 166) with side protection, with danger of projections.

Skin protection - Hand protection:

Normally not necessary.

With long-term contact:

Chemical resistant protective gloves (EN 374).

If applicable

Rubber gloves (EN 374).

Protective PVC gloves (EN 374)

Protective hand cream recommended.

Skin protection - Other:

Usual protective working garments

Respiratory protection:

Normally not necessary.

Thermal hazards:

Not applicable

Additional information on hand protection - No tests have been performed.

In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents. Selection of materials derived from glove manufacturer's indications.

Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.

Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.

The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

#### 8.2.3 Environmental exposure controls

No information available at present.

## **SECTION 9: Physical and chemical properties**

#### 9.1 Information on basic physical and chemical properties

Physical state:

Colour:

Not determined
Black



Page 5 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005

Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012

PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

Characteristic Odour threshold: Not determined pH-value: 8 (20°C) Melting point/freezing point: Not determined

Initial boiling point and boiling range: 100 °C Flash point: n.a.

Evaporation rate: Not determined

Flammability (solid, gas): n.a.

Lower explosive limit: Not determined Upper explosive limit: Not determined Vapour pressure: 23 hPa (23°C) Vapour density (air = 1): Not determined 1 g/cm3 (20°C) Density: Bulk density: n.a.

Solubility(ies): Not determined Water solubility: Mixable

Partition coefficient (n-octanol/water): Not determined

Auto-ignition temperature: No

Decomposition temperature: Not determined Viscosity: 35-50 mPas

Product is not explosive. Explosive properties:

Oxidising properties:

9.2 Other information

Miscibility: Not determined Fat solubility / solvent: Not determined Conductivity: Not determined Surface tension: Not determined

Solvents content: 0 %

## **SECTION 10: Stability and reactivity**

#### 10.1 Reactivity

Not to be expected

#### 10.2 Chemical stability

Stable with proper storage and handling.

### 10.3 Possibility of hazardous reactions

No dangerous reactions are known.

#### 10.4 Conditions to avoid

See also section 7.

None known

#### 10.5 Incompatible materials

See also section 7.

None known

#### 10.6 Hazardous decomposition products

See also section 5.2

No decomposition when used as directed.

## **SECTION 11: Toxicological information**

Possibly more information on health effects, see Section 2.1 (classification).

Kunststoff "Wie Neu" (schwarz) 250ML							
Art.: 1552							
Toxicity/effect	Endpoin	Value	Unit	Organism	Test method	Notes	
	t						
Acute toxicity, by oral route:						n.d.a.	
Acute toxicity, by dermal route:						n.d.a.	
Acute toxicity, by inhalation:						n.d.a.	
Skin corrosion/irritation:						n.d.a.	
Serious eye damage/irritation:						n.d.a.	
Respiratory or skin						n.d.a.	
sensitisation:							



Page 6 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005

Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012 PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

Germ cell mutagenicity:	n.d.a.
Carcinogenicity:	n.d.a.
Reproductive toxicity:	n.d.a.
Specific target organ toxicity -	n.d.a.
single exposure (STOT-SE):	
Specific target organ toxicity -	n.d.a.
repeated exposure (STOT-RE):	
Aspiration hazard:	n.d.a.
Respiratory tract irritation:	n.d.a.
Repeated dose toxicity:	n.d.a.
Symptoms:	n.d.a.
Other information:	Classification according
	to calculation procedure.

## **SECTION 12: Ecological information**

Possibly more information on environmental effects, see Section 2.1 (classification).

Kunststoff "Wie Neu" (schwarz) 250ML							
Art.: 1552							
Toxicity/effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
Toxicity to fish:							n.d.a.
Toxicity to daphnia:							n.d.a.
Toxicity to algae:							n.d.a.
Persistence and							n.d.a.
degradability:							
Bioaccumulative							n.d.a.
potential:							
Mobility in soil:							n.d.a.
Results of PBT and							n.d.a.
vPvB assessment							
Other adverse effects:							n.d.a.

## **SECTION 13: Disposal considerations**

#### 13.1 Waste treatment methods

#### For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product. Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2001/118/EC, 2001/119/EC, 2001/573/EC) 07 03 04 other organic solvents, washing liquids and mother liquors

Recommendation:

Pay attention to local and national official regulations

E.g. suitable incineration plant.

E.g. dispose at suitable refuse site.

#### For contaminated packing material

Pay attention to local and national official regulations

Empty container completely.

Uncontaminated packaging can be recycled.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

#### **SECTION 14: Transport information**

#### **General statements**

UN number: n.a.

#### Transport by road/by rail (ADR/RID)

UN proper shipping name:

Transport hazard class(es): n.a. Packing group: n.a.



Page 7 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005

Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012

PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

 Classification code:
 n.a.

 LQ (ADR 2011):
 n.a.

 LQ (ADR 2009):
 n.a.

Environmental hazards: Not applicable

Tunnel restriction code:

Transport by sea (IMDG-code)

UN proper shipping name:

Transport hazard class(es):

Packing group:

n.a.

Marine Pollutant:

n.a

Environmental hazards: Not applicable

Transport by air (IATA)

UN proper shipping name:

Transport hazard class(es):

Packing group:

n.a.

n.a.

Environmental hazards: Not applicable

Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Non-dangerous material according to Transport Regulations.

#### SECTION 15: Regulatory information

#### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

For classification and labelling see Section 2.

 Observe restrictions:
 n.a.

 VOC (1999/13/EC):
 < 0,1%</td>

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

#### **SECTION 16: Other information**

2.3.9

These details refer to the product as it is delivered.

Revised sections:

The following statements are the indicated R-phrases / H-phrases and classification codes (GHS/CLP) for the ingredients (listed in Section 3). 36/38 Irritating to eyes and skin.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

Skin Irrit.-Skin irritation Eye Irrit.-Eye irritation

#### Any abbreviations and acronyms used in this document:

AC Article Categories

acc., acc. to according, according to

ACGIH American Conference of Governmental Industrial Hygienists

ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)

AOEL Acceptable Operator Exposure Level

AOX Adsorbable organic halogen compounds

approx. approximately

Art., Art. no. Article number

ATE Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)

BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)

BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)

BCF Bioconcentration factor

BGV Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)

BHT Butylhydroxytoluol (= 2,6-Di-t-butyl-4-methyl-phenol)



Page 8 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005

Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012

PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

BMGV Biological monitoring guidance value (EH40, UK)

BOD Biochemical oxygen demand

BSEF Bromine Science and Environmental Forum

bw body weight

CAS Chemical Abstracts Service

CESIO Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques

CIPAC Collaborative International Pesticides Analytical Council

CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances

and mixtures)

CMR carcinogenic, mutagenic, reproductive toxic

COD Chemical oxygen demand

CTFA Cosmetic, Toiletry, and Fragrance Association

DMEL Derived Minimum Effect Level
DNEL Derived No Effect Level
DOC Dissolved organic carbon

DT50 Dwell Time - 50% reduction of start concentration

DVS Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)

dw dry weight

e.g. for example (abbreviation of Latin 'exempli gratia'), for instance

EC European Community
ECHA European Chemicals Agency
EEA European Economic Area
EEC European Economic Community

EINECS European Inventory of Existing Commercial Chemical Substances

ELINCS European List of Notified Chemical Substances

EN European Norms

EPA United States Environmental Protection Agency (United States of America)

ERC Environmental Release Categories

ES Exposure scenario
etc. et cetera
EU European Union

EWC European Waste Catalogue

Fax. Fax number gen. general

GHS Globally Harmonized System of Classification and Labelling of Chemicals

GWP Global warming potential

HET-CAM Hen's Egg Test - Chorionallantoic Membrane

HGWP Halocarbon Global Warming Potential
IARC International Agency for Research on Cancer
IATA International Air Transport Association
IBC Intermediate Bulk Container

IBC (Code) International Bulk Chemical (Code)

IC Inhibitory concentration

IMDG-code International Maritime Code for Dangerous Goods

incl. including, inclusive

**IUCLID International Uniform Chemical Information Database** 

LC lethal concentration

LC50 lethal concentration 50 percent kill LCLo lowest published lethal concentration

LD Lethal Dose of a chemical LD50 Lethal Dose, 50% kill LDLo Lethal Dose Low

LOAEL Lowest Observed Adverse Effect Level LOEC Lowest Observed Effect Concentration

LOEL Lowest Observed Effect Level

LQ Limited Quantities

MARPOL International Convention for the Prevention of Marine Pollution from Ships

n.a. not applicablen.av. not availablen.c. not checkedn.d.a. no data available

NIOSH National Institute of Occupational Safety and Health (United States of America)

NOAECNo Observed Adverse Effective Concentration

NOAEL No Observed Adverse Effect Level



Page 9 of 9

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 30.08.2012 / 0005

Replaces revision of / Version: 06.09.2011 / 0004

Valid from: 30.08.2012

PDF print date: 30.08.2012

Kunststoff "Wie Neu" (schwarz) 250ML Art.: 1552

NOEC No Observed Effect Concentration

NOEL No Observed Effect Level ODP Ozone Depletion Potential

OECD Organisation for Economic Co-operation and Development

org. organic

PAH polycyclic aromatic hydrocarbon PBT persistent, bioaccumulative and toxic

PC Chemical product category

PE Polyethylene

PNEC Predicted No Effect Concentration
POCP Photochemical ozone creation potential

ppm parts per million
PROC Process category
PTFE Polytetrafluorethylene

REACHRegistration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)

REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.

RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)

SADT Self-Accelerating Decomposition Temperature

SAR Structure Activity Relationship

SU Sector of use

SVHC Substances of Very High Concern

Tel. Telephone

ThOD Theoretical oxygen demand

TOC Total organic carbon

TRGS Technische Regeln für Gefahrstoffe (=Technical Regulations for Hazardous Substances)
VbF Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))

VOC Volatile organic compounds

vPvB very persistent and very bioaccumulative

WEL-TWA, WEL-STEL WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).

WHO World Health Organization

wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge. No responsibility.

These statements were made by

## Chemical Check GmbH, Wöbbeler Straße 2-4, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.