

## Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

**Auspuff-Montage-Paste 150GR**  
**Art.: 3342**

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

##### Relevant identified uses of the substance or mixture:

Seam sealant

Sector of use [SU]:

SU 3 - Industrial uses: Uses of substances as such or in preparations at industrial sites

SU21 - Consumer uses: Private households (=general public = consumers)

SU22 - Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

Chemical product category [PC]:

PC 1 - Adhesives, sealants

Process category [PROC]:

PROC 8a - Transfer of substance or preparation (charging/discharging) from/to vessels/large containers at non-dedicated facilities

PROC 8b - Transfer of substance or preparation (charging/discharging) from/to vessels/large containers at dedicated facilities

PROC 9 - Transfer of substance or preparation into small containers (dedicated filling line, including weighing)

PROC10 - Roller application or brushing

Article Categories [AC]:

AC99 - Not required.

Environmental Release Category [ERC]:

ERC 4 - Industrial use of processing aids in processes and products, not becoming part of articles

ERC 7 - Industrial use of substances in closed systems

ERC 8a - Wide dispersive indoor use of processing aids in open systems

ERC 8d - Wide dispersive outdoor use of processing aids in open systems

##### Uses advised against:

No information available at present.

#### 1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH, Jerg-Wieland-Straße 4, D-89081 Ulm-Lehr

Telephone (+49) 0731-1420-0, Fax (+49) 0731-1420-88

E-mail address of the competent person: [info@chemical-check.de](mailto:info@chemical-check.de), [k.schnurbusch@chemical-check.de](mailto:k.schnurbusch@chemical-check.de)

#### 1.4 Emergency telephone

##### Emergency information services / official advisory body:

##### Telephone number of the company in case of emergencies:

Tel.: (+49) 0731-1420-0

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### 2.1.1 Classification according to Regulation (EC) 1272/2008 (CLP)

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

##### 2.1.2 Classification according to Directives 67/548/EEC and 1999/45/EC (including amendments)

The mixture is not classified as dangerous in the terms of the directive 1999/45/EC.

#### 2.2 Label elements

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 21.11.2012 / 0006  
 Replaces revision of / Version: 19.01.2011 / 0005  
 Valid from: 21.11.2012  
 PDF print date: 05.12.2012  
 Auspuff-Montage-Paste 150GR Art.: 3342

## 2.2.1 Labeling according to Regulation (EC) 1272/2008 (CLP)

Not applicable

## 2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

## SECTION 3: Composition/information on ingredients

### 3.1 Substance

n.a.

### 3.2 Mixture

--	
<b>Registration number (REACH)</b>	--
<b>Index</b>	-
<b>EINECS, ELINCS, NLP</b>	-
<b>CAS</b>	-
<b>content %</b>	
<b>Classification according to Directive 67/548/EEC</b>	---
<b>Classification according to Regulation (EC) 1272/2008 (CLP)</b>	---

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

Never pour anything into the mouth of an unconscious person!

#### Inhalation

Supply person with fresh air and consult doctor according to symptoms.

#### Skin contact

Wash thoroughly using copious water - remove contaminated clothing immediately. If skin irritation occurs (redness etc.), consult doctor.

#### Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water - call doctor immediately, have Data Sheet available.

#### Ingestion

Give copious water to drink - consult doctor immediately.

Do not induce vomiting.

### 4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

The following may occur:

Irritation of the eyes

with long-term contact:

Product removes fat.

Dermatitis (skin inflammation)

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

### 4.3 Indication of any immediate medical attention and special treatment needed

n.c.

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

Adapt to the nature and extent of fire.

Water jet spray / alcohol resistant foam / CO<sub>2</sub> / dry extinguisher

Cool container at risk with water.

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revised on / Version: 21.11.2012 / 0006

Replaces revision of / Version: 19.01.2011 / 0005

Valid from: 21.11.2012

PDF print date: 05.12.2012

Auspuff-Montage-Paste 150GR Art.: 3342

## Unsuitable extinguishing media

High volume water jet

## 5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Irritating gases

Oxides of carbon

Oxides of nitrogen

Toxic pyrolysis products.

## 5.3 Advice for firefighters

According to size of fire

Protective respirator with independent air supply.

Full protection, if necessary

Dispose of contaminated extinction water according to official regulations.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

Ensure sufficient supply of air.

Avoid contact with eyes or skin.

### 6.2 Environmental precautions

Prevent from entering drainage system.

If leakage occurs, dam up.

Resolve leaks if this possible without risk.

Prevent surface and ground-water infiltration, as well as ground penetration.

If accidental entry into drainage system occurs, inform responsible authorities.

### 6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent) and dispose of according to Section 13.

Or:

Pick up mechanically and dispose of according to Section 13.

### 6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

## SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

### 7.1 Precautions for safe handling

#### 7.1.1 General recommendations

Ensure good ventilation.

Avoid contact with eyes or skin.

Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.

Observe directions on label and instructions for use.

#### 7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

### 7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.

Store product closed and only in original packing.

Store separately from alkalis.

Store separately from acids.

Store in a dry place.

Store in a well ventilated place.

Protect from direct sunlight and warming.

Only store at temperatures from 15°C to 30°C.

### 7.3 Specific end use(s)

No information available at present.

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 21.11.2012 / 0006  
 Replaces revision of / Version: 19.01.2011 / 0005  
 Valid from: 21.11.2012  
 PDF print date: 05.12.2012  
 Auspuff-Montage-Paste 150GR Art.: 3342

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

(GB) Chemical Name	general dust limit	Content %:	
WEL-TWA: 10 mg/m <sup>3</sup> (inhal. dust), 4 mg/m <sup>3</sup> (respir. dust)	WEL-STEL: ---	---	
BMGV: ---	Other information: ---		
(GB) Chemical Name	China stone	Content %:	
WEL-TWA: 2 mg/m <sup>3</sup> (res. dust)	WEL-STEL: ---	---	
BMGV: ---	Other information: ---		

(GB) WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period) EH40. AGW = "Arbeitsplatzgrenzwert" (workplace limit value, Germany). | WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period). | BMGV = Biological monitoring guidance value EH40. BGW = "Biologischer Grenzwert" (biological limit value, Germany) | Other information: Sen = Capable of causing occupational asthma. Sk = Can be absorbed through skin. Carc = Capable of causing cancer and/or heritable genetic damage.  
 \*\* = The exposure limit for this substance is repealed through the TRGS 900 (Germany) of January 2006 with the goal of revision.

### 8.2 Exposure controls

#### 8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.  
 If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.  
 Applies only if maximum permissible exposure values are listed here.

#### 8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.  
 Wash hands before breaks and at end of work.  
 Keep away from food, drink and animal feedingstuffs.  
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:  
 Tight fitting protective goggles with side protection (EN 166).

Skin protection - Hand protection:  
 Chemical resistant protective gloves (EN 374).  
 Recommended  
 Protective nitrile gloves (EN 374)  
 Minimum layer thickness in mm:  
 > 0,4  
 Permeation time (penetration time) in minutes:  
 > 30  
 Protective hand cream recommended.

Skin protection - Other:  
 Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments)  
 According to operation.  
 Natural fibre or heat-resistant synthetic fibre

Respiratory protection:  
 Normally not necessary.

Thermal hazards:  
 If applicable, these are included in the individual protective measures (eye/face protection, skin protection, respiratory protection).

Additional information on hand protection - No tests have been performed.  
 In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.  
 Selection of materials derived from glove manufacturer's indications.  
 Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.

Page 5 of 10  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 21.11.2012 / 0006  
 Replaces revision of / Version: 19.01.2011 / 0005  
 Valid from: 21.11.2012  
 PDF print date: 05.12.2012  
 Auspuff-Montage-Paste 150GR Art.: 3342

Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.

The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

### 8.2.3 Environmental exposure controls

No information available at present.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

Physical state:	Pastelike, Liquid
Colour:	Grey
Odour:	Odourless
Odour threshold:	Not determined
pH-value:	Not determined
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	Not determined
Flash point:	n.a.
Evaporation rate:	Not determined
Flammability (solid, gas):	Not determined
Lower explosive limit:	Not determined
Upper explosive limit:	Not determined
Vapour pressure:	Not determined
Vapour density (air = 1):	Not determined
Density:	~1,71 g/cm <sup>3</sup>
Bulk density:	Not determined
Solubility(ies):	Not determined
Water solubility:	partially, Soluble
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	Not determined
Decomposition temperature:	Not determined
Viscosity:	Not determined
Explosive properties:	Not determined
Oxidising properties:	No

### 9.2 Other information

Miscibility:	Not determined
Fat solubility / solvent:	Not determined
Conductivity:	Not determined
Surface tension:	Not determined
Solvents content:	Not determined

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

See also Subsection 10.2 to 10.6.

The product has not been tested.

### 10.2 Chemical stability

See also Subsection 10.1 to 10.6.

Stable with proper storage and handling.

### 10.3 Possibility of hazardous reactions

See also Subsection 10.1 to 10.6.

### 10.4 Conditions to avoid

See also section 7.

Protect from humidity.

### 10.5 Incompatible materials

See also section 7.

Avoid contact with strong alkalis.

Avoid contact with strong acids.

Avoid contact with strong oxidizing agents.



Page 7 of 10  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 21.11.2012 / 0006  
 Replaces revision of / Version: 19.01.2011 / 0005  
 Valid from: 21.11.2012  
 PDF print date: 05.12.2012  
 Auspuff-Montage-Paste 150GR Art.: 3342

Other information:							According to the recipe, contains no AOX.
--------------------	--	--	--	--	--	--	---

China stone							
Toxicity/effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
Persistence and degradability:							Not relevant for inorganic substances.
Water solubility:							Insoluble

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.  
 Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2001/118/EC, 2001/119/EC, 2001/573/EC)  
 08 04 10 waste adhesives and sealants other than those mentioned in 08 04 09

Recommendation:

Pay attention to local and national official regulations

E.g. suitable incineration plant.

E.g. dispose at suitable refuse site.

#### For contaminated packing material

Pay attention to local and national official regulations

15 01 04 metallic packaging

Empty container completely.

Uncontaminated packaging can be recycled.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

## SECTION 14: Transport information

### General statements

UN number: n.a.

#### Transport by road/by rail (ADR/RID)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Classification code: n.a.

LQ (ADR 2011): n.a.

LQ (ADR 2009): n.a.

Environmental hazards: Not applicable

Tunnel restriction code:

#### Transport by sea (IMDG-code)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Marine Pollutant: n.a.

Environmental hazards: Not applicable

#### Transport by air (IATA)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Environmental hazards: Not applicable

### Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

#### Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Non-dangerous material according to Transport Regulations.

## SECTION 15: Regulatory information

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 21.11.2012 / 0006  
 Replaces revision of / Version: 19.01.2011 / 0005  
 Valid from: 21.11.2012  
 PDF print date: 05.12.2012  
 Auspuff-Montage-Paste 150GR Art.: 3342

## 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

For classification and labelling see Section 2.

Observe restrictions: n.a.

VOC 1999/13/EC 0% w/w

## 15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

## SECTION 16: Other information

These details refer to the product as it is delivered.

Revised sections: 2

## Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

## Any abbreviations and acronyms used in this document:

AC Article Categories  
 acc., acc. to according, according to  
 ACGIH American Conference of Governmental Industrial Hygienists  
 ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)  
 AOEL Acceptable Operator Exposure Level  
 AOX Adsorbable organic halogen compounds  
 approx. approximately  
 Art., Art. no. Article number  
 ATE Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)  
 BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)  
 BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)  
 BCF Bioconcentration factor  
 BGV Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)  
 BHT Butylhydroxytoluol (= 2,6-Di-t-butyl-4-methyl-phenol)  
 BMGV Biological monitoring guidance value (EH40, UK)  
 BOD Biochemical oxygen demand  
 BSEF Bromine Science and Environmental Forum  
 bw body weight  
 CAS Chemical Abstracts Service  
 CESIO Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques  
 CIPAC Collaborative International Pesticides Analytical Council  
 CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)  
 CMR carcinogenic, mutagenic, reproductive toxic  
 COD Chemical oxygen demand  
 CTFA Cosmetic, Toiletry, and Fragrance Association  
 DMEL Derived Minimum Effect Level  
 DNEL Derived No Effect Level  
 DOC Dissolved organic carbon  
 DT50 Dwell Time - 50% reduction of start concentration  
 DVS Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)  
 dw dry weight  
 e.g. for example (abbreviation of Latin 'exempli gratia'), for instance  
 EC European Community  
 ECHA European Chemicals Agency  
 EEA European Economic Area



Page 9 of 10  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 21.11.2012 / 0006  
 Replaces revision of / Version: 19.01.2011 / 0005  
 Valid from: 21.11.2012  
 PDF print date: 05.12.2012  
 Auspuff-Montage-Paste 150GR Art.: 3342

EEC European Economic Community  
 EINECS European Inventory of Existing Commercial Chemical Substances  
 ELINCS European List of Notified Chemical Substances  
 EN European Norms  
 EPA United States Environmental Protection Agency (United States of America)  
 ERC Environmental Release Categories  
 ES Exposure scenario  
 etc. et cetera  
 EU European Union  
 EWC European Waste Catalogue  
 Fax. Fax number  
 gen. general  
 GHS Globally Harmonized System of Classification and Labelling of Chemicals  
 GWP Global warming potential  
 HET-CAM Hen's Egg Test - Chorionallantoic Membrane  
 HGWP Halocarbon Global Warming Potential  
 IARC International Agency for Research on Cancer  
 IATA International Air Transport Association  
 IBC Intermediate Bulk Container  
 IBC (Code) International Bulk Chemical (Code)  
 IC Inhibitory concentration  
 IMDG-code International Maritime Code for Dangerous Goods  
 incl. including, inclusive  
 IUCLID International Uniform Chemical Information Database  
 LC lethal concentration  
 LC50 lethal concentration 50 percent kill  
 LCLo lowest published lethal concentration  
 LD Lethal Dose of a chemical  
 LD50 Lethal Dose, 50% kill  
 LDLo Lethal Dose Low  
 LOAEL Lowest Observed Adverse Effect Level  
 LOEC Lowest Observed Effect Concentration  
 LOEL Lowest Observed Effect Level  
 LQ Limited Quantities  
 MARPOL International Convention for the Prevention of Marine Pollution from Ships  
 n.a. not applicable  
 n.av. not available  
 n.c. not checked  
 n.d.a. no data available  
 NIOSH National Institute of Occupational Safety and Health (United States of America)  
 NOAEC No Observed Adverse Effective Concentration  
 NOAEL No Observed Adverse Effect Level  
 NOEC No Observed Effect Concentration  
 NOEL No Observed Effect Level  
 ODP Ozone Depletion Potential  
 OECD Organisation for Economic Co-operation and Development  
 org. organic  
 PAH polycyclic aromatic hydrocarbon  
 PBT persistent, bioaccumulative and toxic  
 PC Chemical product category  
 PE Polyethylene  
 PNEC Predicted No Effect Concentration  
 POCP Photochemical ozone creation potential  
 ppm parts per million  
 PROC Process category  
 PTFE Polytetrafluorethylene  
 REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)  
 REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.  
 RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)  
 SADT Self-Accelerating Decomposition Temperature  
 SAR Structure Activity Relationship

Page 10 of 10  
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
Revised on / Version: 21.11.2012 / 0006  
Replaces revision of / Version: 19.01.2011 / 0005  
Valid from: 21.11.2012  
PDF print date: 05.12.2012  
Auspuff-Montage-Paste 150GR Art.: 3342

SU Sector of use  
SVHC Substances of Very High Concern  
Tel. Telephone  
ThOD Theoretical oxygen demand  
TOC Total organic carbon  
TRGS Technische Regeln für Gefahrstoffe (=Technical Regulations for Hazardous Substances)  
VbF Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))  
VOC Volatile organic compounds  
vPvB very persistent and very bioaccumulative  
WEL-TWA, WEL-STEL WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).  
WHO World Health Organization  
wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.  
No responsibility.

These statements were made by:

**Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90**

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.