

ZYXEL

Zyxel GS1915-8 Managed L2 Gigabit Ethernet (10/100/1000) Black

Brand : Zyxel

Product code: GS1915-8-GB0101F

Product name : GS1915-8

GS1915-8 - 8-port GbE Smart Managed Switch

Zyxel GS1915-8. Switch type: Managed, Switch layer: L2. Basic switching RJ-45 Ethernet ports type: Gigabit Ethernet (10/100/1000), Basic switching RJ-45 Ethernet ports quantity: 8. Full duplex. MAC address table: 8000 entries, Switching capacity: 16 Gbit/s. Networking standards: IEEE 802.1Q, IEEE 802.1s, IEEE 802.1x, IEEE 802.3ab, IEEE 802.3af, IEEE 802.3at, IEEE 802.3az,.... Power connector: AC-in jack



Management features		Design	
Switch type *	Managed	Product colour	Black
Switch layer	L2	LED indicators	✓
Quality of Service (QoS) support	✓	Electromagnetic compatibility	LVD EN60950-1, BSMI CNS14336-1
Web-based management	✓	Performance	
System event log	✓	Noise level	0 dB
MIB support	RFC 1213 MIB II, RFC 2819, RFC 1215, RFC 1493	Mean time between failures (MTBF)	1144461 h
Ports & interfaces		Power	
Basic switching RJ-45 Ethernet ports quantity *	8	Power source *	AC
Basic switching RJ-45 Ethernet ports type *	Gigabit Ethernet (10/100/1000)	AC input voltage	220 - 240 V
Gigabit Ethernet (copper) ports quantity	8	AC input frequency	50 - 60 Hz
Power connector	AC-in jack	Power consumption (max)	4.7 W
Network		Power over Ethernet (PoE)	
Networking standards *	IEEE 802.1Q, IEEE 802.1s, IEEE 802.1x, IEEE 802.3ab, IEEE 802.3af, IEEE 802.3at, IEEE 802.3az, IEEE 802.3u, IEEE 802.3x	Power over Ethernet (PoE) *	✗
10G support *	✗	Operational conditions	
Copper ethernet cabling technology	10BASE-T, 100BASE-TX, 1000BASE-T	Operating temperature (T-T)	0 - 40 °C
Full duplex	✓	Storage temperature (T-T)	-40 - 70 °C
Flow control support	✓	Operating relative humidity (H-H)	10 - 95%
Broadcast storm control	✓	Storage relative humidity (H-H)	10 - 95%
Rate limiting	✓	Heat dissipation	16.03 BTU/h
Auto MDI/MDI-X	✓	Weight & dimensions	
VLAN support	✓	Width	250 mm
		Depth	104 mm
		Height	27 mm
		Weight	620 g
		Packaging content	
		Cables included	AC

Network		Packaging content	
Number of VLANs	8	Quick start guide	✓
Data transmission		User guide	✓
Switching capacity *	16 Gbit/s	Manual	✓
Forwarding rate	11.9 Mpps	Packaging data	
MAC address table *	8000 entries	Package type	Box
Jumbo frames support	✓	Package width	302 mm
Jumbo frames	9000	Package depth	227 mm
Packet buffer memory	0.5 MB	Package height	64 mm
Security		Package weight	1.1 kg
IGMP snooping	✓	Certificates	
MAC address filtering	✓	Certification	CE, FCC, C-Tick, Class A, Class B, BSMI CNS13438
SSH/SSL support	✓		
Multicast features			
Multicast support	✓		
Protocols			
Management protocols	SNMP v1,v2,v3, RMON (1,2,3,9)		



4718937621903

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.