



Material Safety Data Sheet
Date: April, 22nd 2008

Identification : M1100 – M1120 – M1140 : Permanent Polyester Tape
1. Company : Dymo bvba Industriepark Noord 30 9100 St-Niklaas Belgium Telephone : +32 (03) 778 85 11 Fax : +32 (03) 776 51 81
2. Composition – Hazardous components Individual components of this product do not contribute to any known hazards. OSHA hazardous components (29 CFR1910.1200): None
3. Hazards identification Potential health effects : none Acute: no significant toxic hazard. When burned may produce toxic fumes. Chronic : no significant toxic hazard. None of the components present in this material at concentrations equal to or greater than 0.1% are listed by IARC, NTP, OSHA or ACGIH as a carcinogen.
4. First aid measures Inhalation: N/A Skin: N/A Eyes: N/A Ingestion: N/A
5. Fire fighting measures Flash point : N/A Extinguishing media : use multi-rated ABC extinguisher or water Special fire fighting procedures : In case of fire, use self-contained breathing apparatus and full protective equipment – all fires liberate toxic gases Unusual fire and explosion hazards : None
6. Accidental release measures N/A

<p>7. Handling and storage</p> <p>No special handling required, other than storing away from excessive heat sources.</p>								
<p>8. Exposure controls/personal protection</p> <p>Respiratory protection : none required Skin protections : no precautions required Eye protection : none required Exposure guidelines : none established Engineering controls : none required</p>								
<p>9. Physical/chemical Properties</p> <table> <tr> <td>Boiling point : N/A</td> <td>Vapor pressure (mm Hg) : N/A</td> </tr> <tr> <td>Solubility in water : N/A</td> <td>Appearance and odor : N/A</td> </tr> <tr> <td>Specific gravity : N/A</td> <td>Vapor density : N/A</td> </tr> <tr> <td>Reactivity of water : N/A</td> <td>Melting point : N/A</td> </tr> </table>	Boiling point : N/A	Vapor pressure (mm Hg) : N/A	Solubility in water : N/A	Appearance and odor : N/A	Specific gravity : N/A	Vapor density : N/A	Reactivity of water : N/A	Melting point : N/A
Boiling point : N/A	Vapor pressure (mm Hg) : N/A							
Solubility in water : N/A	Appearance and odor : N/A							
Specific gravity : N/A	Vapor density : N/A							
Reactivity of water : N/A	Melting point : N/A							
<p>10. Stability and reactivity</p> <p>Stability : N/A Conditions to avoid : fire or excessive heat Incompatibility : none Hazardous decomposition products : none Hazardous polymerization : will not occur</p>								
<p>11. Toxicological information</p> <p>Carcinogen status ...NTP : none.....IARC : none.....OSHA : none</p>								
<p>12. Ecological information</p> <p>No data available</p>								
<p>13. Disposal considerations</p> <p>Waste disposal : dispose of in accordance with local, state and federal regulations.</p>								
<p>14. Transport information</p> <p>Transportation and hazardous materials description: not a hazardous material for DOT shipping.</p>								

