

**Features:**

- Multiple keys and poles
- Interlock and individual lock

**Applications:**

- Various switching purposes in all home electronic equipment and industrial electronic equipment

**Specifications:**

Switch specifications	
Pole – position	2P2T, 4P2T, 6P2T, Momentary and lock type are available
Contact rating	30V DC, 0.1A
Contact resistance	409mΩ max.; 1.5V DC; 100mA, by method of voltage drop
Insulation resistance	100MΩ min.; 500V DC
Dielectric strength	Breakdown is not allowable; 500V AC for 1 minute
Operating force	250 ± 150gf
Operating life	10,000 cycles
Operating temperature range	-20°C to +70°C
Total travel	Lock travel: 2.5 ± 0.3mm Total travel: 3.0 ± 0.3mm


**Frame type:**

- Cover – PST, POM
- Actuator – PA + GF
- Base frame – PBT + GF
- Terminal – silver, gold plating



**Unit weight:**

- **78-0060:** 1.1 ± 0.05g/pcs
- **78-0062:** 2.3 ± 0.05g/pcs





### 78-0060 Schematic




### 78-0060 Dimensions




### 78-0060 PCB Layout



### 78-0062 Schematic



### 78-0062 Dimensions



### 78-0062 PCB Layout

