



Magnetic Contact Switches

Specification: MCS-121 Series


- *Mini stick on contact with flange
- *Side leads with #22 AWG 18" length
- *Adhesive and screw mount included
- *Switch or Magnet are available separately
- *Specials leads available on request
- *Resistor, Diode and Supervisory Loop available on request
- *Colours: White, Brown, Grey

Surface mounted



 ϵ

Dimensions (mm)





Note: For small hole version please add S after the color letter

Order Information X denotes colour W=White, B=Brown, G= Grey

Part Number	Loop Type	Reed Form	Closed Gap Inch (mm)	Departure Gap Inch (mm)	Max Initial Contact Resistance (Ohm)	Max Initial Contact rating (W)	Max Switching Voltage (VDC/VAC)	Max Switching Current (A)
MCS-121-1X	Closed	N/O	1 (25)	0.6 (17)	0.150	10	100	0.5
MCS-121-2X	Closed	N/O	1 (25)	1.1 (28)	0.150	10	100	0.5
MCS-121-3X	Closed	N/O	1¼ (31)		0.150	10	100	0.5
MCS-121-4X	Open	N/C	1 (24)		0.150	3	30	0.2
MCS-121-5X	Open & Closed	SPDT	1 (24)		0.150	3	30	0.2



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: +44 (0)1255 862236

www.assemtech.co.uk

Fax: +44 (0)1255 862014