



Lenovo EPYC AMD 7313 processor 3 GHz 128 MB L3 Tray

Brand : Lenovo

Product family: EPYC

Product code: 4XG7A63588

Product name : AMD EPYC
7313



16 cores, 32 threads, 3GHz base clock, 3.7GHz boost clock, 128MB L3 cache, 155W TDP

[Lenovo EPYC AMD 7313 processor 3 GHz 128 MB L3 Tray:](#)

Accelerate Workload Performance

Data centers that require the best CPU performance, security features, and scalability count on

Solution Briefs and White Papers

Find the technical resources you need to learn more about AMD EPYC™.

Where to Buy EPYC™ Powered Solutions

Find a partner offering AMD EPYC™ Processors and solutions.

AMD Data Center Insights and Updates

Sign up to receive the latest data center news and server content.

AMD Infinity Guard

Help minimize potential attack surfaces as software is booted, executed, and processes your critical data

AMD Infinity Architecture

With architecture, performance, and security leadership, our approach to processor design accelerates the pace of innovation so that you can break through years of data center stagnation.

Processor		Memory	
Processor manufacturer *	AMD	Memory types supported by processor	DDR4-SDRAM
Processor model *	7313	Memory clock speeds supported by processor	3200 MHz
Processor base frequency *	3 GHz	Memory channels *	Octa-channel
Processor family *	AMD EPYC	Memory bandwidth (max)	204.8 GB/s
Processor cores *	16	Graphics	
Processor socket *	Socket SP3	On-board graphics card *	×
Component for	Server/workstation	Discrete graphics card *	×
Processor threads	32	On-board graphics card model *	Not available
Processor boost frequency	3.7 GHz	Discrete graphics card model *	Not available
Processor cache	128 MB	Features	
Processor cache type	L3	Market segment	Server
Thermal Design Power (TDP)	155 W	Maximum number of PCI Express lanes	128
Configurable TDP-up	180 W	PCI Express slots version	4.0
Package type *	Tray		
Cooler included *	×		
Configurable TDP-down	155 W		



0889488572366



889488572366

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.