

Philips S Line 273S1/00 computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LCD Black

Brand : Philips

Product family: S Line

Product code: 273S1/00

Product name : 273S1/00

Monitor 273S1 LCD monitor with USB-C docking

Philips S Line 273S1/00 computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LCD Black:

The Philips USB-C monitor replaces cable clutter. View FHD image and charge your laptop at the same time with a single USB-C cable. Features like Daisy chain for multi-display setup, and Eye comfort with TUV certification to reduce eye fatigue.

Philips S Line 273S1/00. Display diagonal: 68.6 cm (27"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LCD, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	68.6 cm (27")	VESA mounting *	✓
Display resolution *	1920 x 1080 pixels	Panel mounting interface	100 x 100 mm
HD type *	Full HD	Cable lock slot *	✓
Native aspect ratio *	16:9	Cable lock slot type	Kensington
Display technology *	LCD	Height adjustment *	✓
Panel type *	IPS	Adjustable height (max)	13 cm
Backlight type	W-LED	Pivot	✓
Touchscreen *	✗	Pivot angle	-90 - 90°
Display brightness (typical)	300 cd/m²	Swivelling	✓
Response time *	4 ms	Swivel angle range	-180 - 180°
Anti-glare screen	✓	Tilt angle range	-5 - 25°
Screen shape *	Flat	On Screen Display (OSD)	✓
Contrast ratio (typical) *	1000:1	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Contrast ratio (dynamic)	50000000:1		
Dynamic contrast ratio marketing name	SmartContrast	Plug and Play	✓
Maximum refresh rate *	75 Hz	LED indicators	Operation, Stand-by
Viewing angle, horizontal	178°	Power	
Viewing angle, vertical	178°	Energy efficiency class (SDR) *	E
Display number of colours *	16.7 million colours	Energy efficiency class (HDR) *	Not available
Pixel pitch	0.3114 x 0.3114 mm	Energy consumption (SDR) per 1000 hours *	21 kWh
Pixel density	82 ppi	Power consumption (typical) *	17.2 W
Horizontal scan range	30 - 85 kHz	Power consumption (standby) *	0.3 W
Vertical scan range	48 - 75 Hz	Power consumption (off)	0.3 W
Viewable size, horizontal	59.8 cm	AC input voltage	100 - 240 V
Viewable size, vertical	33.6 cm		
Display diagonal (metric)	68.6 cm		
DDC/CI	✓		
Haze rate	25%		

Display		Power	
Surface hardness	3H	AC input frequency	50 - 60 Hz
Colour depth	6 bit	Power supply type	Internal
Colour gamut standard	sRGB	Energy efficiency scale	A to G
sRGB coverage (typical)	102%	Operational conditions	
NTSC coverage (typical)	81%	Operating temperature (T-T)	0 - 40 °C
Display sRGB	✓	Storage temperature (T-T)	-20 - 60 °C
Performance		Operating relative humidity (H-H)	20 - 80%
NVIDIA G-SYNC *	✗	Operating altitude	0 - 3658 m
AMD FreeSync *	✗	Non-operating altitude	3658 - 12192 m
Fast charging	✓	Weight & dimensions	
Fast charging technology	Power Delivery	Width (with stand)	613 mm
Component video sync	Separate Sync	Depth (with stand)	205 mm
Flicker-free technology	✓	Height (with stand)	537 mm
Low Blue Light technology	✓	Weight (with stand)	6.79 kg
Multimedia		Width (without stand)	613 mm
Number of speakers	2	Depth (without stand)	54 mm
RMS rated power	4 W	Height (without stand)	366 mm
Built-in speaker(s) *	✓	Weight (without stand)	5.03 kg
Built-in camera *	✗	Packaging data	
Design		Package width	730 mm
Market positioning *	Office	Package depth	193 mm
Product colour *	Black	Package height	471 mm
Front bezel colour	Black	Package weight	10.3 kg
Feet colour	Black	Packaging content	
Ports & interfaces		Stand included	✓
Built-in USB hub *	✓	Cables included	HDMI, DisplayPort, USB Type-C, AC
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Manual	✓
USB upstream port type	USB Type-C	Bundled software	SmartControl
Number of USB Type-C upstream ports quantity	1	Sustainability	
USB Type-A downstream ports quantity	4	Sustainability compliance	✓
USB Type-C DisplayPort Alternate Mode	✓	Sustainability certificates	ENERGY STAR, TCO
USB Power Delivery (USB PD)	✓	Doesn't contain	PVC/BFR, Mercury
USB Power Delivery up to	65 W	Other features	
HDMI *	✓	Compatible operating systems	Mac OS X Windows 11 / 10 / 8.1 / 8 / 7
HDMI ports quantity	1	Exterior finish type	Textured
HDMI version	1.4	Picture enhancement	SmartImage
DisplayPorts quantity	1	Regulatory Approvals	CB; FCC Class B; ICES-003; CE Mark; TUV/GS; TUV Ergo; SEMKO; CU-EAC; EAEU RoHS; TUV Eye Comfort certified
DisplayPort version	1.2	EasyRead mode	✓
Audio output	✓	LowBlue mode	✓
HDCP	✓	Compliance certificates	RoHS
HDCP version	1.4/2.2	Mean time between failures (MTBF)	70000 h
DisplayPort output	✓	Ethernet LAN data rates	10,100,1000 Mbit/s
Network		Wake-on-LAN	✓
Ethernet LAN	✓	Recycling data	
		Recyclable packaging material	100%
		Post-consumer recycled plastic	85%



8712581799922

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.