StarTech.com SPDIF Digital Coaxial or Toslink Optical to Stereo RCA Audio Converter



Brand : StarTech.com

Product code: SPDIF2AA


Product name : SPDIF Digital Coaxial or Toslink Optical to Stereo RCA Audio Converter

StarTech.com SPDIF Digital Coaxial or Toslink Optical to Stereo RCA Audio Converter - Digital Audio Adapter
StarTech.com SPDIF Digital Coaxial or Toslink Optical to Stereo RCA Audio Converter. Sample frequencies: 32, 44.1, 48, 96 KHz. Operating voltage: 5 V, Power consumption (typical): 0.5 W, Input voltage: 100 - 240 V. Width: 42 mm, Depth: 52 mm, Height: 27 mm. Package width: 120 mm, Package depth: 170 mm, Package height: 58 mm



Inputs	
Digital audio coaxial in *	1
Digital audio optical in *	1
Sample frequencies	32, 44.1, 48, 96 KHz
Outputs	
Audio (L/R) out *	1
Technical details	
Product colour	Black
Housing material	Steel
Certification	CE, FCC
Power	
Operating voltage	5 V
External power adapter	✔
Power consumption (typical)	0.5 W
Input voltage	100 - 240 V
Weight & dimensions	
Width	42 mm


Weight & dimensions	
Depth	52 mm
Height	27 mm
Weight	72 g
Operational conditions	
Operating temperature (T-T)	0 - 70 °C
Storage temperature (T-T)	-10 - 80 °C
Operating relative humidity (H-H)	10 - 85%
Packaging data	
Quantity	1
Package width	120 mm
Package depth	170 mm
Package height	58 mm
Package weight	368 g
Logistics data	
Harmonized System (HS) code	85176990



0065030832304



065030832304



5052584153110

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date