



## Material Safety Data Sheet

HI-WATT BATTERY

---

### 1 Chemical Product and Company Identification

Date of issue : 01 Jan 2015  
Product name: Carbon-Zinc Battery  
Manufacturer/Supplier: Hi-Watt Battery Industry Co., Ltd  
Rm 2307-2310, Delta House, 3 On Yiu Street,  
Shatin, Hong Kong

---

### 2. Composition/ Information on Ingredients

Chemical/Size	R03 AAA Size	R6 AA Size	R14 C Size	R20 D Size	CAS Registry No
Weight	8.8g	18.5 g	49 g	97 g	
Mercury	Not Detected	Not Detected	Not Detected	Not Detected	7439-97-6
Cadmium	Not Detected	Not Detected	Not Detected	Not Detected	7440-43-9
Lead	0.018%	0.012%	0.013%	0.008%	7439-92-1
Zinc	35.82%	25.96%	19.50%	17.80%	7440-66-6
Carbon	6.18%	10.83%	9.98%	10.72%	7782-42-5
Manganese Dioxide	26.76%	19.15%	20.14%	24.88%	1313-13-9
Cellulose	3.51%	1.57%	2.75%	2.37%	9004-34-6
Polystyrene	1.01%	2.23%	2.53%	2.39%	9003-53-6
Tin	/	20.3%	20.8%	13.72%	7440-31-5
Zinc Chloride	7.68%	5.988%	7.29%	8.436%	7646-85-7
Ammonium Chloride Solution	17.902%	13.96%	16.997%	19.676%	12125-02-9
Copper	1.12%	/	/	/	7440-50-8
	100%	100%	100%	100%	

The components in this section may only represent a hazard, if the batteries are damaged.



# Material Safety Data Sheet

HI-WATT BATTERY

### 3. Hazards Identification:

Warning: When recharge batteries or discard in the fire or use used battery with new one, or connected improperly may cause battery vent, leak or explode.

Damaged batteries may cause skin and eye burn, may cause respiratory tract irritation.

---

### 4. First-aid Measure

General speaking it is not expected to result in situation that requires first-aid measure, except the damaged batteries may cause they release the contents.

Inhalation: If vapours or fumes from vented or leaked batteries are irritation, move to fresh air and get medical attention.

Eyes: Check for and remove any contact lens, flush eyes with plenty of water, holding eyelids open, for at least 20 minutes, get medical help.

Skin: Immediately move the metal fragments and chemical components flush skin with plenty of water at least 15 minutes, get medical, if necessary,

Ingestion: Get immediately medical attention, do not induce vomiting or give a liquid to unconscious person.

---

### 5. Fire Fighting Measure:

Extinguishing media: Use appropriate agent for adjacent fire.

Flash point: Not available

Auto-ignition temperature: Not available

Flammable limits: Not available

Products of combustion: Zinc oxide, manganese oxide.

---

### 6. Accidental Release Measure:

Not available

---

### 7. Handling and Storage:

Precaution: Handling and transfer the products with care, make sure the packing always in good condition.

Damaged packing may cause batteries contact together, in this case batteries may short circuit or improperly connected, it cause batteries venting, leaking or exploding.

---



## Material Safety Data Sheet

HI-WATT BATTERY

Storage: Store in a dry, cool and well-ventilated area.

---

### 8. Exposure control / Personal protection

Exposure control: If necessary, set local exhaust ventilation.

Personal protection: Gloves, safety glass, dust respirator.

---

### 9. Physical and Chemical Properties

Physical State and Appearance: Solid

Melting Point : 419°C

Vapour pressure: Not available.

PH (1% soln/water): Not available.

Solubility: Insoluble.

Volatility: Not available.

Specific gravity: (water=1) not applicable

Odour: Odourless.

Taste: Not available.

---

### 10. Stability and Reactivity

Stability: The products are stable

Instability temperature: Not available.

Incompatibility: Reactive with acids and alkalis.

Corrosivity: None.

Hazardous Polymerization: Will not occur.

---

### 11. Toxicological information

Note: Since the materials in this battery are sealed in the can, the potential for exposure to the components of the battery is negligible, when the battery is used as directed. However technical or electrical abuse of the battery may result in the release of battery contents.

Toxicity to Animals: Not applicable

Chronic Effects on Human: Not applicable.

---

### 12. Ecological information

This product has not been tested for environmental effects.

---



# Material Safety Data Sheet

HI-WATT BATTERY

## 13. Disposal consideration

Waste disposal: Consult your local or regional authorities, disposal maybe subject to national, state, or local laws.

---

## 14. Regulatory information

ACGH: American Conference of Government Industrial Hygiene.

IARC: International Agency for Research Cancer.

NPT: US National Toxicology Program.

NIOSH: National Institute of Occupational Safety and Health

ACGIH, documentation on TLVS and BELS 1992-1993

ACGIH, threshold limit values, current listing

---

## 15. Other information

Warning wordings: “Keep out reach of children”

“Do not recharge or discard in fire or use used battery with new one, make sure polarity”

---

## 16. Transportation-Shipping:

The transportation of dry cell batteries manufactured or sold by Hi-Watt company is not prohibited for sea shipment by any major international regulatory bodies. It is not classified as dangerous goods under the IMDG Code, Amendment 36-12 by IMO and all applicable carrier and governmental regulations.

---

17. 24 hour emergency response number : 852 – 2348 0111

---

### Notice to reader

Although reasonable precaution have been taken in the preparation of the data Contained herein, it is offered solely for your information, consideration, and Investigation, HI-WATT extends no warranty of any kind.

---