








Features:

- Made in the UK
- Input Voltage: 240 or 120V
- Power: 3 ~ 36 VA 50/60Hz
- High Quality PCB Transformer
- UL94-V0 Materials
- Isolated Primary/Secondary windings
- Temperature Class: - Class B (130°C)
- Dielectric Strength: 4200Vrms
- Manufactured and tested in accordance to EN61558, EN60950, CE




Unused Pins will be omitted from standard parts.


3VA



6VA



12VA




Single Primary winding uses the two outer pins, the inner pins are left in for mounting support.

5mm Grid PCB VIEW

240V: Link in Series

120V: Link in Parallel



Windings can be connected in Parallel or Series

VA Rating	Dimension (mm)										Hole (mm)	PCB Hole	Weight (g)
	A	B	C	D	E	F	G	H	I				
3	38	32	30	4	25	5.08	Sq 0.7				1.2	140	
6	43	36	32	4	25	5.08	1.0x 0.7				1.2	180	
12	54	45	39	4	30	5.08	1.0x 0.7	45	36	3.4	1.5	340	
Tolerance	+/-0.5	+/-0.5	+/-0.5	+/-1.0	+/-0.5	+/-0.2	+/-0.1				Dia	approx	
12 ~ 36	Please contact us to discuss your requirements												

Please contact Vigortronix for any enquires. Products can be altered to suit custom requirements. The information contained in this document is subject to change without notice.

Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK
 Tel. +44 (0)1993 777570 Fax. +44 (0)1993 777580 Web. www.vigortronix.com E-mail: sales@vigortronix.com
 Vigortronix is a trading name of Vigortronix (UK) Limited

Twin Secondaries						
VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (mA)	Regulation (%)	Recommended Sec. Fuse
3	VTX-120-003-6045	2 x 120	2 x 4.5	333	20	0.35AT
3	VTX-120-003-606	2 x 120	2 x 6	250	20	0.25AT
3	VTX-120-003-609	2 x 120	2 x 9	166	20	0.16AT
3	VTX-120-003-612	2 x 120	2 x 12	125	20	0.125AT
3	VTX-120-003-615	2 x 120	2 x 15	100	20	0.10AT
3	VTX-120-003-618	2 x 120	2 x 18	83	20	0.09AT
3	VTX-120-003-620	2 x 120	2 x 20	75	20	0.08AT
3	VTX-120-003-624	2 x 120	2 x 24	63	20	0.063AT
6	VTX-120-006-6045	2 x 120	2 x 4.5	666	25	0.630AT
6	VTX-120-006-606	2 x 120	2 x 6	500	25	0.500AT
6	VTX-120-006-609	2 x 120	2 x 9	333	25	0.315AT
6	VTX-120-006-612	2 x 120	2 x 12	250	25	0.250AT
6	VTX-120-006-615	2 x 120	2 x 15	200	25	0.200AT
6	VTX-120-006-618	2 x 120	2 x 18	166	25	0.170AT
6	VTX-120-006-620	2 x 120	2 x 20	150	25	0.160AT
6	VTX-120-006-624	2 x 120	2 x 24	125	25	0.125AT
12	VTX-120-012-606	2 x 120	2 x 6	1000	15	1.00AT
12	VTX-120-012-609	2 x 120	2 x 9	666	15	0.630AT
12	VTX-120-012-612	2 x 120	2 x 12	500	15	0.500AT
12	VTX-120-012-615	2 x 120	2 x 15	400	15	0.400AT
12	VTX-120-012-618	2 x 120	2 x 18	333	15	0.350AT
12	VTX-120-012-620	2 x 120	2 x 20	300	15	0.315AT
12	VTX-120-012-624	2 x 120	2 x 24	250	15	0.250AT