

Safety Data Sheet

Artline

Xstamper

According to OSHA 29 CFR 1910.1200 HCS & Canada WHMIS

Revision Date: 28.05.2015

Artline519

SECTION 1: Identification

1.1. Product identifier

Product Name : Artline WHITEBOARD MARKER Color : (Black)

EK-517, EK-519

1.2. Recommended use of the chemical and restrictions on use

Recommended use : Whiteboard marker ink

1.3. Details of the supplier of the safety data sheet

Company Name : Shachihata Inc. (U.S.A.)

Address : 20775 S. Western Ave., Suite 105 Torrance, CA 90501 U.S.A.

Telephone : 1-800-541-9719 Fax : 1-800-541-7166

Contact (e-mail) : customerservice@xstamper.com



CHEMTREC 1-800-424-9300

(For Hazardous materials or dangerous goods incident, Spill, leak, fire, exposure or accident)

SECTION 2: Hazard(s) identification

United States (US): According to OSHA 29 CFR 1910.1200 HCS 2012

2.1.1 Classification of the substance or mixture

Flammable liquids, Category 2

Serious eye damage /eye irritation, Category 1

Specific target organ toxicity; single exposure, Category 3

H225

: Highly flammable liquid and vapour

H318
: Causes serious eye damage

: May cause drowsiness or dizziness

(narcotic effects)

2.1.2 Label elements

Hazard pictograms :







Signal word : Danger

Hazard statement : Highly flammable liquid and vapour (H225)

Causes serious eye damage (H318)
May cause drowsiness or dizziness (H336)

Precautionary statement

[Prevention]

Keep away from heat/sparks/open flames/hot surfaces. - No smoking. (P210)
Take precautionary measures against static discharge. (P243)
Wear protective gloves/protective clothing/eye protection/face protection. (P280)
Avoid breathing dust/fume/gas/mist/vapours/spray. (P261)
Use only outdoors or in a well-ventilated area. (P271)
Wash hands thoroughly after handling. (P264)

[Response]

In case of fire : Use dry chemical powder,form or carbon dioxide for extinction. (P370+P378)

IF INHALED : Remove victim to fresh air and keep at rest in a position comfortable for breathing. (P304+P340)

IF IN EYES : Rinse cautiously with water for several minutes. (P305+P351+P338)

Remove contact lenses, if present and easy to do. Continue rinsing.

If eye irritation persists : Get medical advice/attention. (P337+P313)

[ANSI Z400.1/Z129.1-2010][Shachihata Inc.] [EK-517_black_a] 2/6

IF ON SKIN (or hair) : Remove/Take off immediately all contaminated clothing. (P303+P361+P353)

Rinse skin with water/shower.

If skin irritation occurs : Get medical advice/attention. (P332+P313)

IF SWALLOWED : Get medical advice/attention if you feel unwell.Rinse mouth. (P301+P314+P330)

[Storage]

Store in a well-ventilated place. Keep container tightly closed. (P403+P233)

[Disposal]

Dispose of contents/container to waste in accordance with

local/regional/ national/international regulation (to be specified).

2.1.3 Other hazards

Under United States Regulations (29 CFR 1910.1200 - Hazard Communication Standard), this product is considered hazardous.

Canada : According to WHMIS

2.2.1 Classification of the substance or mixture

Class B2 : Flammable Liquids
Class D2B : Eye irritation

2.2.2 Label elements






2.2.3 Other hazards

In Canada, the product mentioned above is considered hazardous under the Workplace Hazardous Materials Information System (WHMIS)

2.3 Other information





(P501)

SECTION 3: Composition/information on ingredients

Substance/Mixture : Mixture

Ingredients :

Chemical Name / Composition C

Chemical Name /	Composition	CAS	Classification (OSHA HCS 2012)	
Generic name	weight %	Registry No.	Hazard Class	Hazard statement
Ethanol	20 ~ 30	64-17-5	Flam.Liq. 2	H225
Propan-2-ol	30 ~ 40	67-63-0	Flam.Liq. 2 Eye Irrit. 2 STOT.SE. 3	H225 H319 H336
Propan-1-ol	20 ~ 30	71-23-8	Flam.Liq. 2 Eye Dam. 1 STOT.SE. 3	H225 H318 H336
Carbon black	1 ~ 10	1333-86-4	none	none
Synthetic resin	1 ~ 10	Confidential	none	none
Additive	1 ~ 10	Confidential	none	none
total	100			

HMIS

SECTION 4: First-aid measures

4.1. Description of first aid measures

IF INHALED : Remove victim to fresh air and keep at rest in a position comfortable for breathing.

Consult a doctor if symptoms persist.

[ANSI Z400.1/Z129.1-2010][Shachihata Inc.] [EK-517_black_a] 3/6

IF ON SKIN : Remove/Take off immediately all contaminated clothing. Wash with soap and water.

If skin irritation/rash occurs or feel unwell, consult a doctor for medical advice.

IF IN EYES : Rinse cautiously with water for several minutes. Remove contact lenses, if present and

easy to do. Continue rinsing. If eye irritation persists, get medical advice/attention.

IF SWALLOWED : After rinse mouth immediately, give about 250 ml of water or milk and thin in the stomach,

and do not vomit forcibly. Moreover, do not give anything from the mouth to the patient

when not conscious. Receive the doctor's treatment (stomach pump) promptly.

Note to Physicians:

All treatments should be based on observed signs and symptoms of distress in the patient.

Consideration should be given to the possibility that overexposure to materials other than this product may have occurred.

SECTION 5: Fire-fighting measures

5.1. Extinguishing media

Suitable extinguishing media : Dry chemical powder, foam or carbon dioxide

Unsuitable extinguishing media : Water jet

5.2. Special hazards arising from the substance or mixture

For initial stage extinction, carbon dioxide or dry chemical powder.

When a fire extends, fire is extinguished by a large amount of water spray.

Do not discharge extinguishing waters into the aquatic environment.

5.3. Advice for firefighters

In the extinction work, an appropriate protective equipment (gloves, glasses, and mask) has to be worn.

Because during a fire, hazardous gases may be generated, fire-fighters have to wear self-contained breathing apparatus and other protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate personnel to safe area. Shut off all sources of ignition.

No Flares, smoking or flame in area. Put on protective equipment. Ensure adequate ventilation.

6.2. Environmental precautions

Do not throw the leakage thing directly into environment

6.3. Methods and material for containment and cleaning up

In case of a small spill, remove by absorbing with absorbents (sawdust, soil, sand, waste cloth,etc.),

and then wipe off the waste well with waste cloth, and rag.

In case of large spills, prevent leakage by enclosing with nonflammables (earth and sand, etc.)

and collect into empty container by scoop, suction equipment or the like.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling : Use with adequate ventilation.

Avoid contact with skin, eyes and clothing. Obtain special instructions before use.

Do not handle until all safety precautions have been read and understood.

Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage : Keep containers tightly closed and store in a cool and dry place.

areas and containers Keep away from heat and flame,ignition source and sunlight.

Keep out of the reach of children.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

ACGIH (2013)

Ethanol	STEL	1000ppm
Propan-2-ol	TWA	200ppm
Propan-1-ol	TWA	100ppm
Carbon black	TWA	3 mg/m ³

OSHA PEL

Ethanol TWA 1000ppm Propan-2-ol TWA 400ppm Propan-1-ol TWA 200ppm Carbon black TWA 3.5 mg/m^3

Canada Ontario Provincial

EthanolSTEL1000ppmPropan-2-olTWA200ppmPropan-1-olTWA100ppmCarbon blackTWA3.5 mg/m³

Canada Quebec Provincial

 Ethanol
 TWA
 1000ppm

 Propan-2-ol
 TWA
 400ppm

 Propan-1-ol
 TWA
 200ppm

 Carbon black
 TWA
 3.5 mg/m³

8.2. Exposure controls

Personal protective equipment

Respiratory Protection : Use with local exhaust ventilation, when in long use.

Avoid breathing vapours. Wear mask to prevent organic gas, if necessary.

Hand Protection : Avoid contact with hands. Wear safety gloves, if necessary. Eye Protection : Avoid contact with eyes. Wear safety glasses, if necessary.

Skin Protection : Avoid skin contact. Wear personal protection apron, boots, if necessary.

Environmental exposure controls

General advice : Prevent product from entering drains.

Prevent further leakage or spillage if safe to do so.

If the product contaminates rivers and lakes or drains inform respective authorities.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : black liquid

Odor : minor solvent odor pH : Not applicable

Boiling point : No data available

Flash point : 55.4 °F (13 °C) (closed cup)

Relative Density (at 77 °F, 25 °C) : $0.8 \sim 0.85$ (g/cm³)

Solubility in Water : Insoluble

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reaction known under conditions of normal use.

10.2. Possibility of hazardous reactions

Under normal conditions of storage and use, hazardous reactions will not occur.

10.3. Chemical stability

The product is stable.

10.4. Conditions to Avoid

High temperature, Direct sunlight, Fire

10.5. Incompatible Materials

No data available

10.6. Hazardous decomposition products

CO, CO₂

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : LD/LC50 values that are relevant for classification

[Ethanol]

Oral-rat LD50 7,060mg/kg Inhalation-rat LC50 20,000ppm/10h

[Propan-2-ol]

 Oral-rat
 LD50
 >5,000mg/kg

 Dermal-rabbit
 LD50
 >5,000mg/kg

[Propan-1-ol]

1,870mg/kg Oral-rat LD50 4,060mg/kg Dermal-rabbit LD50 Inhalation-rat LC50 4,000mg/l/4H

Serious eye damage /eye irritation : Category 1 Causes serious eye damage

Specific target organ toxicity : Category 3 May cause drowsiness or dizziness

(single exposure)

: Carbon black has been classified by the IARC as Group 2B. Carcinogenicity

> Other materials; Not contain any component that is considered a human carcinogen by IARC, ACGIH, EPA, EU or NTP.

Regarding the carcinogenicity of carbon black, International Agency for Research on Cancer (IARC) has classified as a group 2B. However, ACGIH(American Conference of Governmental Industrial Hygienists), EPA(Environmental Protection Agency), EU (European Chemicals Agency), NTP (National Toxicology Program, USA) in the classification of suspected carcinogenic to humans has not been done. Therefore, as the ink product we could not classify the carcinogenicity of GHS from that there is no sufficient data.

SECTION 12: Ecological information

12.1. Ecotoxicity : No data available : No data available 12.2. Persistence and degradability 12.3. Bioaccumulative potential : No data available 12.4. Mobility in soil : No data available

12.5. Other adverse effects : No known significant effects or critical hazards.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal must be made according to official regulations.

Comply with all Federal, State, and Local regulations regarding disposal.

Do not allow product to reach ground, any water course or sewage system.

SECTION 14: Transport information

14.1. UN number DOT, TDG, IMO / IMDG, IATA / ICAO : UN1210

14.2. UN proper shipping name DOT, TDG, IMO / IMDG, IATA / ICAO : PRINTING INK, flammable

14.3. Transport hazard class(es) DOT, TDG, IMO / IMDG, IATA / ICAO

> · Class 3 (Flammable liquids.)

Label

DOT, TDG, IMO / IMDG, IATA / ICAO 14.4. Packing group : II Marine pollutant 14.5. Environmental hazards : No **EMS Number** : F-E,S-D 14.6. Special precautions for user

14.7. Transport in bulk according to Annex II of : Not applicable.

MARPOL 73/78 and the IBC Code

**

Artline WHITEBOARD MARKER (EK-517, EK-519) is not a hazardous material by the special provision.

Artline WHITEBOARD MARKER (EK-517, EK-519) (The amount of ink: less than 10ml)

UN number : UN3175

: Solids containing Flammable Liquid. n.o.s. UN proper shipping name

IATA Special Provision A46 **IMDG** Code Special Provision 216

According to IATA Special Provision A46, and IMDG Code Special Provision 216, small inner packagings consisting of sealed packets and articles containing less than 10 mL of a Class 3 liquid in Packing Group II or III absorbed onto a solid material are not subject to as a hazardous material/dangerous goods provided there is no free liquid in the packet or article.



SECTION 15: Regulatory information

< USA Information >

OSHA STATUS : This product is hazardous under 29 CFR 1910.1200.

TSCA Hazard Communication Program (40 CFR Part 721) (SNUR) : not Listed EPCRA Section 302 Extremely Hazardous Substances (EHS) : not Listed EPCRA Section 313 Toxic Chemicals : not Listed CERCLA Hazardous Substances : not Listed CAA Section 112(r) List of Substances for Accidental Release Prevention : not Listed

California Proposition 65 : listed [carbon black]

< Canada Information >

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all the information required by the CPR.

WHMIS Ingredient Disclosure List (SOR/88-64) : Ethanol, Propan-2-ol, Propan-1-ol

(WHMIS: Canadian Workplace Hazardous Material Information System)

SECTION 16: Other information, including date of preparation or last revision

Last Revision Date :

Preparation Date : 28.05.2015



EU RoHS Directive(2002/95/EC) and ELV Directive(2000/53/EC) This product does not contain lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenylethers (PBDE).

This data sheet may not be enough when evaluating danger or hazard. The above information, which is created from currently available documents, information and data, may be revised when new findings announced. This document has been written on the assumption that when dealing with a large amount of ink on the business case and emergency. When handling as a normal product, please refer to the notes that is described in the produce or packaging. The information contained herein is not intended to provide any kind of warranty other than information, there is no guarantee for the accuracy of the content.