Section 1. Product and Company Identification.

1.1 Model Number; SCS014 v1

1.2 Description; White Grease Lubricant 500ml Pack of 6



1.3 Manufacturer;

Sealey Group. Kempson Way, Bury St. Edmunds, Suffolk. IP32 7AR

1.4 Emergency telephone number; 44 (0) 1284 757 500 (Office Hours)

Date of source compilation; 14 April 2014

Section 2. Hazards Identification.

2.1 Classification of the substance or mixture.

Risk phrases;

R11 Highly flammable

R12 Extremely flammable.

R38 Irritating to skin.

R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R67 Vapours may cause drowsiness and dizziness.

2.2 Label elements.

Hazard pictogram(s)







Hazard statements;

H315 Causes skin irritation.

H222 Extremely flammable aerosol.

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H304 May be fatal if swallowed and enters airways.

H336 May cause drowsiness or dizziness.

H411 Toxic to aquatic life with long lasting effects.



Section 2. Hazards Identification (continued)

Precautionary statements;

P102 Keep out of reach of children.

P271 Use only outdoors or in a well-ventilated area.

P261 Avoid breathing vapour/spray.

P280 Wear protective gloves.

P270 Do not eat, drink or smoke when using this product.

P302+352 IF ON SKIN: Wash with plenty of soap and water.

P501 Dispose of contents/container in accordance with local regulations.

Supplementary Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P211 Do not spray on an open flame or other ignition source.

P251 Pressurized container: Do not pierce or burn, even after use.

P273 Avoid release to the environment.

P264 Wash contaminated skin thoroughly after handling.

P321 Specific treatment (see medical advice on this label).

P304+340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P312 Call a POISON CENTER or doctor/physician if you feel unwell.

P332+313 If skin irritation occurs: Get medical advice/attention.

P362 Take off contaminated clothing and wash before reuse.

P391 Collect spillage.

P403+233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

P410+412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.

2.3 Other hazards.

No information available.



Section 3. Substances.

			Classification	
3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Volume	Hazard Class & Category Code	Hazard Statements
Naphtha (Petroleum),	64742-49-0	30 - 60%	Carc. 1B	H350
Hydrotreated Light			Asp. Tox. 1	H304
Propane	74-98-6	10 - 30%	Flam. Gas 1	H220
			Press. Gas	
Butane	106-97-8	10 - 30%	Flam. Gas 1	H220
			Press. Gas	
Isobutane	75-28-5	5 - 10%	Flam. Gas 1	H220
			Press. Gas	
Zinc Oxide	1314-13-2	1 - 5%	Aquatic Acute 1	H400
			Aquatic Chronic 1	H410

For full text of Phrases and Statements, see Section 16.



Section 4. First Aid Measures.

General information

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

4.1 Description of first aid measures

Eve Contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids.

Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

Skin Contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

Inhalation

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

- **4.2.** Most important symptoms and effects, both acute and delayed No information available.
- **4.3.** Indication of any immediate medical attention and special treatment needed No information available.

Section 5. Fire Fighting Measures.

5.1. Extinguishing media

Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

5.2. Special hazards arising from the substance or mixture Aerosol cans may explode in a fire.

5.3. Advice for fire-fighters

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.



Section 6. Accidental Release Measures.

6.1. Personal precautions, protective equipment and emergency procedures No information available.

6.2. Environmental precautions

No information available.

6.3. Methods and material for containment and cleaning up

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

6.4. Reference to other sections

See Section 7 for information on Safe Handling See Section 8 for information of Personal Protective Equipment. See Section 13 for information on disposal.

Section 7. Handling and Storage.

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact.

Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

7.3. Specific end use(s)

Intended for use as a White Grease Lubricant, Model Number identified in 1.1 with Description stated in 1.2.



Section 8. Exposure Controls/Personal Protection.

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min	
Butane	WEL	600 ppm	1450 mg/m ³	750 ppm	1810 mg/m ³
Isobutane	WEL	800 ppm		800 ppm	
Naphtha (Petroleum),			1200 mg/m ³	60 ppm	216 mg/m ³
Hydrotreated Light					
Propane		Asphyxiating	Asphyxiating	Asphyxiating	Asphyxiating

8.2. Exposure controls

Protective equipment





Eye/Face Protection

Use approved safety goggles or face shield.

Skin Protection

Use protective gloves.

Respiratory Protection

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use chemical cartridge protection with appropriate cartridge.

Ventilation

Provide adequate general and local exhaust ventilation.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

SEALEY

Section 9. Physical and Chemical Properties.

9.1. Information on basic physical and chemical properties

The following information is not a technical specification or sales specification.

(a) Appearance: Aerosol.
(b) Odour: Characteristic.

(c) Odour threshold;
No information available.
No information available.
No information available.

(e) Melting point/freezing point; No information available. (f) Initial boiling point and boiling range; No information available. (g) Flash point; No information available. (h) Evaporation rate; No information available. (i) Flammability (solid, gas); No information available. (j) Upper/lower flammability; Lower; 0.8% Upper; 9.0% (k) Vapour pressure; No information available. (I) Vapour density; No information available. No information available. (m) Relative density;

(m) Relative density;
No information available.
(n) Solubility(ies);
No information available.
(o) Partition coefficient: n-octanol/water;
No information available.
(p) Auto-ignition temperature;
No information available.
(q) Decomposition temperature;
No information available.
(r) Viscosity;
No information available.

(s) Explosive properties; No information available. (t) Oxidising properties. No information available.

Section 10. Stability and Reactivity.

10.5. Incompatible materials

10.1. Reactivity No information available.

10.2. Chemical stability Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions No information available.

10.4. Conditions to avoid Avoid heat, flames and other sources of ignition.

Avoid contact with: Strong oxidising agents. Strong

alkalis. Strong mineral acids. No information available.

10.6. Hazardous decomposition products Vapours/gases/fumes of: Carbon monoxide (CO).

Carbon diavida (CO3)

Carbon dioxide (CO2).



Section 11. Toxicological Information.

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Harmful by inhalation. Irritating to respiratory system.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

Skin contact

Harmful in contact with skin. Irritating to skin. Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin.

May cause cracking of skin, and eczema.

Eve contact

Irritating to eyes. May cause chemical eye burns.

Section 12. Ecological Information.

Dangerous for the environment if discharged into watercourses.

12.1. Toxicity	No information available.
12.2. Persistence and degradability	No information available.
12.3. Bioaccumulative potential	No information available.
12.4. Mobility in soil	No information available.
12.5. Results of PBT and vPvB assessment	No information available.
12.6. Other adverse effects	No information available.

Section 13. Disposal Considerations.

13.1. Waste treatment methods

Empty containers must not be burned because of explosion hazard.

Dispose of waste and residues in accordance with local authority requirements.



Section 14. Transport Information.

ADR. International Carriage of Dangerous Goods by Road.

14.1. UN number UN 1950

14.2. Name and Description AEROSOLS, flammable

Label 2.1

Special Provisions 190 344 625

Limited Quantities 1 L
Excepted Quantities E0

Packing Instructions P207, LP02 Special Packaging Provisions RR6 L2

14.3. Transport hazard class(es) Class 2

Classification Code 5F
Transport Category 2
Tunnel restriction code D

14.4. Packing group -

14.5. Environmental hazards Avoid release to the environment

14.6. Special precautions for user Refer to Section 2.2 Precautionary Statements

IATA. International Air Transport Association.

14.1. UN number UN 1950

14.2. UN Proper Shipping Name/Description AEROSOLS, flammable

Hazard Label. Flamm. gas

Excepted Quantity E0
Packaging Instructions Passenger 203

Ltd Qty Y203 Cargo 203 ERG Code 10L A167

Special Provisions

Special Provision A802.

Notwithstanding the absence of a packing group in column E, substances and article assigned to these entries must be packed in UN Specification packaging's that meet packing group II performance standards. This does not apply when aerosols are prepared for transport in accordance with the limited quantity provisions.

14.3. Transport hazard class(es) Class or Division 2.1

14.4. Packing group -

14.5. Environmental hazards Avoid release to the environment

14.6. Special precautions for user Refer to Section 2.2 Precautionary Statements

IMDG. International Maritime Dangerous Goods.

14.1. UN number UN 1950

14.2. UN proper shipping name AEROSOLS, flammable

Special Provisions 63, 190 277, 327, 344, 959 Limited Quantities See Special Provision 277

Excepted Quantities E0

Packaging Instructions P207, LP02 Packaging Provisions PP87, L2

14.3. Transport hazard class(es) Class or Division 2

Subsidiary Risk(s) See Special Provision 63

14.4. Packing group

14.5. Environmental hazards Avoid release to the environment

14.6. Special precautions for user
Refer to Section 2.2 Precautionary Statements
Bulk transport is not applicable to this product



Section 15. Regulatory Information.

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture No information available.

15.2. Chemical safety assessment No information available.

Section 16. Additional Information.

Full text of Phrases and Statements used in Section 3;

H220: Extremely flammable gas.

H304: May be fatal if swallowed and enters airways.

H350: May cause cancer.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

The above information is believed to be accurate and represents the best information currently available.

No warranty is expressed or implied by the above information.

We assume no liability resulting from use of the above information.

The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	12/02/16	First issue.
2	14/09/16	Sections 3, 14, 15 & 16

End of Safety Data Sheet.