



AIM & THURLBY THANDAR INSTRUMENTS

EL-R SERIES

Linear Bench Power Supplies

INSTRUCTION MANUAL

Aim-TTi

Table of Contents

Introduction	2
Specification	2
Safety	4
Installation	5
Connections	6
Operation - Main Outputs	6
Operation – Auxiliary Output	7
Operation - General	8
Maintenance	8
Instructions en Francais	
Sécurité	9
Installation	10
Connexions	11
Fonctionnement - Sorties principales	11
Fonctionnement – Sortie Auxiliaire	12
Fonctionnement - Généralités	13
Maintenance	13
Bedienungsanleitung auf Deutsch	
Sicherheit	14
Installation	15
Anschlüsse	16
Betrieb - Hauptausgänge	16
Betrieb – Hilfsausgang	17
Betrieb - Allgemein	18
Wartung	18
Istruzioni in Italiano	
Sicurezza	19
Installazione	20
Collegamenti	21
Funzionamento - Uscite principali	21
Funzionamento – Uscita Ausiliaria	22
Funzionamento - Generale	23
Manutenzione	23
Instrucciones en Español	
Seguridad	24
Instalación	25
Conexiones	26
Operación - Salidas principales	26
Operación – Salida Auxiliar	27
Operación - General	28
Mantenimiento	28

Introduction

The EL-R series provides medium levels of power (up to 125 watts) in a compact and attractive case style using linear regulation.

High resolution controls allow precise setting of voltage and current levels which are indicated on accurate and highly legible digital meters.

Excellent line and load regulation is matched by very low noise and good transient response. Improved power efficiency ensures that the units require no fan cooling. Remote sense terminals are provided so that good regulation can be maintained across remote loads at high current.

The EL302RD has two independent isolated outputs each with a 0 to 30V, 0 to 2A capability. The outputs operate in constant voltage or constant current mode with automatic crossover and mode indication. Each output has its own on-off switch. The outputs can be wired in either series or parallel to provide voltages up to 60 volts or currents up to 4 amps. The EL302RT has, in addition, an Auxiliary 'logic voltage' output with a 2A current capability. This output can be preset between 1.5 volts and 5 volts via a front panel control.

The EL155R, EL183R, EL301R, EL302R, EL303R and EL561R are single output supplies capable of supplying up to 15V/5A, 18V/3.3A, 30V/1A, 30V/2A, 30V/3A or 56V/1.1A respectively.

The EL-R series incorporates separate digital voltage and current meters on each output. The meters use bright 14mm (0.56") LED displays and have an update rate of 4 per second providing near instantaneous response. Simultaneous metering of voltage and current provides accurate information "at a glance" and avoids any possibility of misinterpretation. When an output switch is set to "off", the current limit setting is displayed enabling conditions to be set before the load is connected. With the right-hand main output off the right-hand meters can be used to momentarily display the preset Auxiliary voltage and current limit.

The EL-R series has been designed to meet the stringent requirements of relevant IEC standards for safety and EMC. All outputs are intrinsically short circuit proof, and are protected against external voltages and reverse currents.

Specification

MAIN OUTPUTS

Voltage Range:	0V to 15V minimum (EL155R) 0V to 18V minimum (EL183R) 0V to 30V minimum (EL301R, EL302R, EL303R, EL302RD, EL302RT) 0 to 56V minimum (EL561R)
Current Range:	0A to 1A minimum (EL301R) 0A to 1.1A minimum (EL561R) 0A to 2A minimum (EL302R, EL302RD, EL302RT) 0A to 3A minimum (EL303R) 0A to 3.3A minimum (EL183R) 0A to 5A minimum (EL155R)
Voltage Setting:	By coarse and fine controls.
Current Setting:	By single logarithmic control.
Operating Mode:	Constant voltage or constant current with automatic cross-over.
Output Switch:	Electronic. Preset voltage and current displayed when off.
Output Terminals:	Universal 4mm safety binding posts on 19mm (0.75") pitch.
Sensing:	Switchable between local and remote. Spring-loaded push terminals for remote connection.
Output Protection:	Outputs will withstand forward voltages of up to 20V above the rated output voltage. Reverse protection by diode clamp for currents up to 3A.

Load Regulation:	<0.01% of maximum output for 90% load change, using remote sense.
Line Regulation:	<0.01% of maximum output for 10% line change.
Ripple & Noise: (20MHz bandwidth)	Typically <1mVrms, constant voltage mode.
Transient Load Response:	<20µs to within 50mV of set level for 5% to 95% load change.
Temperature Coefficient:	Typically <100ppm/°C.
Status Indication:	Output on lamp. Constant current mode lamp.

METER SPECIFICATIONS (Main Outputs)

Meter Types:	Dual 4 digit meters with 14mm (0.56") LEDs. Reading rate 4 Hz.
Meter Resolutions:	10mV, 1mA.
Meter Accuracies:	Voltage 0.3% of reading ± 3 digits. Current 0.5% of reading ± 3 digits.

AUXILIARY LOGIC OUTPUT (EL302RT only)

Voltage:	Variable <1.5V to >5V by front panel control.
Meter Voltage Accuracy:	0.3% ± 4 digits.
Current Limit:	2A minimum.
Output Protection:	Output will withstand up to 7V forward voltage. Diode clamp reverse protection for currents up to 3A.
Ripple & Noise (20MHz bandwidth):	Typically <5mVrms, <15mVpk-pk (CV mode).
Load Regulation:	<3% for 90% load change.
Line Regulation:	<0.2% for 10% line voltage change.
Status Indication:	UNREG lamp.

GENERAL

AC Input:	230V AC or 115VAC ± 10%, 50/60Hz. Installation Category II.	
Power Consumption:	EL301R:	85VA max;
	EL302R/EL183R/EL561R:	160VA max;
	EL155R/EL303R:	275VA max;
	EL302RD/EL302RT:	320VA max.
Operating Range:	+5°C to +40°C, 20% to 80% RH.	
Storage Range:	-40°C to + 70°C.	
Environmental:	Indoor use at altitudes up to 2000m, Pollution Degree 2.	
Safety & EMC:	Complies with EN61010-1 & EN3126-1. For details, download the EU Declaration of Conformity for this instrument from http://www.aimtti.com/support (serial no. needed).	
Size:	Singles:	140 x 160 x 295 mm (WxHxD).
	Dual & Triple:	260 x 160 x 295 mm (WxHxD).
Weight:	EL301R:	3.1kg;
	EL302R/EL183R/EL561R:	4.1kg;
	EL155R/EL303R:	4.5kg;
	EL302RD/EL302RT:	7.4kg.

This power supply is a Safety Class I instrument according to IEC classification and has been designed to meet the requirements of EN61010-1 (Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use). It is an Installation Category II instrument intended for operation from a normal single phase supply.

This instrument has been tested in accordance with EN61010-1 and has been supplied in a safe condition. This instruction manual contains some information and warnings which have to be followed by the user to ensure safe operation and to retain the instrument in a safe condition.

This instrument has been designed for indoor use in a Pollution Degree 2 environment in the temperature range 5°C to 40°C, 20% - 80% RH (non-condensing). It may occasionally be subjected to temperatures between +5°C and -10°C without degradation of its safety. Do not operate while condensation is present.

Use of this instrument in a manner not specified by these instructions may impair the safety protection provided. Do not operate the instrument outside its rated supply voltages or environmental range.

WARNING! THIS INSTRUMENT MUST BE EARTHED

Any interruption of the mains earth conductor inside or outside the instrument will make the instrument dangerous. Intentional interruption is prohibited. The protective action must not be negated by the use of an extension cord without a protective conductor.






When the instrument is connected to its supply, terminals may be live and opening the covers or removal of parts (except those to which access can be gained by hand) is likely to expose live parts. The apparatus shall be disconnected from all voltage sources before it is opened for any adjustment, replacement, maintenance or repair. Capacitors inside the power supply may still be charged even if the power supply has been disconnected from all voltage sources but will be safely discharged about 1 minute after switching off power.

Any adjustment, maintenance and repair of the opened instrument under voltage shall be avoided as far as possible and, if inevitable, shall be carried out only by a skilled person who is aware of the hazard involved.

If the instrument is clearly defective, has been subject to mechanical damage, excessive moisture or chemical corrosion the safety protection may be impaired and the apparatus should be withdrawn from use and returned for checking and repair.

Make sure that only fuses with the required rated current and of the specified type are used for replacement. The use of makeshift fuses and the short-circuiting of fuse holders is prohibited.


Do not wet the instrument when cleaning it. The following symbols are used on the instrument and in this manual:-

	Earth (ground) terminal.
	mains supply OFF.
	mains supply ON.
	alternating current (ac)
	direct current (dc)

Mains Operating Voltage

Check that the instrument operating voltage marked on the rear panel is suitable for the local supply. Should it be necessary to change the operating voltage, proceed as follows:

1. Ensure that the instrument is disconnected from the AC supply.
2. Remove the screws holding the case upper and handle and lift off the case upper.
3. Change the transformer connections following the diagram below:



4. Re-assemble in the reverse order.
5. To comply with safety standard requirements the operating voltage marked on the rear panel must be changed to clearly show the new voltage setting.

Fuse

The AC fuse is located in the fuse drawer in the lower part of the IEC inlet connector. To change the fuse remove the line cord and open the fuse drawer with a suitable tool.

The correct fuse type is 20 x 5mm 250V HBC time-lag with the following rating:

Model	230V	115V
30V/1A	800mA (T)	1.6A (T)
30V/2A; 18V/3.3A; 56V/1.1A	1.25A (T)	2.5A (T)
30V/3A; 15V/5A	1.6A (T)	3.15A (T)
Dual and Triple	2.5A (T)	4A (T)

Make sure that only fuses with the required current rating and of the specified type are used for replacement. The use of makeshift fuses and the short-circuiting of fuseholders are prohibited.

Mains Lead

Connect the instrument to the AC supply using the mains lead provided. Should a mains plug be required for a different mains outlet socket, a suitably rated and approved mains lead set should be used which is fitted with the required wall plug and an IEC60320 C13 connector for the instrument end. To determine the minimum current rating of the lead-set for the intended AC supply, refer to the power rating information on the equipment or in the Specification.


WARNING! THIS INSTRUMENT MUST BE EARTHED.

Any interruption of the mains earth conductor inside or outside the instrument will make the instrument dangerous. Intentional interruption is prohibited.

All connections are made from the front panel.

The load should be connected to the positive (red) and negative (black) terminals marked OUTPUT. Both are fully floating and either can be connected to ground.

Remote sense connections to the load, if required, are made from the positive (+) and negative (–) SENSE terminals. Switch the LOCAL/REMOTE switch to REMOTE when remote sensing is required. Switch back to LOCAL when remote sensing is not in use.


The terminal marked  is connected to the chassis and safety earth ground.


Operation - Main Outputs

Switching On

The POWER switch is located at the bottom left of the front panel. When the POWER switch is turned on (I) the right hand meter briefly indicates the firmware revision before the display shows Volts and Amps.

Setting Up the Output

With the POWER switch on (I) and the  output OFF the output voltage and current limit can be accurately preset using the VOLTAGE and CURRENT controls; the left-hand meter shows the set voltage and the right-hand meter shows the set maximum current.

When the output switch is switched ON, the  lamp lights; the left-hand meter now shows the actual voltage and the right-hand meter the actual load current.

Constant Voltage

The output voltage is adjusted using the coarse and fine VOLTAGE controls; the CURRENT control sets the maximum current that can be supplied.

Constant Current

If the load resistance is low enough such that, at the output voltage set, a current greater than the current limit setting would flow, the power supply will automatically move into constant current operation.

The current output is adjusted by the CURRENT control and the VOLTAGE controls set the maximum voltage that can be generated.

The CC lamp lights to show constant current mode.

Instantaneous Current Output

The current limit control can be set to limit the continuous output current to levels down to 10mA. However, in common with all precision bench power supplies, a capacitor is connected across the output to maintain stability and good transient response. This capacitor charges to the output voltage and short-circuiting of the output will produce a current pulse as the capacitor discharges which is independent of the current limit setting.

Efficiency

To improve efficiency at low output levels the overhead voltage to the output regulators is automatically switched by a relay to a lower voltage; hysteresis at the threshold point prevents unnecessary switching when the output voltage is set at about that level. Apart from an audible 'click' the user will be unaware that the relay has switched; there will be no disturbance on the output. The higher power 15V/5A and 30V/3A models use electronic pre-regulation, instead of relay control, to maintain a low overhead voltage.

Protection

The output has intrinsic short-circuit protection and is protected from reverse voltages by a diode; the continuous reverse current must not exceed 3 Amps, although transients can be much higher.

In common with all series regulated single-ended power supplies, the unit is not capable of sinking current provided from an external source.

If a voltage greater than the set output voltage of the unit is applied from an external source, the internal regulator will turn off, no current will flow, and the voltage meter will read the applied voltage. No damage will result providing the applied voltage does not exceed the maximum output voltage of the power supply by more than 20 Volts. Application of a voltage greater than this is prohibited.

Remote Sensing

The unit has a very low output impedance, but this is inevitably increased by the resistance of the connecting leads. At high currents this can result in significant differences between the indicated source voltage and the actual load voltage (two 20m Ω connecting leads will drop 0.2V at 5 Amps, for instance). This problem can be minimised by using short, thick, connecting leads, but where necessary it can be completely overcome by using the remote sense facility.

This requires the sense terminals to be connected to the output at the load instead of at the source; insert wires into the spring-loaded SENSE terminals and connect directly to the load. Switch the LOCAL/REMOTE switch to REMOTE. To avoid instability and transient response problems, care must be taken to ensure good coupling between each output and sense lead. This can be done either by twisting the leads together or by using coaxially screened cable (sense through the inner). An electrolytic capacitor directly across the load connection point may also be beneficial.

The voltage drop in each output lead must not exceed 0.5 Volts.

Switch the LOCAL/REMOTE switch back to LOCAL when remote sensing is not in use.

Operation – Auxiliary Output

Output Voltage

The output voltage can be set between 1.5V and 5.0V using the front panel rotary adjustment beside the centre terminals. With the right-hand main output OFF, pressing the SHOW AUX PRESET button will display the AUX output voltage and current limit on the right-hand meters.

Current Limit

The output will go into current limit above 2A; the UNREG lamp lights in this condition.

Protection

The output has intrinsic short-circuit protection and is protected from reverse voltages by a diode; the continuous reverse current must not exceed 3 Amps, although transients can be much higher.


The output is protected against external forward voltages up to 16 Volts.

Connection to the Load

The load should be connected to the positive (red) and negative (black) output terminals. Both are fully floating and either can be connected to ground.

Series or Parallel Connection with Other Outputs

The outputs of the power supply are fully floating and may be used in series with other power supply units to generate high DC voltages up to 300V DC.

The maximum permissible voltage between any terminal and earth ground () is 300VDC; the maximum permissible voltage between either terminal of one output and any terminal of another output on the same supply is also 300VDC.

WARNING! Such voltages are exceedingly hazardous and great care should be taken to shield the output terminals for such use. On no account should the output terminals be touched when the unit is switched on under such use. All connections to the terminals must be made with the power switched off on all units.

It should be noted that the unit can only source current and cannot sink it, thus units cannot be series connected in anti-phase.

The unit can be connected in parallel with others to produce higher currents. Where several units are connected in parallel, the output voltage will be equal to that of the unit with the highest output voltage setting until the current drawn exceeds its current limit setting, upon which the output will fall to that of the next highest setting, and so on. In constant current mode, units can be connected in parallel to provide a current equal to the sum of the current limit settings.

Ventilation

The power supply can generate significant heat at full power. The supply relies on convection cooling only and it is therefore important that ventilation is never restricted if performance and safety are to be maintained.

Maintenance

The Manufacturers or their agents overseas will provide repair for any unit developing a fault. Where owners wish to undertake their own maintenance work, this should only be done by skilled personnel in conjunction with the service manual which may be purchased directly from the Manufacturers or their agents overseas.

Cleaning

If the PSU requires cleaning use a cloth that is only lightly dampened with water or a mild detergent. Polish the display window with a soft dry cloth.

WARNING! TO AVOID ELECTRIC SHOCK, OR DAMAGE TO THE PSU, NEVER ALLOW WATER TO GET INSIDE THE CASE. TO AVOID DAMAGE TO THE CASE OR DISPLAY WINDOW NEVER CLEAN WITH SOLVENTS.



Thurlby Thandar Instruments Ltd.

Glebe Road • Huntingdon • Cambridgeshire • PE29 7DR • England (United Kingdom)

Telephone: +44 (0)1480 412451 • Fax: +44 (0)1480 450409

International web site: www.aimtti.com • UK web site: www.aimtti.co.uk

Email: info@aimtti.com

