



SAFETY DATA SHEET
FOODLUBE CHAIN SPRAY

Page: 1

Compilation date: 09/09/2014

Revision No: 8

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: FOODLUBE CHAIN SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Chain Lubricant.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Aerosol 1: H222; -: H229

Classification under CHIP: F+: R12

Most important adverse effects: Extremely flammable aerosol. Pressurised container: May burst if heated.

2.2. Label elements

Label elements under CLP:

Hazard statements: H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

Signal words: Danger

Hazard pictograms: GHS02: Flame



Precautionary statements: P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P251: Pressurized container: Do not pierce or burn, even after use.

[cont...]

SAFETY DATA SHEET

FOODLUBE CHAIN SPRAY

Page: 2

P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P211: Do not spray on an open flame or other ignition source.

P285: In case of inadequate ventilation wear respiratory protection.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) - REACH registered number(s): EXEMPT

EINECS	CAS	CHIP Classification	CLP Classification	Percent
270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	50-70%

AMINIC PHENYL DERIVATIVE

270-128-1	68411-46-1	-	Aquatic Chronic 3: H412	<2%
-----------	------------	---	-------------------------	-----

PHOSPHATE ALKYL AMINE DERIVATIVE

279-632-6	80939-62-4	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Aquatic Chronic 2: H411	<2%
-----------	------------	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water. Do not induce vomiting.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Do not use water. Alcohol resistant foam. Dry chemical powder. Carbon dioxide. Use water spray to cool containers.

[cont...]

SAFETY DATA SHEET

FOODLUBE CHAIN SPRAY

Page: 3

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Extremely flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Do not use equipment in clean-up procedure which may produce sparks. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

[cont...]

SAFETY DATA SHEET

FOODLUBE CHAIN SPRAY

Page: 4

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Respiratory protection not normally required.

Hand protection: Protective gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Colourless

Odour: Barely perceptible odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Oily

Boiling point/range°C: <0

Melting point/range°C: <-100

Flammability limits %: lower: 1.8

upper: 9.4

Flash point°C: -100

Autoflammability°C: >200

Vapour pressure: >200

Relative density: <1

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

[cont...]

SAFETY DATA SHEET

FOODLUBE CHAIN SPRAY

Page: 5

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Highly volatile. Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET

FOODLUBE CHAIN SPRAY

Page: 6

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, Flammable

14.3. Transport hazard class(es)

Transport class: 2.1

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: Contains only FDA listed ingredients. NSF H1 registered.

EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

R12: Extremely flammable.

Legend to abbreviations: PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

[cont...]

SAFETY DATA SHEET
FOODLUBE CHAIN SPRAY

Page: 7

LC50 = median lethal concentration
EC50 = median effective concentration
IC50 = median inhibitory concentration
dw = dry weight
bw = body weight
cc = closed cup
oc = open cup
MUS = mouse
GPG = guinea pig
RBT = rabbit
HAM = hamster
HMN = human
MAM = mammal
PGN = pigeon
IVN = intravenous
SCU = subcutaneous
SKN = skin
DRM = dermal
OCC = ocular/corneal
PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide.

This company shall not be held liable for any damage resulting from handling or from contact with the above product.