





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		B2	NEW CAD-DRAWING CREATED	08MAY2003	-	-

D

C

B

A



1:1

- Bemerkungen
NOTES
- Geeignet für UMNL Stift- und Buchsenkontakte
BEEN SUITABLE FOR UMNL PIN- AND SOCKET CONTACTS
 - Empfohlene Blechstärke 0.75 - 2.3 mm
RECOMMEND SHEET METAL THICKNESS 0.75 - 2.3 mm
 - Gehäuse muß in Stanzrichtung eingeführt werden
HOUSING MUST BE INTRODUCED TO PUNCHING DIRECTION
 - Für verschlüsseltes Einsetzen der Gehäuse
FOR CODED USING OF THE HOUSINGS
 - Position von Kammer 1 bei verschlüsseltem Einsetzen
POSITION OF CAVITY 1 FOR CODED USING
 - Neues Material (Phosphor und Halogen frei)
NEW MATERIAL (PHOSPHORUS AND HALOGENEOUS FREE)

926681-5	B	PA6.6 UL94 V-2	natur/NATURAL
926681-4	B	PA6.6 UL94 V-2 DURETHAN VPKU2	weiß/WHITE
926681-3	B	PA6.6 UL94 V-0	6 natur/NATURAL
926681-2	A	PA6.6 UL94 V-0	6 schwarz/BLACK
926681-1	A	PA6.6 UL94 V-2 ZYTEL E101	natur/NATURAL
PART NO.	REV.	MATERIAL	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN Abraham.G. CHK Kampmann.H. APVD -	08MAY03 09MAY03 -	tyco Electronics AMP GmbH D - 64625 Bensheim	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 12-pol. UMNL Aufnahmegehäuse UMNL 12-WAY CAP HSG	
MATERIAL -		FINISH -		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO. 926681	
				RESTRICTED TO -	
				WEIGHT 9.5 g	
				CUSTOMER DRAWING	
				SCALE 2:1	
				SHEET 1 OF 1	
				REV. B2	