



**SAFETY DATA SHEET**  
FUELSEAL

Page: 1

Compilation date: 24/11/2014

Revision No: 2

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** FUELSEAL

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Jointing compound.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** STOT SE 3: H336; Eye Irrit. 2: H319; Flam. Liq. 2: H225; Skin Sens. 1: H317

**Most important adverse effects:** Highly flammable liquid and vapour. May cause an allergic skin reaction. Causes serious eye irritation. May cause drowsiness or dizziness.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H225: Highly flammable liquid and vapour.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark



[cont...]

# SAFETY DATA SHEET

FUELSEAL

Page: 2

**Signal words:** Danger

**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P241: Use explosion-proof electrical/ventilating/lighting/.. equipment.  
P243: Take precautionary measures against static discharge.  
P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.  
P264: Wash thoroughly after handling.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P302+352: IF ON SKIN: Wash with plenty of water/.  
P303+361+353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.  
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P333+313: If skin irritation or rash occurs: Get medical advice/attention.  
P337+313: If eye irritation persists: Get medical advice/attention.  
P403+233: Store in a well-ventilated place. Keep container tightly closed.  
P501: Dispose of contents/container to local/national regulations.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

##### CHINA CLAY

EINECS	CAS	PBT / WEL	CLP Classification	Percent
310-194-1	1332-58-7	Substance with a Community workplace exposure limit.	-	30-50%

##### PROPAN-2-OL

200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	10-30%
-----------	---------	---	---	--------

##### PINE TAR

232-374-8	8011-48-1	-	Skin Sens. 1: H317	<2%
-----------	-----------	---	--------------------	-----

[cont...]

# SAFETY DATA SHEET

FUELSEAL

Page: 3

XYLENE

215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	<2%
-----------	-----------	---	--	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Use water spray to cool containers. Dry chemical powder. Alcohol resistant foam. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Eliminate all sources of ignition. Do not attempt to take action without suitable protective clothing - see section 8 of SDS.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

[cont...]

# SAFETY DATA SHEET

FUELSEAL

Page: 4

## 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Clean-up should be dealt with only by qualified personnel familiar with the specific substance. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

## 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Smoking is forbidden. Use non-sparking tools.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep away from sources of ignition. Keep container tightly closed.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**CHINA CLAY**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	2.0 mg/m <sup>3</sup>	-	-	-

**PROPAN-2-OL**

UK	400 ppm, 999 mg/m <sup>3</sup>	500 ppm, 1250 mg/m <sup>3</sup>	-	-
----	--------------------------------	---------------------------------	---	---

**XYLENE**

UK	220 mg/m <sup>3</sup>	441 mg/m <sup>3</sup>	-	-
----	-----------------------	-----------------------	---	---

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

**Respiratory protection:** Respiratory protection not normally required.

**Hand protection:** Nitrile gloves.

**Eye protection:** Safety glasses with side-shields. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

[cont...]

# SAFETY DATA SHEET

FUELSEAL

Page: 5

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Red-brown

**Odour:** Characteristic odour

**Evaporation rate:** Fast

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Slightly soluble

**Viscosity:** Viscous

**Melting point/range°C:** < 0

**Flash point°C:** <21

**Autoflammability°C:** > 200

**Relative density:** > 1

**pH:** Approx. 7

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat. Direct sunlight.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

[cont...]

# SAFETY DATA SHEET

FUELSEAL

Page: 6

## PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg

## XYLENE

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

### Relevant hazards for substance:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

## Section 12: Ecological information

### 12.1. Toxicity

#### Hazardous ingredients:

##### CHINA CLAY

ALGAE	72H IC50	> 1000	mg/l
DAPHNIA	48H EC50	> 1000	mg/l
FISH	96H LC50	> 1000	mg/l

### 12.2. Persistence and degradability

**Persistence and degradability:** Only slightly biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Volatile. Readily absorbed into soil.

[cont...]

# SAFETY DATA SHEET

FUELSEAL

Page: 7

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

## 12.6. Other adverse effects

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1993

### 14.2. UN proper shipping name

**Shipping name:** FLAMMABLE LIQUID, N.O.S.  
(contains propan-2-ol, xylene)

### 14.3. Transport hazard class(es)

**Transport class:** 3

### 14.4. Packing group

**Packing group:** II

### 14.5. Environmental hazards

**Environmentally hazardous:** No

**Marine pollutant:** No

### 14.6. Special precautions for user

**Tunnel code:** D/E

**Transport category:** 2

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** H225: Highly flammable liquid and vapour.

[cont...]

## SAFETY DATA SHEET

FUELSEAL

Page: 8

H226: Flammable liquid and vapour.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H336: May cause drowsiness or dizziness.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.