

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Auto-Intensiv-Reiniger 500ml
Art.: 1546

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture:

Vehicle cleansing

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH, Jerg-Wieland-Straße 4, D-89081 Ulm-Lehr
Telephone (+49) 0731-1420-0, Fax (+49) 0731-1420-88

E-mail address of the competent person: info@chemical-check.de, k.schnurbusch@chemical-check.de

1.4 Emergency telephone

Advisory office in case of poisoning:

Telephone number of the company in case of emergencies:

Tel.: (+49) 0731-1420-0

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) 1272/2008 (CLP)

Not determined

2.1.2 Classification according to Directives 67/548/EEC and 1999/45/EC (including amendments).

The mixture is not classified as dangerous in the terms of the directive 1999/45/EC.

2.2 Label elements

2.2.1 Labeling according to Regulation (EC) 1272/2008 (CLP)

Not determined

2.2.2 Labeling according to Directives 67/548/EEC and 1999/45/EC (including amendments).

Symbols: Not applicable

Indications of danger: ---

R-phrases:

S-phrases:

Additions: n.a.

2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

Page 2 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revised on / Version: 19.04.2012 / 0013
Replaces revision of / Version: 19.01.2011 / 0012
Valid from: 19.04.2012
PDF print date: 19.04.2012
Auto-Intensiv-Reiniger 500ml Art.: 1546

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

REGULATION (EC) No 648/2004

less than 5 %
amphoteric surfactants
anionic surfactants
non-ionic surfactants

perfumes
BENZISOTHIAZOLINONE
METHYLISOTHIAZOLINONE

SECTION 3: Composition/information on ingredients

3.1 Substance

n.a.

3.2 Mixture

--	
Registration number (REACH)	--
Index	-
EINECS, ELINCS, NLP	-
CAS	-
content %	
Classification according to Directive 67/548/EEC	---
Classification according to Regulation (EC) 1272/2008 (CLP)	---

SECTION 4: First aid measures

4.1 Description of first aid measures

Inhalation

Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.

Give copious water to drink - consult doctor immediately.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

4.3 Indication of any immediate medical attention and special treatment needed

n.c.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Adapt to the nature and extent of fire.

Unsuitable extinguishing media

n.c.

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Page 3 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revised on / Version: 19.04.2012 / 0013
Replaces revision of / Version: 19.01.2011 / 0012
Valid from: 19.04.2012
PDF print date: 19.04.2012
Auto-Intensiv-Reiniger 500ml Art.: 1546

Oxides of carbon
Oxides of sulphur
Oxides of nitrogen
Toxic gases

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.
Protective respirator with independent air supply.
Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Ensure sufficient supply of air.
Avoid contact with eyes or skin.
If applicable, caution - risk of slipping

6.2 Environmental precautions

If leakage occurs, dam up.
Prevent surface and ground-water infiltration, as well as ground penetration.
Prevent from entering drainage system.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.
Diluting with water is possible.
Flush residue using copious water.

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Ensure good ventilation.
Avoid contact with eyes or skin.
Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.
Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.
Wash hands before breaks and at end of work.
Keep away from food, drink and animal feedingstuffs.
Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.
Store product closed and only in original packing.
Protect from frost.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.
If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.

Page 4 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 19.04.2012 / 0013
 Replaces revision of / Version: 19.01.2011 / 0012
 Valid from: 19.04.2012
 PDF print date: 19.04.2012
 Auto-Intensiv-Reiniger 500ml Art.: 1546

Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.
 Wash hands before breaks and at end of work.
 Keep away from food, drink and animal feedingstuffs.
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:
 If there is a risk of contact with the eyes or while decanting:
 Tight fitting protective goggles with side protection (EN 166).

Skin protection - Hand protection:
 Chemical resistant protective gloves (EN 374).
 If applicable
 Rubber gloves (EN 374).
 Protective hand cream recommended.

Skin protection - Other:
 Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments)

Respiratory protection:
 Normally not necessary.

Thermal hazards:
 Not applicable

Additional information on hand protection - No tests have been performed.
 In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.
 Selection of materials derived from glove manufacturer's indications.
 Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.
 Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.
 In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.
 The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Light yellow
Odour:	Characteristic
Odour threshold:	Not determined
pH-value:	8,9 (20°C)
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	>100 °C
Flash point:	n.a.
Evaporation rate:	Not determined
Flammability (solid, gas):	Not determined
Lower explosive limit:	n.a.
Upper explosive limit:	n.a.
Vapour pressure:	Not determined
Vapour density (air = 1):	Not determined
Density:	1,051 g/cm ³ (20°C)
Bulk density:	Not determined
Solubility(ies):	Not determined
Water solubility:	Mixable
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	No
Decomposition temperature:	Not determined

Page 5 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 19.04.2012 / 0013
 Replaces revision of / Version: 19.01.2011 / 0012
 Valid from: 19.04.2012
 PDF print date: 19.04.2012
 Auto-Intensiv-Reiniger 500ml Art.: 1546

Viscosity: Not determined
 Explosive properties: Product is not explosive.
 Oxidising properties: Not determined

9.2 Other information

Miscibility: Not determined
 Fat solubility / solvent: Not determined
 Conductivity: Not determined
 Surface tension: Not determined
 Solvents content: Not determined

SECTION 10: Stability and reactivity

10.1 Reactivity

Not to be expected

10.2 Chemical stability

Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

None known

10.5 Incompatible materials

None known

10.6 Hazardous decomposition products

See also section 5.2

No decomposition when used as directed.

SECTION 11: Toxicological information

Auto-Intensiv-Reiniger 500ml Art.: 1546

Toxicity/effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:						n.d.a.
Acute toxicity, by dermal route:						n.d.a.
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin sensitisation:						n.d.a.
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity - single exposure (STOT-SE):						n.d.a.
Specific target organ toxicity - repeated exposure (STOT-RE):						n.d.a.
Aspiration hazard:						n.d.a.
Respiratory tract irritation:						n.d.a.
Repeated dose toxicity:						n.d.a.
Symptoms:						n.d.a.
Other toxicity data:						Classification according to calculation procedure.
Other toxicity data:						According to current knowledge that mixture does not endanger man under normal conditions of application.

SECTION 12: Ecological information

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 19.04.2012 / 0013
 Replaces revision of / Version: 19.01.2011 / 0012
 Valid from: 19.04.2012
 PDF print date: 19.04.2012
 Auto-Intensiv-Reiniger 500ml Art.: 1546

Auto-Intensiv-Reiniger 500ml							
Art.: 1546							
Toxicity/effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
Toxicity to fish:							n.d.a.
Toxicity to daphnia:							n.d.a.
Toxicity to algae:							n.d.a.
Persistence and degradability:							The surfactant(s) contained in this mixture complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents., Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
Bioaccumulative potential:							n.d.a.
Mobility in soil:							n.d.a.
Results of PBT and vPvB assessment							n.d.a.
Other adverse effects:							n.d.a.
Other ecotoxicological data:							According to the recipe, contains no AOX.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2001/118/EC, 2001/119/EC, 2001/573/EC)

20 01 30 detergents other than those mentioned in 20 01 29

Recommendation:

Pay attention to local and national official regulations

E.g. dispose at suitable refuse site.

E.g. suitable incineration plant.

For contaminated packing material

Pay attention to local and national official regulations

Empty container completely.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

Uncontaminated packaging can be recycled.

Recommended cleaner:

Water

SECTION 14: Transport information

General statements

UN number:

n.a.

Transport by road/by rail (ADR/RID)

Page 7 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revised on / Version: 19.04.2012 / 0013
 Replaces revision of / Version: 19.01.2011 / 0012
 Valid from: 19.04.2012
 PDF print date: 19.04.2012
 Auto-Intensiv-Reiniger 500ml Art.: 1546

UN proper shipping name:	
Transport hazard class(es):	n.a.
Packing group:	n.a.
Classification code:	n.a.
LQ (ADR 2011):	n.a.
LQ (ADR 2009):	n.a.
Environmental hazards:	Not applicable
Tunnel restriction code:	

Transport by sea (IMDG-code)

UN proper shipping name:	
Transport hazard class(es):	n.a.
Packing group:	n.a.
Marine Pollutant:	n.a.
Environmental hazards:	Not applicable

Transport by air (IATA)

UN proper shipping name:	
Transport hazard class(es):	n.a.
Packing group:	n.a.
Environmental hazards:	Not applicable

Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

For classification and labelling see Section 2.

Observe restrictions:	n.a.
-----------------------	------

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

These details refer to the product as it is delivered.

Revised sections:	2, 3, 8, 10, 11, 12, 13, 16
-------------------	-----------------------------

Any abbreviations and acronyms used in this document:

AC Article Categories
 acc., acc. to according, according to
 ACGIH American Conference of Governmental Industrial Hygienists
 ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)
 AOEL Acceptable Operator Exposure Level
 AOX Adsorbable organic halogen compounds
 approx. approximately
 Art., Art. no. Article number
 ATE Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)
 BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)
 BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
 BCF Bioconcentration factor
 BGV Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)
 BHT Butylhydroxytoluol (= 2,6-Di-*t*-butyl-4-methyl-phenol)
 BMGV Biological monitoring guidance value (EH40, UK)
 BOD Biochemical oxygen demand
 BSEF Bromine Science and Environmental Forum
 bw body weight

CAS	Chemical Abstracts Service
CESIO	Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques
CIPAC	Collaborative International Pesticides Analytical Council
CLP	Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
CMR	carcinogenic, mutagenic, reproductive toxic
COD	Chemical oxygen demand
CTFA	Cosmetic, Toiletry, and Fragrance Association
DMEL	Derived Minimum Effect Level
DNEL	Derived No Effect Level
DOC	Dissolved organic carbon
DT50	Dwell Time - 50% reduction of start concentration
DVS	Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)
dw	dry weight
e.g.	for example (abbreviation of Latin 'exempli gratia'), for instance
EC	European Community
ECHA	European Chemicals Agency
EEA	European Economic Area
EEC	European Economic Community
EINECS	European Inventory of Existing Commercial Chemical Substances
ELINCS	European List of Notified Chemical Substances
EN	European Norms
EPA	United States Environmental Protection Agency (United States of America)
ERC	Environmental Release Categories
ES	Exposure scenario
etc.	et cetera
EU	European Union
EWC	European Waste Catalogue
Fax.	Fax number
gen.	general
GHS	Globally Harmonized System of Classification and Labelling of Chemicals
GWP	Global warming potential
HET-CAM	Hen's Egg Test - Chorionallantoic Membrane
HGWP	Halocarbon Global Warming Potential
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IBC	Intermediate Bulk Container
IBC (Code)	International Bulk Chemical (Code)
IC	Inhibitory concentration
IMDG-code	International Maritime Code for Dangerous Goods
incl.	including, inclusive
IUCLID	International Uniform Chemical Information Database
LC	lethal concentration
LC50	lethal concentration 50 percent kill
LCLo	lowest published lethal concentration
LD	Lethal Dose of a chemical
LD50	Lethal Dose, 50% kill
LDLo	Lethal Dose Low
LOAEL	Lowest Observed Adverse Effect Level
LOEC	Lowest Observed Effect Concentration
LOEL	Lowest Observed Effect Level
LQ	Limited Quantities
MARPOL	International Convention for the Prevention of Marine Pollution from Ships
n.a.	not applicable
n.av.	not available
n.c.	not checked
n.d.a.	no data available
NIOSH	National Institute of Occupational Safety and Health (United States of America)
NOAEC	No Observed Adverse Effective Concentration
NOAEL	No Observed Adverse Effect Level
NOEC	No Observed Effect Concentration
NOEL	No Observed Effect Level
ODP	Ozone Depletion Potential
OECD	Organisation for Economic Co-operation and Development

org.	organic
PAH	polycyclic aromatic hydrocarbon
PBT	persistent, bioaccumulative and toxic
PC	Chemical product category
PE	Polyethylene
PNEC	Predicted No Effect Concentration
POCP	Photochemical ozone creation potential
ppm	parts per million
PROC	Process category
PTFE	Polytetrafluorethylene
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)
REACH-IT List-No.	9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
RID	Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)
SADT	Self-Accelerating Decomposition Temperature
SAR	Structure Activity Relationship
SU	Sector of use
SVHC	Substances of Very High Concern
Tel.	Telephone
ThOD	Theoretical oxygen demand
TOC	Total organic carbon
TRGS	Technische Regeln für Gefahrstoffe (=Technical Regulations for Hazardous Substances)
VbF	Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))
VOC	Volatile organic compounds
vPvB	very persistent and very bioaccumulative
WEL-TWA, WEL-STEL	WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).
WHO	World Health Organization
wwt	wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.

No responsibility.

These statements were made by:

Chemical Check GmbH, Wöbbeler Straße 2-4, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.