

Page 1 of 9  
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
Revised on / Version: 15.10.2012 / 0004  
Replaces revision of / Version: 19.01.2011 / 0003  
Valid from: 15.10.2012  
PDF print date: 23.10.2012  
RACING BIKE OIL-ADDITIV 125ML Art.: 1580

## Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

**RACING BIKE OIL-ADDITIV 125ML**

**Art.: 1580**

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

**Relevant identified uses of the substance or mixture:**

Lubricant

**Uses advised against:**

No information available at present.

#### 1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH, Jerg-Wieland-Straße 4, D-89081 Ulm-Lehr  
Telephone (+49) 0731-1420-0, Fax (+49) 0731-1420-88

E-mail address of the competent person: info@chemical-check.de, k.schnurbusch@chemical-check.de

#### 1.4 Emergency telephone

**Emergency information services / official advisory body:**

**Telephone number of the company in case of emergencies:**

Tel.: (+49) 0731-1420-0

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### 2.1.1 Classification according to Regulation (EC) 1272/2008 (CLP)

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

##### 2.1.2 Classification according to Directives 67/548/EEC and 1999/45/EC (including amendments)

The mixture is not classified as dangerous in the terms of the directive 1999/45/EC.

#### 2.2 Label elements

##### 2.2.1 Labeling according to Regulation (EC) 1272/2008 (CLP)

Not applicable

#### 2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

Product can compose a film on the water surface, which can prevent oxygen exchange.

### SECTION 3: Composition/information on ingredients

#### 3.1 Substance

n.a.

#### 3.2 Mixture

--

Page 2 of 9  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 15.10.2012 / 0004  
 Replaces revision of / Version: 19.01.2011 / 0003  
 Valid from: 15.10.2012  
 PDF print date: 23.10.2012  
 RACING BIKE OIL-ADDITIV 125ML Art.: 1580

<b>Registration number (REACH)</b>	--
<b>Index</b>	-
<b>EINECS, ELINCS, NLP</b>	-
<b>CAS</b>	-
<b>content %</b>	
<b>Classification according to Directive 67/548/EEC</b>	---
<b>Classification according to Regulation (EC) 1272/2008 (CLP)</b>	---

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### Inhalation

Remove person from danger area.  
 Supply person with fresh air and consult doctor according to symptoms.

#### Skin contact

Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

#### Eye contact

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

#### Ingestion

Rinse the mouth thoroughly with water.  
 Do not induce vomiting - give copious water to drink. Consult doctor immediately.

### 4.2 Most important symptoms and effects, both acute and delayed

Product removes fat.  
 Drying of the skin.  
 Dermatitis (skin inflammation)

### 4.3 Indication of any immediate medical attention and special treatment needed

Indications for the physician:  
 Symptomatic treatment

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

CO2  
 Dry extinguisher  
 Foam  
 Cool container at risk with water.

#### Unsuitable extinguishing media

High volume water jet

### 5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:  
 Oxides of carbon  
 Oxides of sulphur  
 Toxic pyrolysis products.  
 Hot product gives off combustible vapours.

### 5.3 Advice for firefighters

Protective respirator with independent air supply.  
 According to size of fire  
 Full protection, if necessary  
 Dispose of contaminated extinction water according to official regulations.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

Ensure sufficient supply of air.

GB

Page 3 of 9  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 15.10.2012 / 0004  
 Replaces revision of / Version: 19.01.2011 / 0003  
 Valid from: 15.10.2012  
 PDF print date: 23.10.2012  
 RACING BIKE OIL-ADDITIV 125ML Art.: 1580

Avoid formation of oil mist.  
 Avoid contact with eyes or skin.  
 If applicable, caution - risk of slipping  
 Do not carry cleaning cloths soaked in product in trouser pockets.

### 6.2 Environmental precautions

If leakage occurs, dam up.  
 Resolve leaks if this possible without risk.  
 Prevent from entering drainage system.  
 Prevent surface and ground-water infiltration, as well as ground penetration.

### 6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent) and dispose of according to Section 13.

### 6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

## SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

### 7.1 Precautions for safe handling

#### 7.1.1 General recommendations

Ensure good ventilation.  
 Do not heat to temperatures close to flash point.  
 Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.  
 Observe directions on label and instructions for use.

#### 7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.  
 Wash hands before breaks and at end of work.  
 Keep away from food, drink and animal feedingstuffs.  
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

### 7.2 Conditions for safe storage, including any incompatibilities

Store product closed and only in original packing.  
 Not to be stored in gangways or stair wells.  
 Solvent resistant floor  
 Do not store with oxidizing agents.  
 Store in a well ventilated place.  
 Protect from direct sunlight and warming.

### 7.3 Specific end use(s)

No information available at present.

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

Chemical Name	Oil mist, mineral	Content %:
WEL-TWA: 5 mg/m3 (ACGIH)	WEL-STEL: 10 mg/m3 (ACGIH)	---
BMGV: ---	Other information: ---	
Chemical Name	Baseoil - unspecified	Content %:
WEL-TWA: 300 mg/m3 (AGW)	WEL-STEL: 2(II) (AGW)	---
BMGV: ---	Other information: ---	
Chemical Name	Molybdenum disulphide	Content %:
WEL-TWA: 10 mg/m3 (molybdenum insoluble compounds, as Mo)	WEL-STEL: 20 mg/m3 (molybdenum insoluble compounds, as Mo)	---
BMGV: ---	Other information: ---	

WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period) EH40. AGW = "Arbeitsplatzgrenzwert" (workplace limit value, Germany). | WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period). | BMGV = Biological monitoring guidance value EH40. BGW = "Biologischer Grenzwert" (biological limit value, Germany) | Other information: Sen = Capable of causing occupational asthma. Sk = Can be absorbed through skin. Carc = Capable of causing cancer

and/or heritable genetic damage.

\*\* = The exposure limit for this substance is repealed through the TRGS 900 (Germany) of January 2006 with the goal of revision.

## 8.2 Exposure controls

### 8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.  
If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.  
Applies only if maximum permissible exposure values are listed here.

### 8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.  
Wash hands before breaks and at end of work.  
Keep away from food, drink and animal feedingstuffs.  
Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:  
Tight fitting protective goggles with side protection (EN 166).

Skin protection - Hand protection:  
Protective gloves, oil resistant (EN 374)  
If applicable  
Protective nitrile gloves (EN 374)  
Protective Neopren gloves (EN 374).  
Protective hand cream recommended.

Skin protection - Other:  
Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments)

Respiratory protection:  
Normally not necessary.  
With oil mist formation:  
Filter A P 3 (EN 14387), code colour brown, white

Thermal hazards:  
If applicable, these are included in the individual protective measures (eye/face protection, skin protection, respiratory protection).

Additional information on hand protection - No tests have been performed.  
In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.  
Selection of materials derived from glove manufacturer's indications.  
Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.  
Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.  
In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.  
The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

### 8.2.3 Environmental exposure controls

No information available at present.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Black
Odour:	Characteristic
Odour threshold:	Not determined
pH-value:	n.a.
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	Not determined
Flash point:	201 °C
Evaporation rate:	Not determined
Flammability (solid, gas):	Not determined
Lower explosive limit:	Not determined

Page 5 of 9  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 15.10.2012 / 0004  
 Replaces revision of / Version: 19.01.2011 / 0003  
 Valid from: 15.10.2012  
 PDF print date: 23.10.2012  
 RACING BIKE OIL-ADDITIV 125ML Art.: 1580

Upper explosive limit:	Not determined
Vapour pressure:	Not determined
Vapour density (air = 1):	Not determined
Density:	0,9 g/ml (20°C)
Bulk density:	Not determined
Solubility(ies):	Not determined
Water solubility:	Insoluble
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	Not determined
Decomposition temperature:	Not determined
Viscosity:	95 mm <sup>2</sup> /s (40°C)
Explosive properties:	Not determined
Oxidising properties:	No

## 9.2 Other information

Miscibility:	Not determined
Fat solubility / solvent:	Not determined
Conductivity:	Not determined
Surface tension:	Not determined
Solvents content:	Not determined

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

See also Subsection 10.4 to 10.6.  
The product has not been tested.

### 10.2 Chemical stability

See also Subsection 10.4 to 10.6.  
Stable with proper storage and handling.

### 10.3 Possibility of hazardous reactions

See also Subsection 10.4 to 10.6.

### 10.4 Conditions to avoid

See also section 7.  
Strong heat

### 10.5 Incompatible materials

See also section 7.  
Avoid contact with strong oxidizing agents.

### 10.6 Hazardous decomposition products

See also Subsection 10.4 to 10.6.  
See also section 5.2

## SECTION 11: Toxicological information

Possibly more information on health effects, see Section 2.1 (classification).

### RACING BIKE OIL-ADDITIV 125ML

Art.: 1580

Toxicity/effect	Endpoint t	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:						n.d.a.
Acute toxicity, by dermal route:						n.d.a.
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin sensitisation:						n.d.a.
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity - single exposure (STOT-SE):						n.d.a.

Page 6 of 9  
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
 Revised on / Version: 15.10.2012 / 0004  
 Replaces revision of / Version: 19.01.2011 / 0003  
 Valid from: 15.10.2012  
 PDF print date: 23.10.2012  
 RACING BIKE OIL-ADDITIV 125ML Art.: 1580

Specific target organ toxicity - repeated exposure (STOT-RE):						n.d.a.
Aspiration hazard:						n.d.a.
Respiratory tract irritation:						n.d.a.
Repeated dose toxicity:						n.d.a.
Symptoms:						n.d.a.
Other information:						Classification according to calculation procedure.

Molybdenum disulphide						
Toxicity/effect	Endpoint t	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:	LD50	>2000	mg/kg	Rat		
Acute toxicity, by dermal route:	LD50	>2000	mg/kg	Rat		
Skin corrosion/irritation:				Rabbit		Not irritant
Serious eye damage/irritation:				Rabbit		Mild irritant
Respiratory or skin sensitisation:				Guinea pig	OECD 406 (Skin Sensitisation)	Not sensitising
Germ cell mutagenicity:					OECD 471 (Bacterial Reverse Mutation Test)	Negative
Symptoms:						mucous membrane irritation

## SECTION 12: Ecological information

Possibly more information on environmental effects, see Section 2.1 (classification).

RACING BIKE OIL-ADDITIV 125ML Art.: 1580							
Toxicity/effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
Toxicity to fish:							n.d.a.
Toxicity to daphnia:							n.d.a.
Toxicity to algae:							n.d.a.
Persistence and degradability:							Potentially biologically degradable.
Bioaccumulative potential:							n.d.a.
Mobility in soil:							n.d.a.
Results of PBT and vPvB assessment:							n.d.a.
Other adverse effects:							n.d.a.
Other information:							According to the recipe, contains no AOX.

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### For the substance / mixture / residual amounts

Soaked polluted cloths, paper or other organic materials represent a fire hazard and should be controlled, collected and disposed of.  
EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2001/118/EC, 2001/119/EC, 2001/573/EC)

13 02 05 mineral-based non-chlorinated engine, gear and lubricating oils

Recommendation:

Pay attention to local and national official regulations

Implement substance recycling.

E.g. suitable incineration plant.

#### For contaminated packing material

Pay attention to local and national official regulations

Empty container completely.

Page 7 of 9  
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
Revised on / Version: 15.10.2012 / 0004  
Replaces revision of / Version: 19.01.2011 / 0003  
Valid from: 15.10.2012  
PDF print date: 23.10.2012  
RACING BIKE OIL-ADDITIV 125ML Art.: 1580

Uncontaminated packaging can be recycled.  
Dispose of packaging that cannot be cleaned in the same manner as the substance.

## SECTION 14: Transport information

### General statements

UN number: n.a.

### Transport by road/by rail (ADR/RID)

UN proper shipping name:  
Transport hazard class(es): n.a.  
Packing group: n.a.  
Classification code: n.a.  
LQ (ADR 2011): n.a.  
LQ (ADR 2009): n.a.  
Environmental hazards: Not applicable  
Tunnel restriction code:

### Transport by sea (IMDG-code)

UN proper shipping name:  
Transport hazard class(es): n.a.  
Packing group: n.a.  
Marine Pollutant: n.a.  
Environmental hazards: Not applicable

### Transport by air (IATA)

UN proper shipping name:  
Transport hazard class(es): n.a.  
Packing group: n.a.  
Environmental hazards: Not applicable

### Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

### Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Non-dangerous material according to Transport Regulations.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

For classification and labelling see Section 2.

Observe restrictions: n.a.

VOC 1999/13/EC:

n.a.

### 15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

## SECTION 16: Other information

These details refer to the product as it is delivered.

Revised sections: 2

### Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

## Any abbreviations and acronyms used in this document:



acc., acc. to	according, according to
ACGIH	American Conference of Governmental Industrial Hygienists
ADR	Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)
AOEL	Acceptable Operator Exposure Level
AOX	Adsorbable organic halogen compounds
approx.	approximately
Art., Art. no.	Article number
ATE	Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)
BAM	Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)
BAuA	Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
BCF	Bioconcentration factor
BGV	Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)
BHT	Butylhydroxytoluol (= 2,6-Di- <i>t</i> -butyl-4-methyl-phenol)
BMGV	Biological monitoring guidance value (EH40, UK)
BOD	Biochemical oxygen demand
BSEF	Bromine Science and Environmental Forum
bw	body weight
CAS	Chemical Abstracts Service
CESIO	Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques
CIPAC	Collaborative International Pesticides Analytical Council
CLP	Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
CMR	carcinogenic, mutagenic, reproductive toxic
COD	Chemical oxygen demand
CTFA	Cosmetic, Toiletry, and Fragrance Association
DMEL	Derived Minimum Effect Level
DNEL	Derived No Effect Level
DOC	Dissolved organic carbon
DT50	Dwell Time - 50% reduction of start concentration
DVS	Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)
dw	dry weight
e.g.	for example (abbreviation of Latin 'exempli gratia'), for instance
EC	European Community
ECHA	European Chemicals Agency
EEA	European Economic Area
EEC	European Economic Community
EINECS	European Inventory of Existing Commercial Chemical Substances
ELINCS	European List of Notified Chemical Substances
EN	European Norms
EPA	United States Environmental Protection Agency (United States of America)
ERC	Environmental Release Categories
ES	Exposure scenario
etc.	et cetera
EU	European Union
EWC	European Waste Catalogue
Fax.	Fax number
gen.	general
GHS	Globally Harmonized System of Classification and Labelling of Chemicals
GWP	Global warming potential
HET-CAM	Hen's Egg Test - Chorionallantoic Membrane
HGWP	Halocarbon Global Warming Potential
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IBC	Intermediate Bulk Container
IBC (Code)	International Bulk Chemical (Code)
IC	Inhibitory concentration
IMDG-code	International Maritime Code for Dangerous Goods
incl.	including, inclusive
IUCLID	International Uniform Chemical Information Database
LC	lethal concentration
LC50	lethal concentration 50 percent kill
LCLo	lowest published lethal concentration
LD	Lethal Dose of a chemical



Page 9 of 9  
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II  
Revised on / Version: 15.10.2012 / 0004  
Replaces revision of / Version: 19.01.2011 / 0003  
Valid from: 15.10.2012  
PDF print date: 23.10.2012  
RACING BIKE OIL-ADDITIV 125ML Art.: 1580

LD50 Lethal Dose, 50% kill  
LDLo Lethal Dose Low  
LOAEL Lowest Observed Adverse Effect Level  
LOEC Lowest Observed Effect Concentration  
LOEL Lowest Observed Effect Level  
LQ Limited Quantities  
MARPOL International Convention for the Prevention of Marine Pollution from Ships  
n.a. not applicable  
n.av. not available  
n.c. not checked  
n.d.a. no data available  
NIOSH National Institute of Occupational Safety and Health (United States of America)  
NOAEC No Observed Adverse Effective Concentration  
NOAEL No Observed Adverse Effect Level  
NOEC No Observed Effect Concentration  
NOEL No Observed Effect Level  
ODP Ozone Depletion Potential  
OECD Organisation for Economic Co-operation and Development  
org. organic  
PAH polycyclic aromatic hydrocarbon  
PBT persistent, bioaccumulative and toxic  
PC Chemical product category  
PE Polyethylene  
PNEC Predicted No Effect Concentration  
POCP Photochemical ozone creation potential  
ppm parts per million  
PROC Process category  
PTFE Polytetrafluorethylene  
REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)  
REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.  
RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)  
SADT Self-Accelerating Decomposition Temperature  
SAR Structure Activity Relationship  
SU Sector of use  
SVHC Substances of Very High Concern  
Tel. Telephone  
ThOD Theoretical oxygen demand  
TOC Total organic carbon  
TRGS Technische Regeln für Gefahrstoffe (=Technical Regulations for Hazardous Substances)  
VbF Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))  
VOC Volatile organic compounds  
vPvB very persistent and very bioaccumulative  
WEL-TWA, WEL-STEL WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).  
WHO World Health Organization  
wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.

No responsibility.

These statements were made by:

**Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90**

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.