according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray



BUILDING TRUST

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Everbuild PVCu Acti-Spray

1.2 Relevant identified uses of the substance or mixture and uses advised against

Product use : Adhesive

1.3 Details of the supplier of the safety data sheet

Company : Everbuild - A Sika Company

Site 41

Knowsthorpe Way

Cross Green Industrial Estate

Leeds

West Yorkshire LS9 0SW

United Kingdom

Telephone : 0113 240 3456

: everbuild.sds@uk.sika.com E-mail address

1.4 Emergency telephone number

Emergency telephone num-

ber

: 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Aerosols, Category 1 H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

Skin irritation, Category 2 H315: Causes skin irritation.

Reproductive toxicity, Category 2 H361f: Suspected of damaging fertility.

Specific target organ toxicity - single ex-

posure, Category 3, Central nervous

system

H336: May cause drowsiness or dizziness.

Specific target organ toxicity - repeated

exposure, Category 2

H373: May cause damage to organs through pro-

longed or repeated exposure.

Chronic aquatic toxicity, Category 2 H411: Toxic to aquatic life with long lasting effects.

Country GB 100000013299

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018 Version 2.0







2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :









Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.

H229 Pressurised container: May burst if heated.

H315 Causes skin irritation.

H336 May cause drowsiness or dizziness. H361f Suspected of damaging fertility.

H373 May cause damage to organs through pro-

longed or repeated exposure.

H411 Toxic to aquatic life with long lasting effects.

Precautionary statements : **Prevention**:

P210 Keep away from heat, hot surfaces, sparks,

open flames and other ignition sources. No

smoking.

P211 Do not spray on an open flame or other

ignition source.

P251 Do not pierce or burn, even after use.
P260 Do not breathe dust/ fume/ gas/ mist/ va-

pours/ spray.

P280 Wear protective gloves/ protective clothing/

eye protection/ face protection.

Storage:

P410 + P412 Protect from sunlight. Do not expose to

temperatures exceeding 50 °C/ 122 °F.

Hazardous components which must be listed on the label:

• 203-777-6 n-hexane

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

Chemical name CAS-No. EC-No. Registration number	Classification (REGULATION (EC) No 1272/2008)	Concentration [%]
n-hexane 110-54-3	Flam. Liq.2; H225 Repr.2; H361f	>= 40 - < 60

according to Regulation (EC) No. 1907/2006







Everbuild PVCu Acti-Spray

Revision Date 16.04.2018 Version 2.0 Print Date 09.01.2019

203-777-6 01-2119480412-44-XXXX	Asp. Tox.1; H304 STOT RE2; H373 Skin Irrit.2; H315 STOT SE3; H336 Aquatic Chronic2; H411	
N,N-dimethyl-p-toluidine 99-97-8 202-805-4	Acute Tox.3; H301 Acute Tox.3; H331 Acute Tox.3; H311 STOT RE2; H373 Aquatic Chronic3; H412	>= 0,25 - < 1
Substances with a workplace exposure limit :		
petroleum gases, liquefied 68476-85-7 270-704-2	Flam. Gas1; H220	>= 40 - < 60

For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : Move out of dangerous area.

Consult a physician.

Show this safety data sheet to the doctor in attendance.

If inhaled : Move to fresh air.

In case of skin contact : Take off contaminated clothing and shoes immediately.

Wash off with soap and plenty of water. If symptoms persist, call a physician.

In case of eye contact : Remove contact lenses.

Keep eye wide open while rinsing.

If eye irritation persists, consult a specialist.

If swallowed : Do not induce vomiting without medical advice.

Rinse mouth with water.

Do not give milk or alcoholic beverages.

Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : Erythema

Dermatitis Loss of balance Vertigo

See Section 11 for more detailed information on health effects

and symptoms.

Risks : irritant effects

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018





Version 2.0

Print Date 09.01.2019

Causes skin irritation.

May cause drowsiness or dizziness. Suspected of damaging fertility.

May cause damage to organs through prolonged or repeated

exposure.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local cir-

cumstances and the surrounding environment.

Unsuitable extinguishing

media

: Water

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-

fighting

: Do not allow run-off from fire fighting to enter drains or water

courses.

ucts

Hazardous combustion prod- : No hazardous combustion products are known

5.3 Advice for firefighters

for firefighters

Special protective equipment : In the event of fire, wear self-contained breathing apparatus.

Further information : Use water spray to cool unopened containers. Collect contam-

inated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with

local regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.

Deny access to unprotected persons.

6.2 Environmental precautions

Environmental precautions : Do not flush into surface water or sanitary sewer system.

If the product contaminates rivers and lakes or drains inform

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018





Print Date 09.01.2019

Version 2.0

respective authorities.

6.3 Methods and materials for containment and cleaning up

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling

: Avoid exceeding the given occupational exposure limits (see section 8). Do not get in eyes, on skin, or on clothing. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Take precautionary measures against static discharge. Open drum carefully as content may be under pressure. Take necessary action to avoid static electricity discharge (which might cause ignition of organic vapours). Follow standard hygiene measures when

handling chemical products

Advice on protection against

fire and explosion

: Use explosion-proof equipment. Keep away from heat/sparks/open flames/hot surfaces. No smoking. Do not

spray on a naked flame or any incandescent material. Take precautionary measures against electrostatic discharges.

: Handle in accordance with good industrial hygiene and safety Hygiene measures

practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers

: BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects. Store in original container. Keep container

tightly closed in a dry and well-ventilated place. Observe label precautions. Store in accordance with local regulations.

: No decomposition if stored and applied as directed. Other data

7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any

use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018







Print Date 09.01.2019



Components	CAS-No.	Value	Control parame- ters *	Basis *
n-hexane	110-54-3	TWA	20 ppm 72 mg/m3	GB EH40
petroleum gases, liquefied	68476-85-7	TWA	1.000 ppm 1.750 mg/m3	GB EH40
		STEL	1.250 ppm 2.180 mg/m3	GB EH40

Version 2.0

8.2 Exposure controls

Personal protective equipment

Eye protection : Safety glasses with side-shields conforming to EN166

Eye wash bottle with pure water

Hand protection : Chemical-resistant, impervious gloves complying with an ap-

> proved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manu-

facturer specifications.

Suitable for short time use or protection against splashes:

Butyl rubber/nitrile rubber gloves (0,4 mm), Contaminated gloves should be removed.

Suitable for permanent exposure:

Viton gloves (0.4 mm), breakthrough time >30 min.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345,

long-sleeved working clothing, long trousers).

Respiratory protection : Respirator selection must be based on known or anticipated

exposure levels, the hazards of the product and the safe work-

ing limits of the selected respirator.

organic vapor (Type A) and particulate filter

A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm P1: Inert material; P2, P3: hazardous substances

Ensure adequate ventilation, especially in confined areas. When workers are facing concentrations above the exposure

limit they must use appropriate certified respirators.

Environmental exposure controls

General advice : Do not flush into surface water or sanitary sewer system.

If the product contaminates rivers and lakes or drains inform

respective authorities.

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018



Version 2.0



Print Date 09.01.2019

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance aerosol

Colour colourless

Odour characteristic

Odour Threshold : No data available

Flash point : ca. -40 °C

Autoignition temperature : No data available

Decomposition temperature : No data available

Lower explosion limit (Vol-%) : No data available

Upper explosion limit (Vol-%) : No data available

Flammability : No data available

Explosive properties : No data available

Oxidizing properties No data available

No data available рΗ

Melting point/range / Freez-

Boiling point/boiling range

ing point

Vapour pressure 1 hPa

Density : ca.1 g/cm3

at 20 °C

Water solubility insoluble

Partition coefficient: n-

octanol/water

: No data available

: No data available

: No data available

: No data available Viscosity, dynamic

Viscosity, kinematic : Not applicable

Relative vapour density : No data available

Evaporation rate : No data available

9.2 Other information

No data available

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray





Revision Date 16.04.2018

Version 2.0

Print Date 09.01.2019

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : Heat, flames and sparks.

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Components:

N,N-dimethyl-p-toluidine:

Acute oral toxicity : Acute toxicity estimate: 100 mg/kg

Method: Converted acute toxicity point estimate

Acute dermal toxicity : Acute toxicity estimate: 300 mg/kg

Method: Converted acute toxicity point estimate

Skin corrosion/irritation

Causes skin irritation.

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information. Respiratory sensitisation: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018 Version 2.0





Print Date 09.01.2019

Reproductive toxicity

Suspected of damaging fertility.

STOT - single exposure

May cause drowsiness or dizziness.

STOT - repeated exposure

May cause damage to organs through prolonged or repeated exposure.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered

to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of

0.1% or higher.

12.6 Other adverse effects

Product:

Additional ecological infor-

mation

: An environmental hazard cannot be excluded in the event of

unprofessional handling or disposal.

Toxic to aquatic life with long lasting effects.

Components:

N,N-dimethyl-p-toluidine:

Additional ecological infor-

mation

: An environmental hazard cannot be excluded in the event of

unprofessional handling or disposal.

Harmful to aquatic life with long lasting effects.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Country GB 100000013299

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray



Product : The generation of waste should be avoided or minimized

wherever possible.

Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe

BUILDING TRUST

way.

Dispose of surplus and non-recyclable products via a licensed

waste disposal contractor.

Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional

local authority requirements.

Avoid dispersal of spilled material and runoff and contact with

soil, waterways, drains and sewers.

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated

by dangerous substances

SECTION 14: Transport information

ADR

14.1 UN number : 1950 **14.2 UN proper shipping name** : AEROSOLS

14.3 Transport hazard : 2

class(es)

Classification Code : 5F
Labels : 2.1
Tunnel restriction code : (D)
14.5 Environmental hazards : yes

IATA

14.1 UN number : 1950

14.2 UN proper shipping name : Aerosols, flammable

14.3 Transport hazard : 2.1

class(es)

Labels : 2.1 14.5 Environmental hazards : yes

IMDG

14.1 UN number : 1950 **14.2 UN proper shipping name** : AEROSOLS

 14.3 Class
 : 2.1

 Labels
 : 2.1

 EmS Number 1
 : F-D

 EmS Number 2
 : S-U

 14.5 Marine pollutant
 : yes

 n-hexane

14.6 Special precautions for user

No data available

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018







Print Date 09.01.2019



14.7 Transport in bulk according to Annex II of Marpol and the IBC Code Not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture Prohibition/Restriction

Version 2.0

REACH - Candidate List of Substances of Very High

Concern for Authorisation (Article 59).

: None of the components are listed

(=> 0.1 %).

REACH - List of substances subject to authorisation

(Annex XIV)

: Not applicable

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances,

preparations and articles (Annex XVII)

: Not applicable

REACH Information: All substances contained in our Products are

- preregistered or registered by our upstream suppliers, and/or

- preregistered or registered by us, and/or - excluded from the regulation, and/or - exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

P3a	FLAMMABLE AEROSOLS	Quantity 1 150 t	Quantity 2 500 t
E2	ENVIRONMENTAL HAZARDS	200 t	500 t
18	Liquefied extremely flam- mable gases (including LPG) and natural gas	50 t	200 t

VOC-CH (VOCV) : 99,01 % VOC-EU (solvent) : 99,01 %

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture:

: Environmental Protection Act 1990 & Subsidiary Regulations Health and Safety at Work Act 1974 & Subsidiary Regulations Control of Substances Hazardous to Health Regulations

May be subject to the Control of Major Accident Hazards

Regulations (COMAH), and amendments.

Other regulations : 75/324/EEC

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018







Version 2.0 Print Date 09.01.2019

15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this mixture by the supplier.

SECTION 16: Other information

Full text of H-Statements

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H301 Toxic if swallowed.

H304 May be fatal if swallowed and enters airways.

H311 Toxic in contact with skin.
H315 Causes skin irritation.
H331 Toxic if inhaled.

H336 May cause drowsiness or dizziness. H361f Suspected of damaging fertility.

H373 May cause damage to organs through prolonged or repeated exposure.

H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.

Full text of other abbreviations

Acute Tox. Acute toxicity

Aquatic Chronic
Asp. Tox.
Flam. Gas
Flam. Liq.
Repr.

Chronic aquatic toxicity
Aspiration hazard
Flammable gases
Flammable liquids
Reproductive toxicity

Skin Irrit. Skin irritation

STOT RE Specific target organ toxicity - repeated exposure STOT SE Specific target organ toxicity - single exposure

ADR Accord européen relatif au transport international des marchandises

Dangereuses par Route Chemical Abstracts Service

DNEL Derived no-effect level EC50 Half maximal effective concentration

GHS Globally Harmonized System

IATA International Air Transport Association

IMDG International Maritime Code for Dangerous Goods

LD50 Median lethal dosis (the amount of a material, given all at once, which

causes the death of 50% (one half) of a group of test animals)

LC50 Median lethal concentration (concentrations of the chemical in air that

kills 50% of the test animals during the observation period)

International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978

OEL Occupational Exposure Limit

PBT Persistent, bioaccumulative and toxic PNEC Predicted no effect concentration

REACH Regulation (EC) No 1907/2006 of the European Parliament and of the

Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a

European Chemicals Agency


CAS

MARPOL

according to Regulation (EC) No. 1907/2006

Everbuild PVCu Acti-Spray

Revision Date 16.04.2018







Print Date 09.01.2019



SVHC Substances of Very High Concern vPvB Very persistent and very bioaccumulative

Classification of the mixture: Classification procedure:

Version 2.0

Aerosol 1	H222, H229	Calculation method
Skin Irrit. 2	H315	Calculation method
Repr. 2	H361f	Calculation method
STOT SE 3	H336	Calculation method
STOT RE 2	H373	Calculation method
Aquatic Chronic 2	H411	Calculation method

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

Changes as compared to previous version!