

# EUROPEAN 2-PIN PLUG-IN POWER SUPPLY 5VDC 5WATT

## T6350ST



### Features:

- European Fixed AC Head
- 1 Year Warranty
- Level VI Efficiency
- CE Approved

### Description:

The Stontronics Range of Class II watt AC/DC European plug-in power supplies provide 5 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Specification	
RS Stock Number	T6350ST
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.2A Max
Output Voltage Rating	+5V
Output Current Range	1A
Output Min Current	0.05A
Output Connection Type	2.1x5.5x12mm Centre Positive – Right Angle
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	300mVp-p
Efficiency	73.77% Min
Over Voltage Protection	6.5VDC Maximum
Over Load Protection	1.1-1.8A max with auto-recovery function
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	Meet TUV-GS(EN60950-1)
EMI Standard	Meet CE(EN55022)
MTBF	50K Hours
Size mm max.	67 (L) 26 (W) * 72.2(H)
Weight	80 g
Regulator Type	Switched Mode Power Supply

#### General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | Stontronics Ltd  
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK  
t: +44 (0) 118 931 1199

# EUROPEAN 2-PIN PLUG-IN POWER SUPPLY 5VDC 5WATT


T6350ST

## Diagrams



Case:Black

雷射刻印  
Date Code:WWYYHB  
WW:Week  
YY:Year  
HB:Lead Free Products



General Note  
TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | Stontronics Ltd  
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK  
t: +44 (0) 118 931 1199