

# INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 18WATT



## T5879ST

### Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals



### Description:

The Stontronics range of 18 Watt Interchangeable wall plug power supplies provide 18 watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro & USA AC Heads , all Efficiency Level VI and carry worldwide safety approvals.

Specification	
Part Code	T5879ST
Input Voltage Range	90-264 Vac
Input Frequency Range	47-63Hz
Input Current Rated	600A Max
Input AC Heads	UK, Euro & USA
Output Voltage Rating	9V
Output Current Range	2A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm centre positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 2%
Ripple & Noise	200mVp-p
Efficiency	85.45%Min
Over Voltage Protection	Output shut down and auto restart
Over Load Protection	Output shut down and auto restart
Operating Temperature	0°C to 40°C
Storage Temperature	-10°C to +70°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Hi-Pot	3000Vac 10mA 1min
Leakage Current	<0.25mA max
Safety Standard	UL/CUL ,GS,CE,RCM
EMI Standard	FCC class B , CE ,VCCI – II
MTBF	50k Hours
Size mm max.	74 (L) 43.5 (W) 35.3 (H)
Weight	200 g

# INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 18WATT



T5879ST

## Diagrams

