NDR-240 Series

240W Single Output Industrial DIN Rail



Features

- Universal AC input / Full range
- Protections: Short Circuit / Overload / Over voltage / Over Temperature
- Can be installed on DIN rail TS-35/7.5 or 15
- UL 508 (industrial control equipment) approved
- Cooling by free air convection
- Built-in active PFC Function
- EN61000-6-2 (EN50082-2) industrial immunity level
- 100% full load burn-in test
- 3 years warranty









Specification


Specification			
INPUT	Voltage	90V~264VAC 127~370VDC	
	Frequency	47 ~ 63 Hz	
	Power Factor	PF>0.98/115VAC, PF>0.95/230VAC at full load	
	AC Current (Typ.)	2.5A/115VAC 1.3A/230VAC	
	Inrush Current (Typ.)	20A/115VAC 35A/230VAC	
	Leakage Current	<1mA/240VAC	
	Efficiency	88.5% 90%	
ОИТРИТ	MODEL No.	NDR-240-24 NDR-240-48	
	Voltage	24V 48V	
	Rated Current	10A 5A	
	Current Range	0~10A 0~5A	
	Rated Power	240W 240W	
	Ripple Noise MAX.	150Vp-p 150mVp-p	
	Voltage Adjustment Range	24~28V 48~55V	
	Voltage Tolerance	± 1.0% ± 1.0%	
	Line Regulation	± 0.5% ± 0.5%	
	Load Regulation	± 1.0% ± 1.0%	
	Setup Rise Time	1500ms, 100ms/230VAC 3000ms, 100ms/115VAC at full load	
	Holdup Time (Typ.)	28ms/230VAC 22ms/115VAC at full load	
PROTECTION	Over Load	105~130% rated output power	
		Protection Type: Constant current limiting, recovers automatically after fault condition is removed	
	Over Voltage	29~33V 56~65V	
		Protection Type: Shut down o/p voltage, re-power on to recover	
	Over Temperature	Shut down o/p voltage, recovers automatically after temperature goes down	
ENVIRONMENT	Working Temperature	-20~+70°C (Refer to "Derating Curve")	
	Working Humidity	20~95% RH non-condensing	
	Storage Temp., Humidity	-40- +85°C, 10-95%RH	
	Temp. Co-efficient	±0.03% / °C (0~50°C)	
	Vibration	Component: 10~500Hz, 2G 10min./1cycle, 60 min. each along X, Y, Z axes; Mounting: compliance to IEC60068-2-6	
SAFETY & EMC OTHERS	Safety Standards	UL508, TUV EN60950-1 approved; Meets EN60204-1	
	Withstand Voltage	I/P-0/P:3KVAC I/P-FG:2KVAC 0/P-FG:0.5KVAC	
	Isolation Resistance	I/P-0P, I/P-FG, 0/P-FG:>100M 0hms/500Vdc/25°C/70% RH	
	EMC Emission	Compliance to EN55022 (CISPR22), EN61204-3, Class B, EN61000-3-2,-3	
	EMC Immunity	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN61000-6-2 (EN50082-2), EN61204-3, heavy industry level, criteria A	
	M.T.B.F.	230.2K hrs min. MIL-HDBK-217F (25°C)	
	Packaging	1Kg; 12pcs/13Kg/1.1CUFT	
	1. All parameters NOT specially montioned are measured at 230VMC input, rated load and 25°C of ambient temperature		

- All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.
 Ripple and noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.
 Tolerance: includes set up tolerance, line regulation and load regulation.
 Derating may be needed under low input voltage. Please check the derating curve for more details.
 Installation clearances: 40mm on top, 20mm on the bottom, 5mm on the left and right side are recommended when loaded permanently with full power. In case the adjacent device is a heat source, 15mm clearance is recommended.
- The power supply is considered as a component which will be installed with final equipment. The final equipment must re-confirmed that it still meets EMC Directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies."


NDR-240 Series


240W Single Output Industrial DIN Rail


Mechanical Specification




Case No.979C Unit:mm










Terminal Pin No. Assignment (TB1) Assignment FG (Pin No.

AC/N or DC -AC/L or DC +

Terminal Pin No. Assignment (TB2) Pin No. Assignment DC OUTPUT -V 1,2 3,4 DC OUTPUT+V

Installation instruction



Back View

This series fits DIN-RAIL TS35/7.5 or TS35/15. For installation details, please refer to the USER MANUAL on http://www.meanwell.com/search/NDR-240/NDR_manual.pdf

