

USB Multi Head Power Supplies



DESCRIPTION

R-TECH USB Interchangeable Multi-head AC/DC Power Adapters.

DISTINCTIVE FEATURES

- Interchangeable AC Heads
- Short Circuit Protection
- EN62368 Approved
- DOE Level VI Efficiency
- RoHS Compliant
- USB-A Socket
- Overcurrent Protection
- 1 Year Warranty

APPLICATIONS

The multi-head design allows use in a variety of countries and is ideal for use with Audio Visual equipment, and Information Technology products that require a power supply with a USB-A connector.

5W

5VDC

1A

USB-A

UK

EU

US

AUS



ELECTRICAL SPECIFICATION

Output	
DC Voltage	5VDC
Rated Current	1A
Current Range	0-1A
Rated Power	5W
Ripple & Noise	300mVp-p max
Output Regulation	±5%
Output Connector	USB-A Socket
Input	
Voltage Range	90-264VAC
Frequency Range	47-63Hz
Nominal Voltage Range	100-240VAC
Nominal Frequency Range	50-60Hz
Input Current	0.3A Max
Inrush Current	40A Max
Standby Power	0.075W Max
Leakage Current	0.25A Max
Input Connector	UK, EU, US & AUS AC Heads



GENERAL SPECIFICATION

Series	Power Supplies
Type	USB Multi head AC/DC Adapter
RoHS Compliant	Yes
DOE	Level VI Efficiency
Class Rating	Class II Double Insulated



MATERIALS

Case Material	Polycarbonate
Case Colour	Black



CERTIFICATION AND STANDARDS

Safety Standards	UL/CUL 62368-1, GS/TUV EN62368-1, SAA AS/NZ 60950.1, CCC GB4943.1
EMC Emissions	EN55032, RCM GB9254, FCC Part 15 Class B






ENVIRONMENTAL/OPERATING SPECIFICATION

Operating Temperature	0°C~40°C
Cooling	Convection
Temperature Coefficient	0.05%/°C
Humidity	5~95%RH (non-condensing)
Storage Temperature	-20°C~+60°C
Operating Environment	Designed for indoor use only, and not suitable for use in damp or wet conditions




DIMENSIONS/DRAWINGS


Units	mm - unless stated otherwise
Overall Dimensions	47.0 x 34.57 x 26.5
Weight	26g




UK AC PLUG




US AC PLUG



AU AC PLUG



EU AC PLUG



PART NUMBER TABLE

Part number	UNSPSC	EAN	Country of Origin
85-7074	39121004	5053556007950	China

R-TECH

Tried & trusted technology

Important Notice: This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.