




Specification (test circuit 1):
Turns ratio: 1 to 1 C.T. (series)

DC resistance (Ω +/-15%)
Primary (8 - 5): 24
Secondary (1 - 4): 22.5

Input impedance (Ω): 2.83k Ω (typ.) @ 1kHz
Output impedance (Ω): 194 Ω (typ.) @ 1kHz


Voltage gain @ 1kHz, -0.59dBu (typ.)

Maximum input @ 20Hz, <1% THD: 0dBu

Insertion loss: 2.3dB (typ.)

Leakage inductance @ 1kHz: (8 - 5) (1/2/3/4 S/C) 1.2mH (typ.)

Capacitance @ 10kHz, 0.1V:
Cp-s: 45pF (typ.) or 5pF (typ.) with screen earthed
Cp-scr: 80pF (typ.)
Cs-scr: 85pF (typ.)



Specification (test circuit 2):
Turns ratio: 1 to 0.5 (parallel wired)

DC resistance (Ω +/-15%)
Primary (8 - 5): 24
Secondary (parallel) ((1+2) - (3+4)): 5.75

Input impedance (Ω): 2.83k Ω (typ.) @ 1kHz
Output impedance (Ω): 63 Ω (typ.) @ 1kHz



Voltage gain @ 1kHz, -12.9dBu (typ.)

Maximum input @ 20Hz, <1% THD: 0dBu

Insertion loss: 2.3dB (typ.)

Leakage inductance @ 1kHz: (8 - 5) (1/2/3/4 S/C) 1.2mH (typ.)

Capacitance @ 10kHz, 0.1V:
Cp-s: 45pF (typ.) or 5pF (typ.) with screen earthed
Cp-scr: 80pF (typ.)
Cs-scr: 85pF (typ.)



Pin diameter 0.7mm (0.0276)

Tolerance on dimensions in mm: +/- 0.1 unless stated otherwise.
Inches shown in brackets.

Tolerance on dimensions in inches: +/- 0.005" unless stated otherwise.

Application:
Microphone input transformer

Input impedance: 150 ohms

Input 0dBu max. (@ 20Hz) <1%THD

Frequency response +/-0.2dB (16Hz - 35kHz)

Hi-pot, primary to secondaries: 500VDC
Windings to screens+can: 500VDC

Fitted with multiple electrostatic screens

Low distortion Mu-metal core

Mu-metal screening can reduces electrical noise by up to 30dB

Operating temperature range: 0 to +70°C
Storage temperature range: -25°C to +120°C

Mass = 0.055kg




vigortronix

VIGORTRONIX LTD
16 De Havilland Way
Windrush Park, Witney
Oxon, OX29 0YG, UK
Tel: +44 (0)1993 777570
Fax: +44 (0)1993 777580
www.vigortronix.com




150 Ω microphone isolation transformer
1 to 0.5 + 0.5
page 1 of 2



Scale: nts

All dimensions in mm unless stated otherwise

ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
1	20/11/24	CS		VTX-MIC1
2	02/04/25	CS		



vigortronix

VIGORTRONIX LTD
16 De Havilland Way
Windrush Park, Witney
Oxon, OX29 0YG, UK
Tel: +44 (0)1993 777570
Fax: +44 (0)1993 777580
www.vigortronix.com

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
150Ω microphone isolation transformer 1 to 0.5 + 0.5 page 2 of 2	1	20/11/24	CS		VTX-MIC1
	2	02/04/25	CS		
Scale: nts	All dimensions in mm unless stated otherwise				