

Section 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name: STICKY-OFF

1.2. Relevant identified uses of the substance or mixture and uses advised against**1.3. Details of the supplier of the safety data sheet**

Company name: Rustins Ltd

Waterloo Road

Cricklewood

London

NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number**Section 2: Hazards identification****2.1. Classification of the substance or mixture**

Classification under CHIP: -: R10; Xi: R38; N: R50/53

Classification under CLP: Aquatic Chronic 1: H410; Eye Irrit. 2: H319; Flam. Liq. 3: H226; Skin Irrit. 2: H315; Skin Sens. 1: H317; Aquatic Acute 1: H400

Most important adverse effects: Flammable. Irritating to skin. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements**Label elements under CLP:**

Hazard statements: H226: Flammable liquid and vapour.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H410: Very toxic to aquatic life with long lasting effects.

Signal words: Warning

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

GHS09: Environmental



SAFETY DATA SHEET

STICKY-OFF

Page: 2

Precautionary statements: P243: Take precautionary measures against static discharge.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P303+361+353: IF ON SKIN (or hair): Remove immediately all contaminated clothing.
Rinse skin with water/shower.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P321: Specific treatment (see instructions on this label).
P370+378: In case of fire: Use carbon dioxide for extinction.

Label elements under CHIP:

Hazard symbols: Irritant.
Dangerous for the environment.



Risk phrases: R10: Flammable.
R38: Irritating to skin.
R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases: S61: Avoid release to the environment. Refer to special instructions / safety data sheets.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

CITRUS TERPENES

EINECS	CAS	CHIP Classification	CLP Classification	Percent
-	-	-: R10; Xi: R38; N: R50/53	Flam. Liq. 3: H226; Skin Irrit. 2: H315; Skin Sens. 1: H317; Eye Irrit. 2: H319; Aquatic Chronic 1: H410; Aquatic Acute 1: H400	40.000%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water. Remove all contaminated clothes and footwear immediately unless stuck to skin.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: If accidentally swallowed, wash mouth out with water. Do not induce vomiting, keep at rest and obtain medical attention.

[cont...]

SAFETY DATA SHEET

STICKY-OFF

Page: 3

Inhalation: If irritation of the nose or throat occurs remove to fresh air. Get medical advice if irritation continues.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: No data available.

Eye contact: No data available.

Ingestion: No data available.

Inhalation: No data available.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Use dry powder, foam or carbon dioxide. Never use water as this may float the oil and spread the fire.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Flammable. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Do not attempt to take action without suitable protective clothing - see section 8 of SDS.

6.2. Environmental precautions

Environmental precautions: If the product enters drains or sewers, the local water company should be contacted immediately. In the case of contamination of streams, rivers or lakes contact the relevant environment agency.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Clean preferably with a detergent, avoid the use of solvents. Transfer into a suitable container for disposal in accordance with the waste regulations (see section 13)

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area.

[cont...]

SAFETY DATA SHEET

STICKY-OFF

Page: 4

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Keep away from sources of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses.

Skin protection: Protective clothing.

Environmental: Not applicable.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Characteristic odour

Solubility in water: Insoluble

Flash point °C: 23 - 55

Relative density: 0.8

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

[cont...]

SAFETY DATA SHEET

STICKY-OFF

Page: 5

10.4. Conditions to avoid

Conditions to avoid: Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Oxidising agents. Reducing agents. Strong acids. Strong bases.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Relevant effects for mixture:

Effect	Route	Basis
Irritation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: No data available.

Eye contact: No data available.

Ingestion: No data available.

Inhalation: No data available.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: Insoluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: No data available.

[cont...]

SAFETY DATA SHEET

STICKY-OFF

Page: 6

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: No data available.

Recovery operations: Not applicable.

Disposal of packaging: Dispose of as normal industrial waste.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: 3

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H226: Flammable liquid and vapour.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H410: Very toxic to aquatic life with long lasting effects.

R10: Flammable.

R38: Irritating to skin.

R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

[cont...]

SAFETY DATA SHEET

STICKY-OFF

Page: 7

Legend to abbreviations: PNEC = predicted no effect level
DNEL = derived no effect level
LD50 = median lethal dose
LC50 = median lethal concentration
EC50 = median effective concentration
IC50 = median inhibitory concentration
dw = dry weight
bw = body weight
cc = closed cup
oc = open cup
MUS = mouse
GPG = guinea pig
RBT = rabbit
HAM = hamster
HMN = human
MAM = mammal
PGN = pigeon
IVN = intravenous
SCU = subcutaneous
SKN = skin
DRM = dermal
OCC = ocular/corneal
PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.