



SAFETY DATA SHEET
ANTI-SEIZE COMPOUND

Page: 1

Compilation date: 26/01/2015

Revision No: 7

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: ANTI-SEIZE COMPOUND

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC24: Lubricants, greases, release products.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Acute 1: H400; Aquatic Chronic 1: H410

Classification under CHIP: N: R51/53

Most important adverse effects: Very toxic to aquatic life. Very toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements under CLP:

Hazard statements: H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

Signal words: Warning

Hazard pictograms: GHS09: Environmental



Precautionary statements: P273: Avoid release to the environment.

P391: Collect spillage.

P501: Dispose of contents/container to local and national regulations.

[cont...]

SAFETY DATA SHEET

ANTI-SEIZE COMPOUND

Page: 2

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC (NOTE L - < 3% DMSO EXTRACT)

EINECS	CAS	CHIP Classification	CLP Classification	Percent
265-097-6	64741-96-4	Substance with a Community workplace exposure limit.	-	50-70%

COPPER POWDER

231-159-6	7440-50-8	-	Acute Tox. 4: H302; Aquatic Acute 1: H400; Aquatic Chronic 2: H411	10-30%
-----------	-----------	---	--	--------

GRAPHITE POWDER

231-955-3	7782-42-5	Substance with a Community workplace exposure limit.	-	10-30%
-----------	-----------	--	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Use water spray to cool containers. Alcohol or polymer foam. Dry chemical powder.
Carbon dioxide.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

[cont...]

SAFETY DATA SHEET

ANTI-SEIZE COMPOUND

Page: 3

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC (NOTE L - < 3% DMSO EXTRACT)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5 mg/m ³	10 mg/m ³	-	-

COPPER POWDER

UK	1mg/m ³	2mg/m ³	-	-
----	--------------------	--------------------	---	---

[cont...]

SAFETY DATA SHEET

ANTI-SEIZE COMPOUND

Page: 4

GRAPHITE POWDER

UK	-	-	5 mg/m ³	10 mg/m ³
----	---	---	---------------------	----------------------

DNEL/PNEC Values

Hazardous ingredients:

COPPER POWDER

Type	Exposure	Value	Population	Effect
PNEC	Fresh water	0.0078 mg/l	-	-
PNEC	Fresh water sediments	87 mg/kg	-	-
PNEC	Marine water	0.0052 mg/l	-	-
PNEC	Marine sediments	676 mg/kg	-	-

8.2. Exposure controls

Respiratory protection: Respiratory protection not normally required.

Hand protection: Nitrile gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Dark brown

Odour: Odourless

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: Highly viscous

Melting point/range°C: > 280

Flash point°C: > 200

Autoflammability°C: > 200

Relative density: 1.3

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

[cont...]

SAFETY DATA SHEET

ANTI-SEIZE COMPOUND

Page: 5

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

COPPER POWDER

RAINBOW TROUT (<i>Oncorhynchus mykiss</i>)	96H LC50	0.19	mg/l
--	----------	------	------

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: No data available.

[cont...]

SAFETY DATA SHEET

ANTI-SEIZE COMPOUND

Page: 6

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3077

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.
(contains copper powder)

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H302: Harmful if swallowed.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

[cont...]

SAFETY DATA SHEET

ANTI-SEIZE COMPOUND

Page: 7

H411: Toxic to aquatic life with long lasting effects.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legend to abbreviations: PNEC = predicted no effect level
DNEL = derived no effect level
LD50 = median lethal dose
LC50 = median lethal concentration
EC50 = median effective concentration
IC50 = median inhibitory concentration
dw = dry weight
bw = body weight
cc = closed cup
oc = open cup
MUS = mouse
GPG = guinea pig
RBT = rabbit
HAM = hamster
HMN = human
MAM = mammal
PGN = pigeon
IVN = intravenous
SCU = subcutaneous
SKN = skin
DRM = dermal
OCC = ocular/corneal
PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.