

Product information

09 02 240 T

Lineman's Pliers

With tether attachment point

American style

DIN ISO 5746 ASME B107.20



- High transmission ratio for easy cutting
- Requires 50 % less effort compared with conventional combination pliers thanks to optimised transmission ratio
- Pliers with tether attachment point for mounting a fall protection
- Solid construction for heaviest strain; universally applicable
- Ergonomically optimised handle shape for firm contact to the hand and fatigue reducing operation
- Particularly effective cross-hatched knurled gripping zone in the jaws - for strong gripping and pulling
- Additional gripping zone below the joint for powerful leverage and pressing performance
- With cutting edges for soft and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	09 02 240 T
EAN	4003773079941
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
weight	463 g
Dimensions	240 x 56 x 23 mm
Standard	DIN ISO 5746 ASME B107.20
Reach	no
RohS	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 4.6
Cutting capacities hard wire (diameter)	Ø 3.0
Drop Protection System	yes

Classification

eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112106

technical change and errors excepted



Gripping zone below the joint for powerful leverage

