

WIRE ROPE SPRAY

Page: 1

Compilation date: 08/09/2014

Revision No: 6

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: WIRE ROPE SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Wire Rope Lubricant

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

	ROCOL House
	Swillington
	Leeds
	West Yorkshire
	LS26 8BS
	ENGLAND
Tel:	+44 (0) 113 232 2700
Fax:	+44 (0) 113 232 2740
Email:	customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 2: H411; Flam. Aerosol 1: H222; -: H229 Most important adverse effects: Extremely flammable aerosol. Pressurised container: May burst if heated. Toxic to

aquatic life with long lasting effects.

2.2. Label elements

Label elements:	
Hazard statements:	H222: Extremely flammable aerosol.
	H229: Pressurised container: May burst if heated
	H411: Toxic to aquatic life with long lasting effects.
Hazard pictograms:	GHS02: Flame

GHS09: Environmental



Signal words: Danger

WIRE ROPE SPRAY

Precautionary statements:P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.
P251: Do not pierce or burn, even after use.
P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition
sources. No smoking.
P211: Do not spray on an open flame or other ignition source.
P285: In case of inadequate ventilation wear respiratory protection.
P273: Avoid release to the environment.
P391: Collect spillage.
P501: Dispose of contents/container to local/national regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

CYCLOPENTANE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
206-016-6	287-92-3	-	Flam. Liq. 2: H225; Aquatic Chronic 3: H412	30-50%

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) - REACH registered number(s): EXEMPT

270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	10-30%	
SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)					

265-166-0	64742-62-7	Substance with a Community	-	10-30%
		workplace exposure limit.		

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

WIRE ROPE SPRAY

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Extremely flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of

ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Do not use equipment in clean-up procedure which may produce sparks. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.
Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

WIRE ROPE SPRAY

Page: 4

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits:

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-

Respirable dust

Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)

Workplace exposure limits:

Vorkplace exposure limits:			Respirable dust	
State 8 hour TWA		15 min. STEL 8 hour TWA 15 mir		15 min. STEL
UK	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

				1
EU	-	5 mg/m3	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures:	Ensure there is sufficient ventilation of the area. Ensure lighting and electrical
	equipment are not a source of ignition.
Respiratory protection:	Respiratory protection not normally required.
Hand protection:	Gloves (oil-resistant). Nitrile gloves.
Eye protection:	Safety glasses with side-shields.
Skin protection:	Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State:	Aerosol	
Colour:	Black	
Odour:	Characteristic odour	
Evaporation rate:	Fast	
Oxidising:	Non-oxidising (by EC criteria)	
Solubility in water:	Miscible	
Viscosity:	Non-viscous	
Boiling point/range°C:	<0 Melting point/range°C:	<-130
Flammability limits %: lower:	1.8 upper:	9.4
Flash point°C:	-100 Autoflammability°C:	> 200
Relative density:	<1	

WIRE ROPE SPRAY

Page: 5

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

CYCLOPENTANE

ORAL	RAT	4H LC50	>25.3	mg/l
ORAL	RAT	LD50	>5000	mg/kg

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness

or mental confusion may occur.

Section 12: Ecological information

WIRE ROPE SPRAY

Page: 6

Hazardous ingredients:

CYCLOPENTANE

Daphnia magna	48H EC50	51.1	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	29.3	mg/l

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Highly volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Harmful to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, Flammable

14.3. Transport hazard class(es)

Transport class: 2

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

WIRE ROPE SPRAY

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information:	This safety data sheet is prepared in accordance with Commission Regulation (EU) No
	453/2010.
	Safety data sheet prepared in accordance with Commission Directive 2008/47/EC of 8
	April 2008 amending, for the purposes of adapting to technical progress, Council
	Directive 75/324/EEC relating to aerosol dispensers
	Compiled in accordance with REACH.
Phrases used in s.2 and s.3:	H220: Extremely flammable gas.
	H222: Extremely flammable aerosol.
	H225: Highly flammable liquid and vapour.
	H229: Pressurised container: May burst if heated
	H280: Contains gas under pressure; may explode if heated.
	H411: Toxic to aquatic life with long lasting effects.
	H412: Harmful to aquatic life with long lasting effects.
Legal disclaimer:	The above information is believed to be correct but does not purport to be all inclusive
	and shall be used only as a guide. This company shall not be held liable for any
	damage resulting from handling or from contact with the above product.