

6002 Joker Double open-ended wrenches, 30 x 32 x 305 mm

Joker



EAN:	4013288212801	Size:	370x77x20 mm
Part number:	05020264001	Weight:	637 g
Article number:	6002 Joker Double	Country of origin:	CZ
		Customs tariff number:	82041100



- Practical holding function thanks to the metal plate in the jaw
- Limit stop prevents any slipping
- The double-hex geometry reduces the risk of slipping
- Return angle of only 30°
- With Take it easy tool finder: colour coding by size

High-quality, metric double spanner from Wera: Everything a wrench can do and so much more. Faster, better, more beautiful. A real Joker! The new generation of ring ratchet spanners. For hexagon screw heads and bolts. With holding function by a metal plate in the mouth, which reduces the risk of losing screws and sockets. With its extra hard teeth the exchangeable metal plate in the mouth secures screws and sockets and reduces the risk of slipping. The integrated end stop can prevent the screw head from slipping down and allows to apply high torques. The double hexagon geometry ensures a positive connection with the screw or bolt and thus reduces the risk of slipping. A back-pivoting angle of only 30 ° avoids time-consuming rotating of the wrench while screwdriving. The special forge geometry sees to a high torque transmission and high bending stiffness. Made of high-performance chromium molybdenum steel with nickel-chromium coating for high corrosion protection. With Take it easy tool finder: colour coding by size.

Web link

https://products.wera.de/en/joker_6002_joker_double_open-ended_wrenches_6002_joker_double.html

Wera - 6002 Joker Double
05020264001 - 4013288212801

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Joker

Joker open-ended wrench



With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional tools fail. Particularly in confined spaces, where conventional open-jawed wrenches cannot be used. The combination of limit stop and small return angle enables effective work, even on screw pipe connections.



When we began to think about open-ended wrenches, we asked ourselves: why does the wrench always have to be flipped over; why does it have an offset design; why does it slip off injuring fingers? The new design of the mouth resulted in a real "Joker" that works even when all other trumps have been played.

Double open-ended wrench



The Joker double open-ended wrench is ideally suited for locking down nuts and bolts.

Holding function



The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately – no additional tools required.

Web link


https://products.wera.de/en/joker_6002_joker_double_open-ended_wrenches_6002_joker_double.html

Wera - 6002 Joker Double
05020264001 - 4013288212801

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Joker

Integrated limit-stop




Constant re-positioning of the wrench? Difficulty holding fasteners in confined spaces? Easing off to avoid any risks of injury or fastener damage? That was yesterday. Today, the Joker prevents slipping off of the fastener head with its integrated limit-stop – no longer is the thumb needed to act as a depth stop. This makes applications much easier and allows significantly more force to be applied during fastening jobs.

Double-hex geometry



The Joker's clever double-hex geometry delivers a very positive connection with nuts or bolts – it's a perfect fit. And the exchangeable, hardened metal gripping plate in the Joker's mouth literally bites itself into the bolt, with its extremely hard tips. Both features combine to prevent slipping, even at higher torque.

Small return angle




Instead of 60°, the Joker only has a 30° return angle thanks to its unique double-hex design. Along with the Joker's straight neck, this means that flipping the wrench has become a thing of the past. With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional tools fail. Particularly in confined spaces, where conventional open-jawed wrenches cannot be used. The combination of limit stop and small return angle enables effective work, even on screw pipe connections.

"Take it easy" tool finder



"Take it easy" tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Further versions in this product family:



		mm	mm	mm	mm	mm	mm	mm
05003760001	gelb/tuerkis	10	23	13	27	5.5	7	167
05003765001	rot/blau	17	37	19	42	8.5	9.5	235
05020260001 ¹⁾	leuchtpink/leuchtgelb	20	48	22	51	10	10	260.5
05020261001 ¹⁾	Pantone yellow C/Cyan	22	48	24	51	10	10	260.5
05020262001 ¹⁾	cyan/schwarz	24	51	27	60	11	11	280
05020263001 ¹⁾	schwarz/pink	27	63	32	66	12	12	305
05020264001¹⁾	tuerkis/pink	30	63	32	66	12	12	305

1) Available from May 2020

Web link

https://products.wera.de/en/joker_6002_joker_double_open-ended_wrenches_6002_joker_double.html

Wera - 6002 Joker Double
05020264001 - 4013288212801

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de