



**SAFETY DATA SHEET**  
PIPESEAL PTFE LIQUID

Page: 1

Compilation date: 09/12/2014

Revision No: 5

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** PIPESEAL PTFE LIQUID

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Jointing compound.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** STOT SE 3: H336; Eye Irrit. 2: H319; Flam. Liq. 2: H225

**Classification under CHIP:** F: R11; Xi: R36; -: R67

**Most important adverse effects:** Highly flammable liquid and vapour. Causes serious eye irritation. May cause drowsiness or dizziness.

**2.2. Label elements**

**Label elements under CLP:**

**Hazard statements:** H225: Highly flammable liquid and vapour.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

**Signal words:** Danger

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark



[cont...]

# SAFETY DATA SHEET

## PIPESEAL PTFE LIQUID

Page: 2

**Precautionary statements:** P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
P241: Use explosion-proof electrical/ventilating/lighting equipment.  
P243: Take precautionary measures against static discharge.  
P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.  
P264: Wash thoroughly after handling.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P303+361+353: IF ON SKIN (or hair): Remove immediately all contaminated clothing. Rinse skin with water/shower.  
P304+340: IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P312: Call a POISON CENTER or doctor if you feel unwell.  
P337+313: If eye irritation persists: Get medical advice/attention.  
P501: Dispose of contents/container to local/national regulations.

### 2.3. Other hazards

**Other hazards:** Combustion may also generate: decomposition products that may lead to polymer fume fever (24 - 48 hr influenza-like symptoms).

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

##### PROPAN-2-OL

EINECS	CAS	CHIP Classification	CLP Classification	Percent
200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	30-50%

##### CHINA CLAY

310-194-1	1332-58-7	Substance with a Community workplace exposure limit.	-	10-30%
-----------	-----------	--	---	--------

##### TITANIUM DIOXIDE

-	13463-67-7	Substance with a Community workplace exposure limit.	-	2-10%
---	------------	--	---	-------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

[cont...]

# SAFETY DATA SHEET

## PIPESEAL PTFE LIQUID

Page: 3

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. If conscious, give half a litre of water to drink immediately. If unconscious and breathing is OK, place in the recovery position. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. If conscious, ensure the casualty sits or lies down. If unconscious and breathing is OK, place in the recovery position. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** Irritation or pain may occur at the site of contact. Absorption through the skin may be fatal.

**Eye contact:** There may be irritation and redness. The eyes may water profusely. May cause permanent blindness.

**Ingestion:** There may be soreness and redness of the mouth and throat. Severe poisoning can cause unconsciousness and severe and persistent nausea and vomiting.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur. Nausea and stomach pain may occur.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Use water spray to cool containers. Dry chemical powder. Alcohol resistant foam. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** Highly flammable. Toxic. In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Eliminate all sources of ignition. Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Clean-up should be dealt with only by qualified personnel familiar with the specific substance. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

[cont...]

# SAFETY DATA SHEET

## PIPESEAL PTFE LIQUID

Page: 4

### 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.  
Smoking is forbidden. Use non-sparking tools.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in cool, well ventilated area. Keep away from sources of ignition. Keep container tightly closed.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

#### PROPAN-2-OL

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	400 ppm, 999 mg/m <sup>3</sup>	500 ppm, 1250 mg/m <sup>3</sup>	-	-

#### CHINA CLAY

EU	2.0 mg/m <sup>3</sup>	-	-	-
----	-----------------------	---	---	---

#### TITANIUM DIOXIDE

UK	-	-	4mg/m <sup>3</sup>	-
----	---	---	--------------------	---

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

**Respiratory protection:** Respiratory protection not normally required.

**Hand protection:** Butyl gloves. Impermeable gloves.

**Eye protection:** Safety glasses with side-shields. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** White

[cont...]

# SAFETY DATA SHEET

## PIPESEAL PTFE LIQUID

Page: 5

**Odour:** Characteristic odour

**Evaporation rate:** Fast

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Slightly soluble

**Viscosity:** Non-viscous

**Boiling point/range°C:** > 60

**Melting point/range°C:** < 0

**Flash point°C:** 17

**Autoflammability°C:** > 200

**Relative density:** 1.6

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat. Direct sunlight.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes. In combustion emits toxic fumes of hydrogen fluoride. Combustion may also generate: decomposition products that may lead to polymer fume fever (24 - 48 hr influenza-like symptoms).

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg

[cont...]

# SAFETY DATA SHEET

## PIPESEAL PTFE LIQUID

Page: 6

SCU	MUS	LDLO	6	gm/kg
-----	-----	------	---	-------

### Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** Irritation or pain may occur at the site of contact. Absorption through the skin may be fatal.

**Eye contact:** There may be irritation and redness. The eyes may water profusely. May cause permanent blindness.

**Ingestion:** There may be soreness and redness of the mouth and throat. Severe poisoning can cause unconsciousness and severe and persistent nausea and vomiting.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur. Nausea and stomach pain may occur.

## Section 12: Ecological information

### 12.1. Toxicity

#### Hazardous ingredients:

#### CHINA CLAY

ALGAE	72H IC50	> 1000	mg/l
DAPHNIA	48H EC50	> 1000	mg/l
FISH	96H LC50	> 1000	mg/l

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** Slightly bioaccumulable.

### 12.4. Mobility in soil

**Mobility:** Volatile. Readily absorbed into soil.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

# SAFETY DATA SHEET

PIPESEAL PTFE LIQUID

Page: 7

## Section 14: Transport information

### 14.1. UN number

UN number: UN1993

### 14.2. UN proper shipping name

Shipping name: FLAMMABLE LIQUID, N.O.S.  
(contains propan-2-ol, xylene)

### 14.3. Transport hazard class(es)

Transport class: 3

### 14.4. Packing group

Packing group: II

### 14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

### 14.6. Special precautions for user

Tunnel code: D/E

Transport category: 2

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

.....  
Product label must specify:

CONTAINS SUBSTANCE(S):

PROPAN-2-OL (CAS 67-63-0)  
.....

**Phrases used in s.2 and s.3:** H225: Highly flammable liquid and vapour.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

R11: Highly flammable.

R36: Irritating to eyes.

R67: Vapours may cause drowsiness and dizziness.

**Legend to abbreviations:** PNEC = predicted no effect level

[cont...]

## SAFETY DATA SHEET

### PIPESEAL PTFE LIQUID

Page: 8

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.