

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: KRYLEX KP1137 LIQUID

Index number: 01-005-770

Product code: KP1137 LIQUID

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Solvent-based activator for cyanoacrylate adhesives

1.3. Details of the supplier of the safety data sheet

Company name: Chemence Ltd
Princewood Road
Earlstree Industrial Estate
Corby
Northants
NN17 4XD
United Kingdom
Tel: +44 (0) 1536 402 600
Fax: +44 (0) 1536 400 266
Email: technical@chemence.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 1536 402 600 (9am - 5.30pm)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Asp. Tox. 1: H304; Aquatic Chronic 2: H411; Flam. Liq. 2: H225; Skin Irrit. 2: H315; STOT SE 3: H336

Most important adverse effects: Highly flammable liquid and vapour. May be fatal if swallowed and enters airways.
Causes skin irritation. May cause drowsiness or dizziness. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H225: Highly flammable liquid and vapour.
H304: May be fatal if swallowed and enters airways.
H315: Causes skin irritation.
H336: May cause drowsiness or dizziness.
H411: Toxic to aquatic life with long lasting effects.

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 2

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

GHS08: Health hazard

GHS09: Environmental



Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P233: Keep container tightly closed.

P243: Take action to prevent static discharges.

P261: Avoid breathing vapours.

P271: Use only outdoors or in a well-ventilated area.

P273: Avoid release to the environment.

P280: Wear protective gloves.

P301+P310: IF SWALLOWED: Immediately call a POISON CENTER or doctor.

P331: Do NOT induce vomiting.

P302+P352: IF ON SKIN: Wash with plenty of water.

P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water .

P304+P340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P403+P235: Store in a well-ventilated place. Keep cool.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS - REACH registered number(s): 01-2119475515-33

EINECS	CAS	PBT / WEL	CLP Classification	Percent
927-510-4	-	-	Flam. Liq. 2: H225; Asp. Tox. 1: H304; Skin Irrit. 2: H315; STOT SE 3: H336; Aquatic Chronic 2: H411	>80%

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 3

N,N-DIMETHYL-P-TOLUIDINE - REACH registered number(s): 01-2119937766-23-...

202-805-4	99-97-8	-	Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Aquatic Chronic 3: H412	0.1-1%
-----------	---------	---	--	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water. Remove all contaminated clothes and footwear immediately unless stuck to skin.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water. Do not induce vomiting. Transfer to hospital as soon as possible.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. If unconscious, check for breathing and apply artificial respiration if necessary. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be soreness and redness of the mouth and throat. There may be difficulty swallowing. Nausea and stomach pain may occur. There may be vomiting. May cause dizziness. Aspiration into the lungs may cause chemical pneumonitis, which can be fatal. Inhalation of fumes from the stomach may cause symptoms similar to direct inhalation.

Inhalation: Drowsiness or mental confusion may occur. There may be loss of consciousness. Absorption through the lungs can occur causing symptoms similar to those of ingestion.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol or polymer foam. Carbon dioxide. Dry chemical powder. Do not use water. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. Forms explosive air-vapour mixture. Vapour may travel considerable distance to source of ignition and flash back. In combustion emits toxic fumes of carbon dioxide / carbon monoxide. In combustion emits toxic fumes of nitrogen oxides.

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 4

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid the formation or spread of mists in the air. Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden. Use non-sparking tools. Earth any equipment used in handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Ensure lighting and electrical equipment are not a source of ignition. The floor of the storage room must be impermeable to prevent the escape of liquids. Keep away from direct sunlight. Prevent the build up of electrostatic charge in the immediate area.

Suitable packaging: Stainless steel. Glass. Aluminium containers.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 5

Hazardous ingredients:

HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	500ppm	-	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency. Gas/vapour filter, type A: organic vapours (EN141).

Hand protection: Butyl gloves. Impermeable gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: The floor of the storage room must be impermeable to prevent the escape of liquids.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Light, paraffinic

Evaporation rate: Fast

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Also soluble in: Petroleum ether.

Viscosity: Non-viscous

Kinematic viscosity: 0.42

Viscosity test method: Kinematic viscosity in 10⁻⁶ m²/s at 40°C (ISO 3104/3105)

Boiling point/range°C: 94-99

Melting point/range°C: Not applicable.

Flammability limits %: lower: 1

upper: 7

Flash point°C: -5

Part.coeff. n-octanol/water: ~4.7

Autoflammability°C: 215

Vapour pressure: 5kPa @20°C; 21kPa@50°C

Relative density: 0.71

pH: n/e

VOC g/l: 704

9.2. Other information

Other information: No data available.

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 6

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Direct sunlight. Sources of ignition. Hot surfaces. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide. In combustion emits toxic fumes of nitrogen oxides.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS

IHL	RAT	LC50	>23.3	mg/l
ORL	RAT	LD50	>5840	mg/kg
SKN	RAT	LD50	>2920	mg/kg

N,N-DIMETHYL-P-TOLUIDINE

IPR	MUS	LD50	212	mg/kg
-----	-----	------	-----	-------

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated
Aspiration hazard	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 7

Ingestion: There may be soreness and redness of the mouth and throat. There may be difficulty swallowing. Nausea and stomach pain may occur. There may be vomiting. May cause dizziness. Aspiration into the lungs may cause chemical pneumonitis, which can be fatal. Inhalation of fumes from the stomach may cause symptoms similar to direct inhalation.

Inhalation: Drowsiness or mental confusion may occur. There may be loss of consciousness. Absorption through the lungs can occur causing symptoms similar to those of ingestion.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS

RAINBOW TROUT (<i>Oncorhynchus mykiss</i>)	96H LC50	>13.4	mg/l
Daphnia magna	48H EC50	3	mg/l

12.2. Persistence and degradability

Persistence and degradability: Rapidly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: Readily absorbed into soil. Floats on water. Insoluble in water. Highly volatile.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: Use principally as a fuel or other means to generate energy.

Disposal of packaging: After draining, leave to vent in a safe place away from sources of ignition and heat. Beware of vapours remaining in empty drums that may ignite. Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 8

Section 14: Transport information

14.1. UN number

UN number: UN3295

14.2. UN proper shipping name

Shipping name: HYDROCARBONS, LIQUID, N.O.S.
(HYDROCARBONS C7, N-ALKANES, ISOALKANES, CYCLICS)

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: II

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D/E

Transport category: 2

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H225: Highly flammable liquid and vapour.

H301: Toxic if swallowed.

H304: May be fatal if swallowed and enters airways.

H311: Toxic in contact with skin.

H315: Causes skin irritation.

H331: Toxic if inhaled.

H336: May cause drowsiness or dizziness.

H373: May cause damage to organs ({{{0|||message=<or state all organs affected, if known>||filter=(_)?ORGAN_+.+}}}) through prolonged or repeated exposure ({{{1|||

[cont...]

SAFETY DATA SHEET

KRYLEX KP1137 LIQUID

Page: 9

message=<state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>|||filter=(_)?EXP_ROUTE_.+}}}).

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.