

**Section 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier****Product name:** BRIWAX SPRAYWAX**1.2. Relevant identified uses of the substance or mixture and uses advised against****1.3. Details of the supplier of the safety data sheet****Company name:** Rustins Ltd  
Waterloo Road  
Cricklewood  
London  
NW2 7TX  
United Kingdom**Tel:** +44 (0)208 450 4666**Fax:** +44 (0)208 452 2008**Email:** [rustins@rustins.co.uk](mailto:rustins@rustins.co.uk)**1.4. Emergency telephone number****Emergency tel:** +44 (0)208 450 4666 OFFICE HOURS ONLY**Section 2: Hazards identification****2.1. Classification of the substance or mixture****Classification under CLP:** Flam. Liq. 3: H226; STOT SE 3: H336; -: EUH066; -: EUH208**Most important adverse effects:** Repeated exposure may cause skin dryness or cracking. Contains lemon soda fragrance. May produce an allergic reaction. Flammable liquid and vapour. May cause drowsiness or dizziness.**2.2. Label elements****Label elements:****Hazard statements:** EUH066: Repeated exposure may cause skin dryness or cracking.

EUH208: Contains lemon soda fragrance. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H336: May cause drowsiness or dizziness.

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark



# SAFETY DATA SHEET

BRIWAX SPRAYWAX

Page: 2

**Signal words:** Warning

**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P241: Use explosion-proof electrical/ventilating/lighting/.. equipment.

P280: Wear protective gloves and eye protection.

P303+361+353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P370+378: In case of fire: Use carbon dioxide to extinguish.

## 2.3. Other hazards

**Other hazards:** In use, may form flammable / explosive vapour-air mixture.

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

BAS30

EINECS	CAS	PBT / WEL	CLP Classification	Percent
-	-	-	Flam. Liq. 3: H226; STOT SE 3: H336; Asp. Tox. 1: H304; -: EUH066	89.600%

LEMON SODA FRAGRANCE

-	-	-	Eye Irrit. 2: H319; Skin Sens. 1: H317; Aquatic Chronic 1: H410; Asp. Tox. 1: H304; Skin Corr. 1A: H314; Skin Irrit. 2: H315	0.190%
---	---	---	--	--------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

[cont...]

# SAFETY DATA SHEET

BRIWAX SPRAYWAX

Page: 3

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

## 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** Flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air. Smoking is forbidden. Use non-sparking tools.

[cont...]

# SAFETY DATA SHEET

BRIWAX SPRAYWAX

Page: 4

## 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition.

**Suitable packaging:** Must only be kept in original packaging.

## 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Workplace exposure limits:** No data available.

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Odour:** Aromatic

**Evaporation rate:** No data available.

**Oxidising:** No data available.

**Solubility in water:** Slightly soluble

**Viscosity:** Viscous

**Boiling point/range°C:** No data available.

**Melting point/range°C:** No data available.

**Flammability limits %: lower:** No data available.

**upper:** No data available.

**Flash point°C:** 23 - 55

**Part.coeff. n-octanol/water:** No data available.

**Autoflammability°C:** No data available.

**Vapour pressure:** No data available.

**Relative density:** 1.0

**pH:** No data available.

**VOC g/l:** No data available.

### 9.2. Other information

**Other information:** No data available.

[cont...]

# SAFETY DATA SHEET

BRIWAX SPRAYWAX

Page: 5

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions. Stable at room temperature.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat. Hot surfaces. Sources of ignition. Flames.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Relevant hazards for product:

Hazard	Route	Basis
STOT-single exposure	-	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

[cont...]

# SAFETY DATA SHEET

BRIWAX SPRAYWAX

Page: 6

## 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

## 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

## 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1263

### 14.2. UN proper shipping name

### 14.3. Transport hazard class(es)

**Transport class:** 3

### 14.4. Packing group

**Packing group:** III

### 14.5. Environmental hazards

**Environmentally hazardous:** No

**Marine pollutant:** No

### 14.6. Special precautions for user

**Special precautions:** No special precautions.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

[cont...]

# SAFETY DATA SHEET

BRIWAX SPRAYWAX

Page: 7

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H410: Very toxic to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.