Regulation EC No 1907/2006 Art.31

 Productname :
 GS5 GASKET STRIPPER
 Creationdate :
 30.03.20 Version : 3.0

 Ref.Nr.:
 BDS002226_3_20200330 (EN)
 Replaces:
 BDS002226_20190313

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

GS5 GASKET STRIPPER

Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd. Wylds Road Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom

Tel.: +44 1278 727200 Fax.: +44 1278 425644 E-mail: hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosol, category 2

Flammable aerosol.

Pressurised container: May burst if heated.

Classification is based on test data.

Health: Carcinogenicity, category 2

Suspected of causing cancer . Skin irritation, category 2 Causes skin irritation. Eye irritation, category 2 Causes skin irritation.

Specific target organ toxicity - single exposure, category 3

May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 3



Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD

Regulation EC No 1907/2006 Art.31

 Productname :
 GS5 GASKET STRIPPER
 Creationdate :
 30.03.20 Version : 3.0

 Ref.Nr.:
 BDS002226_3_20200330 (EN)
 Replaces:
 BDS002226_20190313

Harmful to aquatic life with long lasting effects.

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:

dichloromethane; methylene chloride

Hazard pictogram(s):





Signal word: Warning

Hazard statement(s): H223 : Flammable aerosol.

H229: Pressurised container: May burst if heated.

H351: Suspected of causing cancer.

H315: Causes skin irritation.

H319 : Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H412: Harmful to aquatic life with long lasting effects.

Precautionary statement(s): P102 : Keep out of reach of children.

P210: Keep away from heat, hot surfaces, sparks, open flames and other

ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use. P201: Obtain special instructions before use.

P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area.

P280 : Wear protective gloves/protective clothing/eye protection/face

protection.

P308/313 : IF exposed or concerned: Get medical advice/attention.

P410/412: Protect from sunlight. Do not expose to temperatures exceeding

50°C/122°F.

P501-2: Dispose of contents/container to an authorised waste collection point.

Regulation (EC) No

648/2004 on detergents:

aromatic hydrocarbons 5 - 15 %

haloganatad hydroca

halogenated hydrocarbons> 30 %

2.3. Other hazards

The product does not contain any PBT or vPvB substances.

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures



2/11

CRC Industries UK Limited

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD

Regulation EC No 1907/2006 Art.31

Creationdate: 30.03.20 Version: 3.0 Productname: **GS5 GASKET STRIPPER** Ref.Nr.: BDS002226 20190313 BDS002226 3 20200330 (EN) Replaces:

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dichloromethane; methylene chloride	01-2119480404- 41	75-09-2	200- 838-9	50- 75	Carc. 2, Skin Irrit. 2, Eye Irrit. 2, STOT SE 3	H351,H315,H319,H336	
ethanol; ethyl alcohol	01-2119457610- 43	64-17-5	200- 578-6	5-10	Flam. Liq. 2, Eye Irrit. 2	H225,H319	B,X,W
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926- 20	68512- 91-4	270- 990-9	5-10	Press. Gas, Flam. Gas 1	H280,H220	K,G
Hydrocarbons, C10, aromatics,	01-2119463583- 34	-	(918- 811-1)	5-10	STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H336,H304,H411	Q
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558- 25	67-63-0	200- 661-7	<1	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	В
butanone; ethyl methyl ketone	01-2119457290- 43	78-93-3	201- 159-0	<1	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	А

Explanation notes

A: substance with Community workplace exposure limit

B: substance with national established workplace exposure limit

G: exempted from the obligation to register in accordance with art.2(7) of REACH Regulation No 1907/2006

K: not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Q: The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

W: Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

X: SCL (specific concentration limit)in accordance with art.10 of CLP Regulation No 1272/2008

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes : If substance has got into eyes, immediately wash out with plenty of water

Seek medical advice

Contact with skin: Remove contaminated clothing immediately and drench affected skin with

plenty of water. Then wash with soap and water

Seek medical attention if irritation persists

Inhalation: Fresh air, keep warm and at rest.

If breathing is difficult give oxygen

Apply artificial respiration only if patient is not breathing

Seek immediate medical attention

Ingestion: Do not induce vomiting

Rinse mouth with water (do not swallow)

If swallowed seek medical advice immediately and show this container or

label.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation: May cause irritation.

High concentrations may cause narcotic effects.

Symptoms: sore throat, cough, shortness of breath, severe breathing

difficulties, headache



Regulation EC No 1907/2006 Art.31

 Productname :
 GS5 GASKET STRIPPER
 Creationdate :
 30.03.20 Version : 3.0

 Ref.Nr.:
 BDS002226_3_20200330 (EN)
 Replaces:
 BDS002226_20190313

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents

may induce chemical pneumonia.

Symptoms: abdominal pain, dizziness, diarrhea, cough, headache

Skin contact : May cause irritation.

Prolonged skin contact will result in defatting of the skin, leading to irritation,

and in some cases, dermatitis Symptoms: redness and pain

Eye contact : May cause irritation.

Symptoms: redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice: If any symptoms should occur, seek medical advice.

If you feel unwell, seek medical advice (show the label where possible

Methylene chloride is classified as carcinogenic Cat.2

In case of repeated exposures, regular medical examination is advised

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C Forms hazardous decomposition products CO,CO2,HCl chlorinated compounds

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes Substance evolves toxic fumes, wear self-contained breathing apparatus

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up



Regulation EC No 1907/2006 Art.31

GS5 GASKET STRIPPER Creationdate: 30.03.20 Version: 3.0 Productname: Ref.Nr.: BDS002226 3 20200330 (EN) Replaces: BDS002226 20190313

Absorb spillage in suitable inert material Wash spill site with water and detergent

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition

Take precautionary measures against static discharges

Equipment should be earthed

Use explosion-proof electrical/ventilating/lighting/.../equipment.

Use only non-sparking tools.

Do not breathe aerosols or vapours.

Ensure adequate ventilation

Avoid contact with skin and eyes.

Wash thoroughly after use

Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C.

Keep in a cool, dry, well ventilated place

Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits:

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:		-	-
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
dichloromethane; methylene chloride	75-09-2	TWA	100 ppm
		STEL	200 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm
National established exposure limits, United Kingdom			
ethanol; ethyl alcohol	64-17-5	TWA	1000 ppm



Regulation EC No 1907/2006 Art.31

Creationdate: 30.03.20 Version: 3.0 Productname: **GS5 GASKET STRIPPER** Ref.Nr.: BDS002226 3 20200330 (EN) Replaces: BDS002226 20190313

propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
dichloromethane; methylene chloride	75-09-2	TWA	100 ppm
		STEL	300 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm
National established exposure limits, Ireland			•
ethanol; ethyl alcohol	64-17-5	STEL	1000 ppm
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	TWA	200 ppm
		STEL	400 ppm
dichloromethane; methylene chloride	75-09-2	TWA	50 ppm
		STEL	-
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm

8.2. Exposure controls

Control procedures: Ensure adequate ventilation

Keep away from heat and sources of ignition

Take precautions to avoid contact with skin and eyes when handling the Personal protection:

product.

Ensure adequate ventilation

inhalation: In case of insufficient ventilation, wear suitable respiratory equipment.

recommended respiratory protection: Air purifying respirator equiped with organic gas/vapor cartridge (type AX)

Wear suitable protective gloves hands and skin:

The breakthrough time of the glove should be longer than the total duration of

product use. If work lasts longer than the breakthrough time, gloves should be

changed part-way through.

Recommended gloves: (polyvinylalcohol)

eyes: Wear safety eyewear according to EN 166.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state : Liquid under pressure.

colour: Colorless. odour: Solvent. Not applicable. : Hg Boiling point/range: Not available.

Flash point: None

Not available. **Evaporation rate:** Explosion limits: upper limit: Not available. lower limit : Not available. Vapour pressure: Not available.

Relative density: 1.18 g/cm3 (@ 20°C). Solubility in water : Insoluble in water

> 200 °C Auto-ignition:

Viscosity: 80 mPa.s (@ 20°C).



Regulation EC No 1907/2006 Art.31

GS5 GASKET STRIPPER Productname: Ref.Nr.: BDS002226_3_20200330 (EN) Creationdate: Replaces:

30.03.20 Version: 3.0 BDS002226 20190313

9.2. Other information

VOC = volatile organic compounds

1180 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2,HCI traces of chlorine and phosgene

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	Causes skin irritation.
serious eye damage/irritation:	Causes serious eye irritation.
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	Suspected of causing cancer.
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met



7 / 11

CRC Industries UK Limited

Regulation EC No 1907/2006 Art.31

Productname: **GS5 GASKET STRIPPER** Creationdate: 30.03.20 Version: 3.0 Ref.Nr.: Replaces: BDS002226 20190313 BDS002226_3_20200330 (EN)

Information on likely routes of exposure:

Inhalation: May cause irritation.

High concentrations may cause narcotic effects.

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents

may induce chemical pneumonia.

Skin contact: Irritating to skin Eye contact : Irritating to eyes

Toxicological data:

Hazardous ingredient	CAS-nr.	method	
ethanol; ethyl alcohol	64-17-5	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	LD50 oral rat	5840 mg/kg
		LC50 inhal.rat	> 25000 mg/l
		LD50 derm.rabit	13900 mg/kg
dichloromethane; methylene chloride	75-09-2	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rat	> 2000 mg/kg
butanone; ethyl methyl ketone	78-93-3	LD50 oral rat	> 2000 mg/kg
Hydrocarbons, C10, aromatics,	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	4688 mg/m3
		LD50 derm.rabit	> 2000 mg/kg

May cause damage to organs through prolonged or repeated exposure. Methylene chloride is classified as carcinogenic Cat.2

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3 Harmful to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
ethanol; ethyl alcohol	64-17-5	LC50 fish	> 100 mg/l
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	1000 mg/l
		LC50 fish	9640 mg/l
		EC50 daphnia	9714 mg/l
dichloromethane; methylene chloride	75-09-2	IC50 algae	> 662 mg/l
		LC50 fish	193 mg/l
		EC50 daphnia	27 mg/l
Hydrocarbons, C10, aromatics,	-	IC50 algae	> 10 mg/l
		LC50 fish	2-5 mg/l
		EC50 daphnia	3-10 mg/l



Regulation EC No 1907/2006 Art.31

Productname: **GS5 GASKET STRIPPER** Ref.Nr.: BDS002226_3_20200330 (EN) Creationdate: Replaces:

30.03.20 Version: 3.0 BDS002226 20190313

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

no bioaccumulation expected

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

No experimental data available GWP (global warming potential): 7

SECTION 13: Disposal considerations

13.1. Waste treatment methods

SECTION 14: Transport information

14.1. UN number

UN-number: 1950

14.2. UN proper shipping name

Proper shipping name: **AEROSOLS**

14.3. Transport hazard class(es)

Class: 2.1 Subsidiary risk: 6.1 ADR/RID - Classification code: 5TF

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards



Regulation EC No 1907/2006 Art.31

 Productname :
 GS5 GASKET STRIPPER
 Creationdate :
 30.03.20 Version : 3.0

 Ref.Nr.:
 BDS002226_3_20200330 (EN)
 Replaces:
 BDS002226_20190313

ADR/RID - Environmentally

hazardous:

IMDG - Marine pollutant: No

IATA/ICAO - Environmentally

hazardous:

No

No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H220: Extremely flammable gas.

H225: Highly flammable liquid and vapour.

H280: Contains gas under pressure; may explode if heated.

H304 : May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H351: Suspected of causing cancer.

H411: Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE: Classification according to Regulation (EC) No 1272/2008

acronyms and synonyms: TWA = time weight average

STEL = short time exposure limit VOC = volatile organic compounds PBT = persistant bioaccumulative toxic vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.



Regulation EC No 1907/2006 Art.31

Productname: **GS5 GASKET STRIPPER** Ref.Nr.: BDS002226_3_20200330 (EN) Creationdate: Replaces:

30.03.20 Version: 3.0 BDS002226_20190313

	_		
-		- ma	-
1111			
		-	4
	20 W		