

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : SUPERGLUE HV

1.2 Relevant identified uses of the substance or mixture and uses advised against

Product use : Sealant/adhesive

1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company
Site 41
Knowsthorpe Way
Cross Green Industrial Estate
Leeds
West Yorkshire LS9 0SW
United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Skin irritation, Category 2 H315: Causes skin irritation.

Eye irritation, Category 2 H319: Causes serious eye irritation.

Specific target organ toxicity - single exposure, Category 3, Respiratory system H335: May cause respiratory irritation.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Warning

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



Hazard statements	:	H315 H319 H335	Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.
Precautionary statements	:	Prevention: P261 P280 Response: P312 P337 + P313 Storage: P403 + P233 Disposal: P501	Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Wear protective gloves/ eye protection/ face protection. Call a POISON CENTER/doctor if you feel unwell. If eye irritation persists: Get medical advice/ attention. Store in a well-ventilated place. Keep container tightly closed. Dispose of contents/ container to an approved waste disposal plant.

Hazardous components which must be listed on the label:

- ethyl 2-cyanoacrylate

Additional Labelling

EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Registration number	Classification	Concentration (% w/w)
ethyl 2-cyanoacrylate	7085-85-0 230-391-5 01-2119527766-29-XXXX	Eye Irrit. 2; H319 STOT SE 3; H335 Skin Irrit. 2; H315	>= 50 - <= 100

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



1,4-dihydroxybenzene	123-31-9 204-617-8	Carc. 2; H351 Muta. 2; H341 Acute Tox. 4; H302 Eye Dam. 1; H318 Skin Sens. 1; H317 Aquatic Acute 1; H400	< 0,25
----------------------	-----------------------	--	--------

SECTION 4: First aid measures

4.1 Description of first aid measures

- General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.
- If inhaled : Move to fresh air.
Consult a physician after significant exposure.
- In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.
- In case of eye contact : Immediately flush eye(s) with plenty of water.
Remove contact lenses.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

- Symptoms : Cough
Respiratory disorder
Excessive lachrymation
Erythema
Dermatitis
See Section 11 for more detailed information on health effects and symptoms.
- Risks : Causes skin irritation.
Causes serious eye irritation.
May cause respiratory irritation.
- irritant effects

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Deny access to unprotected persons.

6.2 Environmental precautions

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Do not breathe vapours or spray mist.
Avoid exceeding the given occupational exposure limits (see section 8).
Do not get in eyes, on skin, or on clothing.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Follow standard hygiene measures when handling chemical products

Advice on protection against : Normal measures for preventive fire protection.

fire and explosion

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Store in original container. Keep in a well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Observe label precautions. Store in accordance with local regulations.

Further information on storage stability : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters *	Basis *
ethyl 2-cyanoacrylate	7085-85-0	STEL	0,3 ppm 1,5 mg/m3	GB EH40
1,4-dihydroxybenzene	123-31-9	TWA	0,5 mg/m3	GB EH40
Further information	Where no specific short-term exposure limit is listed, a figure three times the long-term exposure should be used			

*The above mentioned values are in accordance with the legislation in effect at the date of the release of this safety data sheet.

8.2 Exposure controls

Personal protective equipment

Eye protection : Safety glasses with side-shields
 Eye wash bottle with pure water

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.

Suitable for short time use or protection against splashes:
 Butyl rubber/nitrile rubber gloves (0,4 mm)
 Contaminated gloves should be removed.
 Suitable for permanent exposure:
 Viton gloves (0.4 mm),
 breakthrough time >30 min.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345,

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019



BUILDING TRUST



Version 2.2

Print Date 03.01.2020

long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.

Respiratory protection : Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
organic vapor filter (Type A)
A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm
Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficient to keep the concentrations under the occupational exposure limits then respiration protection measures must be used.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : liquid

Colour : colourless

Odour : slight

Odour Threshold : No data available

pH : No data available

Melting point/range / Freezing point : No data available

Boiling point/boiling range : No data available

Flash point : ca. 80 °C
Method: closed cup

Evaporation rate : No data available

Flammability (solid, gas) : No data available

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : No data available

Relative vapour density : No data available

Density : ca. 1,05 g/cm³ (20 °C)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



Solubility(ies)	
Water solubility	: soluble
Solubility in other solvents	: No data available
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: Not applicable
Decomposition temperature	: No data available
Viscosity	
Viscosity, dynamic	: No data available
Viscosity, kinematic	: > 7 mm ² /s (40 °C)
Explosive properties	: No data available
Oxidizing properties	: No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

No decomposition if stored and applied as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2



BUILDING TRUST



Print Date 03.01.2020

Components:

1,4-dihydroxybenzene:

Acute oral toxicity : Acute toxicity estimate: 500 mg/kg
Method: Converted acute toxicity point estimate

Skin corrosion/irritation

Causes skin irritation.

Serious eye damage/eye irritation

Causes serious eye irritation.

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

May cause respiratory irritation.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

Components:

1,4-dihydroxybenzene:

M-Factor (Acute aquatic toxicity) : 10

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

12.6 Other adverse effects

Product:

Additional ecological information : There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.
- European Waste Catalogue : 08 04 09* waste adhesives and sealants containing organic solvents or other dangerous substances
- Contaminated packaging : 15 01 10* packaging containing residues of or contaminated by dangerous substances

SECTION 14: Transport information

14.1 UN number

- ADR** : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : UN 3334

14.2 UN proper shipping name

- ADR** : Not regulated as a dangerous good

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



IMDG : Not regulated as a dangerous good
IATA : Aviation regulated liquid, n.o.s.
((ethyl 2-cyanoacrylate)

14.3 Transport hazard class(es)

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : 9

14.4 Packing group

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA (Cargo)
Packing group : Not assigned by regulation
Labels : Miscellaneous Dangerous Goods
IATA (Passenger)
Packing group : Not assigned by regulation
Labels : Miscellaneous Dangerous Goods

14.5 Environmental hazards

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA (Passenger)
Environmentally hazardous : no
IATA (Cargo)
Environmentally hazardous : no

14.6 Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

International Chemical Weapons Convention (CWC) : Not applicable
Schedules of Toxic Chemicals and Precursors

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed
(=> 0.1 %).

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH Information: All substances contained in our Products are
- registered by our upstream suppliers, and/or
- registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

Volatile organic compounds : Law on the incentive tax for volatile organic compounds (VOCV)
no VOC duties

Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations
Health and Safety at Work Act 1974 & Subsidiary Regulations
Control of Substances Hazardous to Health Regulations (COSHH)
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this mixture by the supplier.

SECTION 16: Other information

Full text of H-Statements

H302 : Harmful if swallowed.
H315 : Causes skin irritation.
H317 : May cause an allergic skin reaction.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



H318	:	Causes serious eye damage.
H319	:	Causes serious eye irritation.
H335	:	May cause respiratory irritation.
H341	:	Suspected of causing genetic defects.
H351	:	Suspected of causing cancer.
H400	:	Very toxic to aquatic life.

Full text of other abbreviations

Acute Tox.	:	Acute toxicity
Aquatic Acute	:	Short-term (acute) aquatic hazard
Carc.	:	Carcinogenicity
Eye Dam.	:	Serious eye damage
Eye Irrit.	:	Eye irritation
Muta.	:	Germ cell mutagenicity
Skin Irrit.	:	Skin irritation
Skin Sens.	:	Skin sensitisation
STOT SE	:	Specific target organ toxicity - single exposure
GB EH40	:	UK. EH40 WEL - Workplace Exposure Limits
GB EH40 / TWA	:	Long-term exposure limit (8-hour TWA reference period)
GB EH40 / STEL	:	Short-term exposure limit (15-minute reference period)
ADR	:	European Agreement concerning the International Carriage of Dangerous Goods by Road
CAS	:	Chemical Abstracts Service
DNEL	:	Derived no-effect level
EC50	:	Half maximal effective concentration
GHS	:	Globally Harmonized System
IATA	:	International Air Transport Association
IMDG	:	International Maritime Code for Dangerous Goods
LD50	:	Median lethal dosis (the amount of a material, given all at once, which causes the death of 50% (one half) of a group of test animals)
LC50	:	Median lethal concentration (concentrations of the chemical in air that kills 50% of the test animals during the observation period)
MARPOL	:	International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
OEL	:	Occupational Exposure Limit
PBT	:	Persistent, bioaccumulative and toxic
PNEC	:	Predicted no effect concentration
REACH	:	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
SVHC	:	Substances of Very High Concern
vPvB	:	Very persistent and very bioaccumulative

Further information

Classification of the mixture:

Skin Irrit. 2	H315
Eye Irrit. 2	H319
STOT SE 3	H335

Classification procedure:

Calculation method
Calculation method
Calculation method

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SUPERGLUE HV

Revision Date 21.06.2019

Version 2.2

Print Date 03.01.2020



BUILDING TRUST



The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.



Changes as compared to previous version !

GB / EN